

Common Mode Inductors/EMI Filters

Special Features

- Reduce conductive EMI emission
- High inductance, compact size
- High attenuation at low frequency
- Dielectric strength 3750VRMS
- Coil wound on VW-1 rated plastic bobbin
- Core mounted horizontal or vertical
- Operating temperature -55 to +105°C


7300 Series			
Part Number	L (mH) Min. @ 1KHz	I, DC* (A)	DCR (Ω) Max.
7350	0.5	1.5	0.12
7351	1	1.2	0.22
7352	2	0.85	0.4
7353	5	0.5	1.0
7354	8	0.4	2.0
7355	10	0.35	2.2
7356	22	0.27	4.0

Also available as RoHS compliant.

Notes

* Rated current to cause 35°C maximum temperature rise

Add H or V mounting style after P/N



Vertical Core Mount

Horizontal Core Mount

Dimensions: mm

J.W. Miller
MAGNETICS

306 E. Alondra Blvd. Gardena, CA 90247-1059 • Phone (310) 515-1720 • FAX (310) 515-1962

www.jwmiller.com