

## Housing - HC-B 24-TFL-76/O1STM40S - 1644685

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON sleeve housing B24, for single locking latch, height 76 mm, without support 1x M40, lateral conductor exit



### Key commercial data

Packing unit	1 pc
GTIN	 4 017918 907877
Weight per Piece (excluding packing)	337.21 GRM
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### Dimensions

Height	76 mm
Width	43 mm
Length	120 mm

#### Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

Note	For contact inserts HC-B24, BB46, BBB64, D64, DD108, M
Type	B24
Housing type	Sleeve housings
Locking type	for single locking latch
No. of cable outlets	1

## Housing - HC-B 24-TFL-76/O1STM40S - 1644685

### Technical data

#### General

Cable exit	Lateral
Screw connection	none
Type of the screw connection	1x M40
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray

### Classifications

#### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

#### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437


#### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

### Drawings

## Housing - HC-B 24-TFL-76/O1STM40S - 1644685

Dimensioned drawing



---

Phoenix Contact 2014 © - all rights reserved  
<http://www.phoenixcontact.com>