




REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₂	REVISED	08/04/94	AD

ELECTRICAL	MECHANICAL	ENVIRONMENTAL
Nominal Impedance (Ohms) <u>50</u>	Interface Dimensions	Temperature Rating <u>-65°C to +125°C</u>
Frequency Range (GHz) <u>DC to 4</u>	BNC <u>MIL-STD-348A Fig. 301.2</u>	Vibration <u>MIL-STD-202, Method 204, Condition D</u>
Volt Rating (VRMS MAX)	OSM <u>MIL-STD-348A Fig. 310.1</u>	Shock <u>MIL-STD-202, Method 213, Condition I</u>
@ Sea Level <u>335</u>	Recommended Mating Torque	Thermal Shock <u>MIL-STD-202, Method 107, Condition C,</u>
VSWR <u>1.30 Max at 0.5 to 4.0 GHz</u>	<u>4-6 In-Lbs</u>	
Insertion Loss (dB MAX) <u>0.2√f(GHz)</u>	Mating Characteristics:	Moisture Resistance <u>MIL-STD-202, Method 106</u>
RF Leakage (dB MIN) <u>-55, 2 to 3 GHz</u>	BNC OSM	Corrosion - <u>MIL-STD-202, Method 101, Condition B, 5% salt spray</u>
Corona, 70,000 Ft (VRMS MIN) <u>250</u>	Insertion (Lbs Max) <u>2.0</u> <u>N/A</u>	
Dielectric Withstanding Voltage	Withdrawal (Oz Min) <u>2.0</u> <u>N/A</u>	
(VRMS MIN) @ Sea Level <u>1500</u>	Force to Engage/Disengage	
Contact Resistance (Milliohms MAX)	Longitudinal	
Center Contact <u>4.1</u>	Force (Lb Max) <u>3.0</u> <u>N/A</u>	
Outer Contact <u>2.2</u>	Torque (In-Lb Max) <u>2.5</u> <u>2.0</u>	
RF High Potential @ Sea Level	Contact Retention	
(VRMS MIN @ 5 MHz) <u>670</u>	Axial (Lbs Min) <u>6.0</u>	
I.R.(Megohms MIN) <u>5000</u>	Radial (In-Oz) <u>N/A</u>	
	Weight (Grams) <u>TBD</u>	

HOUSING (OSB)	BRASS PER ASTM-B-16 HALF HARD	NICKEL PLATE PER QQ-N-290
HOUSING (OSM) COUPLING NUT	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER ASTM-A380
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
RETAINING RING	BERYLLIUM COPPER PER ASTM B 194, ALLOY C17200, CONDITION H	N/A
GASKET	SILICONE RUBBER PER ZZ-R-765	N/A
COMPONENT	MATERIAL	FINISH
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°		
DRAWN BY <u>DRW</u> DATE <u>6/6/67</u> CHECKED BY <u>KWW</u> <u>6-9-77</u> APPD BY <u>RMF</u> <u>6/9/77</u>		
These drawings and specifications are the property of M/A-COM Interconnect Division and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.		
USE ASS'Y PROCEDURE NO. AP. <u>N/A</u>		
AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599		
TITLE <u>BNC JACK TO OSM PLUG ADAPTER</u>		
SIZE <u>B</u>	CODE IDENT NO. <u>26805</u>	REV <u>01₂</u>
SCALE <u>4:1</u>	SHEET 1 OF 1	

CUSTOMER DRAWING

AMP PART # 1058083-1
SHEET 1 OF 1 REV A