

			<table><tr><th colspan="4">REVISIONS</th></tr><tr><th>REV</th><th>DESCRIPTION</th><th>DATE</th><th>APPROVED</th></tr><tr><td>01 0</td><td>RELEASED</td><td>3/20/98</td><td><i>[Signature]</i></td></tr><tr><td>C</td><td>REVISED PER 0S14-0146-02</td><td>GV 21MAY03</td><td>JGH</td></tr></table>				REVISIONS				REV	DESCRIPTION	DATE	APPROVED	01 0	RELEASED	3/20/98	<i>[Signature]</i>	C	REVISED PER 0S14-0146-02	GV 21MAY03	JGH																																																																									
			REVISIONS																																																																																												
			REV	DESCRIPTION	DATE	APPROVED																																																																																									
01 0	RELEASED	3/20/98	<i>[Signature]</i>																																																																																												
C	REVISED PER 0S14-0146-02	GV 21MAY03	JGH																																																																																												
<table><tr><th>ELECTRICAL</th><th>MECHANICAL</th><th>ENVIRONMENTAL</th></tr><tr><td>Nominal Impedance (Ohms) 50</td><td>Interface Dimensions</td><td>TEMPERATURE RATING -65° TO +125°C</td></tr><tr><td>Frequency Range (GHz) DC to 18</td><td>DESC SPEC 85071</td><td>Vibration MIL-STD-202, Method 204, Condition D</td></tr><tr><td>Volt Rating (VRMS MAX) @ Sea Level 335</td><td>Mating Characteristics:</td><td>Shock MIL-STD-202, Method 213, Condition I</td></tr><tr><td>VSWR N/A</td><td>Insertion (MAX Lbs) N/A</td><td>Thermal Shock MIL-STD-202, Method 107, Condition B</td></tr><tr><td>Insertion Loss (dB MAX) N/A</td><td>Withdrawal (MIN Oz) N/A</td><td>Moisture Resistance MIL-STD-202, Method 106</td></tr><tr><td>RF Leakage (dB MIN) (Interface Only, Fully Mated) -(90-F(GHz))</td><td>Force to Engage (In-Lbs MAX) 3 & Disengage (In-Lbs MAX) 1.5</td><td>Corrosion - MIL-STD-202, Method 101, Condition B</td></tr><tr><td>Corona, 70,000 Ft (VRMS MIN) 250</td><td>Center Contact Captivation</td><td></td></tr><tr><td>Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1000</td><td>Axial (Lbs) 6</td><td></td></tr><tr><td>Contact Resistance (Milliohms MAX)</td><td>Weight (Grams) TBD</td><td></td></tr><tr><td>Center Contact 2.0</td><td></td><td></td></tr><tr><td>Outer Contact 2.0</td><td></td><td></td></tr><tr><td>Cable to Housing N/A</td><td></td><td></td></tr><tr><td>RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670</td><td></td><td></td></tr><tr><td>I.R.(Megohms MIN) 5000</td><td></td><td></td></tr></table>			ELECTRICAL	MECHANICAL	ENVIRONMENTAL	Nominal Impedance (Ohms) 50	Interface Dimensions	TEMPERATURE RATING -65° TO +125°C	Frequency Range (GHz) DC to 18	DESC SPEC 85071	Vibration MIL-STD-202, Method 204, Condition D	Volt Rating (VRMS MAX) @ Sea Level 335	Mating Characteristics:	Shock MIL-STD-202, Method 213, Condition I	VSWR N/A	Insertion (MAX Lbs) N/A	Thermal Shock MIL-STD-202, Method 107, Condition B	Insertion Loss (dB MAX) N/A	Withdrawal (MIN Oz) N/A	Moisture Resistance MIL-STD-202, Method 106	RF Leakage (dB MIN) (Interface Only, Fully Mated) -(90-F(GHz))	Force to Engage (In-Lbs MAX) 3 & Disengage (In-Lbs MAX) 1.5	Corrosion - MIL-STD-202, Method 101, Condition B	Corona, 70,000 Ft (VRMS MIN) 250	Center Contact Captivation		Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1000	Axial (Lbs) 6		Contact Resistance (Milliohms MAX)	Weight (Grams) TBD		Center Contact 2.0			Outer Contact 2.0			Cable to Housing N/A			RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670			I.R.(Megohms MIN) 5000			<table><tr><td>HOUSING</td><td>STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303</td><td>GOLD PLATE PER MIL-G-45204</td></tr><tr><td>DIELECTRIC</td><td>PTFE FLUOROCARBON PER ASTM-D-1457</td><td>N/A</td></tr><tr><td>CENTER CONTACT</td><td>BRASS PER ASTM B 16</td><td>GOLD PLATE PER MIL-G-45204</td></tr><tr><td>O-RING</td><td>FLOUROSILICONE PER MIL-R-25988, CLASS I, TYPE I.</td><td>N/A</td></tr><tr><td>COMPONENT</td><td>MATERIAL</td><td>FINISH</td></tr><tr><td colspan="3">UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES</td></tr><tr><td>FRAC. ± 1/64</td><td>DEC. ± .005</td><td>ANGLES ± 1°</td></tr><tr><td colspan="3">DRAWN BY <i>S. Morby</i> DATE 1/22/98</td></tr><tr><td colspan="3">CHECKED BY <i>[Signature]</i></td></tr><tr><td colspan="3">APP'D BY <i>[Signature]</i> 3/20/98</td></tr><tr><td colspan="3">USE ASS'Y PROCEDURE</td></tr><tr><td colspan="3">NO. AP. N/A</td></tr><tr><td colspan="3">TITLE OSP PRINTED CIRCUIT BOARD PLUG RECEPTACLE - STRAIGHT TERMINAL</td></tr><tr><td>SIZE B</td><td>CODE IDENT NO. 26805</td><td>REV 01 0</td></tr><tr><td>SCALE 5:1</td><td colspan="2">SHEET 1 OF 1</td></tr></table>			HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	GOLD PLATE PER MIL-G-45204	DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A	CENTER CONTACT	BRASS PER ASTM B 16	GOLD PLATE PER MIL-G-45204	O-RING	FLOUROSILICONE PER MIL-R-25988, CLASS I, TYPE I.	N/A	COMPONENT	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES			FRAC. ± 1/64	DEC. ± .005	ANGLES ± 1°	DRAWN BY <i>S. Morby</i> DATE 1/22/98			CHECKED BY <i>[Signature]</i>			APP'D BY <i>[Signature]</i> 3/20/98			USE ASS'Y PROCEDURE			NO. AP. N/A			TITLE OSP PRINTED CIRCUIT BOARD PLUG RECEPTACLE - STRAIGHT TERMINAL			SIZE B	CODE IDENT NO. 26805	REV 01 0	SCALE 5:1	SHEET 1 OF 1	
ELECTRICAL	MECHANICAL	ENVIRONMENTAL																																																																																													
Nominal Impedance (Ohms) 50	Interface Dimensions	TEMPERATURE RATING -65° TO +125°C																																																																																													
Frequency Range (GHz) DC to 18	DESC SPEC 85071	Vibration MIL-STD-202, Method 204, Condition D																																																																																													
Volt Rating (VRMS MAX) @ Sea Level 335	Mating Characteristics:	Shock MIL-STD-202, Method 213, Condition I																																																																																													
VSWR N/A	Insertion (MAX Lbs) N/A	Thermal Shock MIL-STD-202, Method 107, Condition B																																																																																													
Insertion Loss (dB MAX) N/A	Withdrawal (MIN Oz) N/A	Moisture Resistance MIL-STD-202, Method 106																																																																																													
RF Leakage (dB MIN) (Interface Only, Fully Mated) -(90-F(GHz))	Force to Engage (In-Lbs MAX) 3 & Disengage (In-Lbs MAX) 1.5	Corrosion - MIL-STD-202, Method 101, Condition B																																																																																													
Corona, 70,000 Ft (VRMS MIN) 250	Center Contact Captivation																																																																																														
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1000	Axial (Lbs) 6																																																																																														
Contact Resistance (Milliohms MAX)	Weight (Grams) TBD																																																																																														
Center Contact 2.0																																																																																															
Outer Contact 2.0																																																																																															
Cable to Housing N/A																																																																																															
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670																																																																																															
I.R.(Megohms MIN) 5000																																																																																															
HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	GOLD PLATE PER MIL-G-45204																																																																																													
DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A																																																																																													
CENTER CONTACT	BRASS PER ASTM B 16	GOLD PLATE PER MIL-G-45204																																																																																													
O-RING	FLOUROSILICONE PER MIL-R-25988, CLASS I, TYPE I.	N/A																																																																																													
COMPONENT	MATERIAL	FINISH																																																																																													
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES																																																																																															
FRAC. ± 1/64	DEC. ± .005	ANGLES ± 1°																																																																																													
DRAWN BY <i>S. Morby</i> DATE 1/22/98																																																																																															
CHECKED BY <i>[Signature]</i>																																																																																															
APP'D BY <i>[Signature]</i> 3/20/98																																																																																															
USE ASS'Y PROCEDURE																																																																																															
NO. AP. N/A																																																																																															
TITLE OSP PRINTED CIRCUIT BOARD PLUG RECEPTACLE - STRAIGHT TERMINAL																																																																																															
SIZE B	CODE IDENT NO. 26805	REV 01 0																																																																																													
SCALE 5:1	SHEET 1 OF 1																																																																																														

CUSTOMER DRAWING

AMP PART # 1253111-1
SHEET 1 OF 1 REV C