

89 Series

Metal-Mite® Aluminum Housed Axial Terminal Wirewound, 1% Tolerance



The 89 Series is a high-performance axial type resistor. These molded-construction metal-housed resistors are available in higher power ratings than standard axial resistors and are better suited to withstanding vibration, shock and harsh environmental conditions.

The 89 Series Metal-Mite® resistors are aluminum housed to maintain high stability during operation and to permit secure mounting to chassis surfaces.

The metal housing also provides heat-sinking capabilities.

FEATURES

- High Stability: $\pm 0.5\%$ ΔR
- High power to size ratio
- Metal housing allows chassis mounting and provides heat sink capability

SERIES SPECIFICATIONS

Series	Wattage	Ohms	Voltage
805	5	0.10-25K	210
810	10	0.10-50K	320
825	25	0.005-75K	520
850	50	0.005-100K	1170

Non-Inductive versions available. Insert "N" before tolerance code.
Example: 850NF560

CHARACTERISTICS

Housing	Metal, anodized aluminum
Internal Coating	Silicone
Core	Ceramic
Terminals	Solder-coated axial
Derating	Linearly from 100% @ +25°C to 0% @ +275°C.
Tolerance	$\pm 1\%$ and $\pm 5\%$ (other tolerances available).
Power rating	Rating is based on chassis mounting area and temperature stability. Proper heat sink as follows: 5W and 10W units, 4" x 6" x 2" x .040" Aluminum chassis; 25W units, 5" x 7" x 2" x .040" Aluminum chassis; 50W units, 12" x 12" x .059" Aluminum panel.
Maximum ohmic values	See chart.
Overload	5 times rated wattage for 5 seconds.
Temperature coefficient	Under 1Ω: ± 90 ppm/°C; 1 to 9.99Ω: ± 50 ppm/°C; 10Ω and over: ± 20 ppm/°C.
Dielectric withstanding voltage	5W and 10W rating, 1000 VAC; 25 and 50W ratings, 2250 VAC.


(continued)

89 Series

Metal-Mite® Aluminum Housed Axial Terminal Wirewound, 1% Tolerance

DIMENSIONS

(in./mm)



Dimensions have changed
as of August 2015

	A max.	B max.	C max.	D max.	E max.	F ±.3mm	G ±.3mm	H max.	J max.	K max.	L ±.25mm
805	0.65" / 16.5	1.18" / 30.0	0.35" / 8.8	0.33" / 8.5	0.63" / 15.9	0.44" / 11.3	0.49" / 12.4	0.18" / 4.5	0.09" / 2.4	0.07" / 1.8	0.09" / 2.4
810	0.83" / 21.0	1.44" / 36.5	0.43" / 11.0	0.44" / 11.2	0.78" / 19.9	0.56" / 14.3	0.63" / 15.9	0.22" / 5.5	0.11" / 2.8	0.07" / 1.8	0.09" / 2.4
825	1.10" / 28.0	2.01" / 51.0	0.58" / 14.8	0.56" / 14.2	1.07" / 27.3	0.72" / 18.3	0.78" / 19.8	0.30" / 7.7	0.20" / 5.2	0.10" / 2.6	0.13" / 3.2
850	1.10" / 28.0	2.85" / 72.5	0.58" / 14.8	0.56" / 14.2	1.93" / 49.1	1.56" / 39.7	0.84" / 21.4	0.33" / 8.4	0.20" / 5.2	0.10" / 2.6	0.13" / 3.2

ORDERING INFORMATION

Ohmic value	Wattage					Ohmic value	Wattage					Ohmic value	Wattage				
	Part No. Prefix ▶ Suffix ▼	5	10	25	50		Part No. Prefix ▶ Suffix ▼	5	10	25	50		Part No. Prefix ▶ Suffix ▼	5	10	25	50
		805F	810F	825F	850F			805F	810F	825F	850F			805F	810F	825F	850F
0.005 — R005			✓	✓		20 — 20R	✓	✓			1,500 — 1K5	✓	✗	✗	✓		
0.010 — R010			✓	✓		25 — 25R	✓	✓			2,000 — 2K0	✓		✗	✗		
0.025 — R025			✓	✓		30 — 30R	✗	✗	✓		2,500 — 2K5	✓	✓	✗	✗		
0.1 — R10			✓	✓		40 — 40R	✗	✓			3,000 — 3K0	✗	✗	✓		✗	
0.3 — R30			✓	✗		50 — 50R	✓	✓	✓	✓	3,500 — 3K5	✗	✗				
0.5 — R50			✓	✗		75 — 75R	✓	✗	✓	✓	4,000 — 4K0	✓	✓				
0.7 — R70			✗	✗		100 — 100	✓	✓	✓	✓	4,500 — 4K5	✓	✓				
1.0 — 1R0	✓	✓	✓	✓		150 — 150	✓	✓	✓	✓	5,000 — 5K0	✓	✓	✓		✓	
1.5 — 1R5	✗	✓				200 — 200	✗	✗	✓	✓	6,000 — 6K0	✗	✗				
2.0 — 2R0	✗	✓	✓	✓		250 — 250	✓	✓	✓	✓	10,000 — 10K	✓	✓	✓	✓		
3.0 — 3R0	✓	✓	✓	✓		300 — 300	✓	✗			15,000 — 15K	✓	✓	✗	✗		
4.0 — 4R0	✗	✓				400 — 400	✗	✗			20,000 — 20K	✓	✗				
5.0 — 5R0	✓	✓	✓	✓		500 — 500	✓	✗	✓	✓	25,000 — 25K	✓	✗		✗		
10.0 — 10R	✓	✓	✓	✓		750 — 750	✗	✓	✓		50,000 — 50K		✗				
15.0 — 15R	✓	✓	✓	✓		1,000 — 1K0	✗	✗	✓	✓	75,000 — 75K			✗			
											100,000 — 100K						

Non-Inductive Winding
Optional (blank = std. winding) RoHS Compliant

805 N F 5 R 0 E

Series: 805 = 5 Watt, 810 = 10 watt, 825 = 25 watt, 850 = 50 watt
Tolerance: F = 1%, J = 5%
Ohms: R005 = 0.005Ω, R10 = 0.1Ω, 1R0 = 1.0Ω, 250 = 250Ω, 1K0 = 1,000Ω, 1K5 = 1,500Ω, 25K = 25,000Ω

✓ = Standard values

✖ = Non-standard values subject to minimum handling charge per item

Shaded values involve very fine resistance wire and should not be used in critical applications without burn-in and/or thermal cycling.

As of September 2006,
the 89 Series is no longer
offered as Mil. Spec.