





1. DIMENSIONS IN [] ARE IN INCHES.
2. 0.6 dB MAX ASSEMBLY LOSS.
3. DIMENSION MEASURED TO END OF CERAMIC CAPILLARY (BACKBONE ASSEMBLY)
4. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702

122+2.44/-0 [4803+96/-0]	9-5492231-9
107+2.14/-0 [4213+84/-0]	9-5492231-8
92+1.84/-0 [3622+72/-0]	9-5492231-2
77+1.54/-0 [3031+61/-0]	7-5492231-7
61+1.22/-0 [2402+48/-0]	6-5492231-1
54+1.08/-0 [2126+43/-0]	5-5492231-4
46+0.92/-0 [1811+36/-0]	4-5492231-6
37+0.74/-0 [1457+29/-0]	3-5492231-7
31+0.62/-0 [1220+24/-0]	3-5492231-1
22+0.44/-0 [866+17/-0]	2-5492231-2
20+0.4/-0 [787+15/-0]	2-5492231-0
16+0.32/-0 [630+13/-0]	1-5492231-6
15+0.30/-0 [591+12/-0]	1-5492231-5
13+0.26/-0 [512+10/-0]	1-5492231-3
10+0.20/-0 [394+8/-0]	1-5492231-0
7+0.20/-0 [276+8/-0]	5492231-7
5+0.20/-0 [197+8/-0]	5492231-5
4+0.20/-0 [157+8/-0]	5492231-4
3+0.20/-0 [118+8/-0]	5492231-3
2+0.20/-0 [79+8/-0]	5492231-2
1+0.10/-0 [39+4/-0]	5492231-1
L	
PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
METERS [INCHES]	
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -
MATERIAL -	FINISH -

DWN	C.S.VASU	08 NOV 05
CHK	J.DUNCAN	08 NOV 05
APVD	J.DUNCAN	08 NOV 05
PRODUCT SPEC	-	
APPLICATION SPEC	-	
WEIGHT	-	
CUSTOMER DRAWING		

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608

NAME

CABLE ASSEMBLY, FIBER OPTIC, 62.5/125 DUAL RISER, ESCON TO ESCON, OPTIMATE

SIZE

A2

CAGE CODE

00779

DRAWING NO

C=5492231

RESTRICTED TO

-

SCALE

NTS

SHEET

1

OF

1

REV

A