





WIRING FACE



MATING FACE



NOTES

MATERIALS		SEE TABLE	
SHELL		STAINLESS STEEL	
COUPLING LATCH		LUBRICATED RED SILICON	
O'RING			
PERFORMANCES CHARACTERISTICS			
MECHANICAL			
TEMPERATURE CLASS		IEC61984/UL1977	-40°C TO 105°C
DURABILITY		IEC61984	500 MATE / UNMATE CYCLES
SEALING IN MATED CONDITIONS		IEC60529	IP68 1BAR DURING 1WEEK
		DIN40050	IP69K
SEALING IN UNMATED CONDITIONS		IEC60529	IP67 WITH CAPS
POLLUTION DEGREE		IEC61984	4
CORROSION SALT SPRAY			MIN 1000H
FLAMMABILITY		UL94	MATERIAL RATING: 5VA
OUTDOOR SUITABILITY (UV RESIST)		UL746C	MATERIAL RATING: (f1)
SCOOP PROOF			
ELECTRICAL			
TOUCH PROOF		IEC60529	IP2X
POWER AND GROUND LINES:			
NOMINAL CURRENT		UL1977	16A WITH AWG14 WIRE / 13A WITH AWG16 WIRE
NOMINAL CURRENT		IEC61984	16A WITH 2.5MM² WIRE / 13A WITH 1.5MM² WIRE AT 60°C
NOMINAL VOLTAGE		UL1977	600V
NOMINAL VOLTAGE		IEC61984	250VAC 4KV 4 FOR CLASS II
		IEC61984	500VAC 6KV 4 FOR CLASS I
SIGNAL CONTAC (a,b,c) LINES:			
NOMINAL VOLTAGE		IEC61984	48V AC
NOMINAL CURRENT		IEC61984	5A

- ROHS COMPLIANT
- COUNTERPART REFERENCE UTL RECEPTACLE OR FREE HANGING
 - CONNECTORS ARE DELIVERED AS PRE-ASSEMBLED KIT
 - CONNECTOR BLOCKS ACCEPTS TRIM TRIO CONTACTS #16 AND #20 , R*M* OR S*M* TYPES
 - CONTACTS TO BE ORDERED SEPARATELY.
 - WARNING: PHASE AND SIGNAL CONTACTS ARE FEMALE VERSION AND GROUND CONTACT IS MALE VERSION
 - UNIT IN MM

P/N	SHELL' S MATERIAL
UTL6102G1W3S	PA GF REINFORCED BLACK COLOR
UTL6102G1W3S03	PA GF REINFORCED LIGHT GREY COLOR

P/N : SEE TABLE

a	17/07/13	New drawing		
ISS	DATE	Latest modification - by: --		MOD N°
Designed by:		R.M.	Date:17/07/13	CUSTOMER DRAWING
TITLE		FEMALE PLUG LAYOUT 6 CONTACTS SIZE 10		
		UTL CONNECTOR		
Scale	1/1		General linear Tolerances: ± 0,2	NPRDS / PROJECT UTL
SOURIAU		WWW.SOURIAU.COM		This document is the property of SOURIAU It must not be reproduced or communicated without permission
FORMAT	A2	SOURIAU DRG N° UTL1-0050A-C01		SHEET 1 / 1