



MLE-140-01-G-DV



CLM-115-02-L-D

MLE-120-01-G-DV



CLM-125-02-F-D

Surface
SMT
Mount

1mm PITCH SOCKETS

CLM, MLE SERIES

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?CLM

Insulator Material:

Black LCP

Contact Material:

Phosphor Bronze

Plating: Au, Sn or SnPb

over 50µ" (1,27µm) Ni

Current Rating:

3A @ 80°C ambient

Operating Temp Range:

-55°C to +125°C

Contact Resistance:

15 mΩ max

Insertion Depth:

Top Entry = (1,40mm) .055"

min., Bottom Entry = (2,41mm)

.095" min. (Add board

thickness for correct post OAL)

Insertion Force:

1.5oz (0,42N) average

Normal Force:

40 grams (0,39N) average

Withdrawal Force:

.75oz (0,21N) average

Max Cycles:

100 with 10µ" (0,25µm) Au

RoHS Compliant:

Yes

Note: Some lengths, styles and options are non-standard, non-returnable.

CLM

1

NO. PINS
PER ROW

02

PLATING
OPTION

D

OPTIONS


Mates with:
FTM, FTMH, MW

**TIGER
CLAW**
CONTACT



02 thru 50

PIN/ROW	A
04-15	(3,56) .140
16-50	(7,11) .280



PROCESSING

- **Max Processing Temp:**
230°C for 60 seconds, or 260°C for 20 seconds 3x
- **Lead-Free Solderable:**
Yes
- **SMT Lead Coplanarity:**
(0,10mm) .004" max (02-25)
(0,15mm) .006" max (26-50)

—F
= Gold flash on
contact,
Matte Tin on tail

—L
= 10µ" (0,25µm)
Gold on contact,
Matte Tin on tail

—BE
= Bottom Entry
(Required for bottom entry)

—K
= (3,50mm) .138" DIA
Polyimide film Pick & Place Pad
(7 positions minimum)

—P
= Pick & Place Pad
(7 positions minimum)

—PA
= Pick & Place Pad with
integral Alignment Pin

—TR
= Tape & Reel Packaging

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?MLE

Insulator Material:

Black LCP

Contact Material:

BeCu

Operating Temp Range:

-55°C to +125°C

Plating:

Au over 10µ" (0,25µm) Ni

Insertion Depth:

(1,63mm) .064" to (3,18mm)

.125" with (0,38mm) .015"

wipe, pass-through, or

(2,44mm) .096" minimum

for bottom entry

Insertion Force:

2.70oz (0,75N) average

Withdrawal Force:

0.50oz (0,14N) average

RoHS Compliant:

Yes

Note: Some lengths, styles and options are non-standard, non-returnable.

MLE

1

NO. PINS
PER ROW

01

PLATING
OPTION

DV


OPTIONS

Mates with:
FTM, FTMH, MW

**TIGER
BEAM**
CONTACT



02 thru 50



—G
= 10µ" (0,25µm)
Gold

—A
= Alignment Pin
(3 positions minimum)
Metal or plastic at Samtec
discretion.

—K
= (4,00mm) .1575" DIA
Polyimide film Pick & Place Pad
(5 positions minimum)

—P
= Metal Pick & Place Pad
(5 positions minimum)

—TR
= Tape & Reel Packaging

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 • Fax: 812-948-5047
SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0 • Fax: +49 (0) 89 / 89460-299
SAMTEC NORDIC/BALTIC • Tel: +46-84477280 • Fax: +46-87420413
SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 • Fax: 65 6841-1502
SAMTEC HONG KONG • Tel: 852-26904858 • Fax: 852-26904842
SAMTEC JAPAN • Tel: 045-475-1385 • Fax: 045-475-1340
SAMTEC KOREA • Tel: 82-31-717-5685 • Fax: 82-31-717-5681
SAMTEC SILICON VALLEY • Tel: 408-395-5900 • Fax: 408-395-1520
SAMTEC FRANCE • Tel: 01 60 95 06 60 • Fax: 01 60 95 06 61
SAMTEC ISRAEL • Tel: 972-3-7526600 • Fax: 972-3-7526690
SAMTEC CHINA • Tel: 86-21-61103766 • Fax: 86-21-5423 4575
SAMTEC SOUTH AFRICA • Tel: 27 11 454 4317 • Fax: 27 86 6714432
SAMTEC UK • Tel: 01236 739292 • Fax: 01236 727113
SAMTEC ITALY • Tel: 39 039 6890337 • Fax: 39 039 6890315
SAMTEC INDIA • Tel: +91-80-3272 1612 • Fax: +91-80-4152 8187
SAMTEC TAIWAN • Tel: 886-2-2735-6109 • Fax: 886-2-2735-5036
SAMTEC ANZ • Tel: 613 9512 7747 • Fax: 613 9512 7745