

PCLH - 206A1SP,000 Product Details

PCLH - 206A1SP,000

(5 - 1461059 - 8)

TE Internal Number: 5 - 1461059 - 8

Active

Add to Part List

View 3D PDF

Industrial Relays (General Purpose)

Always EU RoHS compliant but not ELV Compliant

([Statement of Compliance](#))

Product Highlights:

?

 PCL Series

?

 Contact Arrangement = 2 Form C, DPDT, 2 C/O

?

 Contact Current Rating = 15 Amps.

?

 Monostable Coil Magnetic System

?

 Input Voltage = 110 VAC, 120 VAC

View all Features

 |

Find Similar Products

Quick Links

Check Pricing & Availability

Search for Tooling

Product Feature Selector

Contact Us About This Product

Request Samples

NEW!

Documentation & Additional Information	
Product Drawings: ? PCLH-20_A1SP_CUSTOMER_DWG (PDF, English) Catalog Pages/Data Sheets: ? None Available Product Specifications: ? None Available Application Specifications: ? None Available onlinecomponents.com THE ONLINE DISTRIBUTOR OF ELECTRONIC COMPONENTS Instruction Sheets: ? None Available CAD Files: (CAD Format & Compression Information) ? 2D Drawing (DXF, Version A) ? 3D Model (IGES, Version A) ? 3D Model (STEP, Version A) List all Documents	Additional Information: ? Product Line Information Related Products: ? Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: ? Termination Type = Through Hole Electrical Characteristics: ? Contact Current Rating (Amps.) = 15 ? Input Voltage (VAC) = 110, 120 ? Coil Resistance (?) = 3400 ? Actuating System = AC ? Coil Power, Nominal (VA) = 1.40 Body Related Features: ? Series = PCL Contact Related Features: ? Mounting Options = PC Board ? Enclosure = Dust Cover ? FCC Part 68 Isolation = No ? Relay Type = PCB ? Contact Material = Silver Alloy ? Approx. Dimensions (L x W x H) (mm [in]) = 27.50 x 21.20 x 33.60 [1.083 x .835 x 1.323] ? Approved Standards = UL Recognized, CSA Certified	

 Configuration Related Features: ? [Contact Arrangement](#) = 2 Form C, DPDT, 2 C/O ? [Coil Magnetic System](#) = Monostable ? [Coil Suppression Diode](#) = Without ? [Coil Selection Criteria](#) = Nominal Voltage ? Coil Latching = Without ? [LED Indicator](#) = Without Industry Standards: ? [RoHS/ELV Compliance](#) = RoHS/Not ELV Compliant ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260° C, Wave solder capable to 265°C, Reflow solder capable to 245°C, Reflow solder capable to 260°C, Pin -in -Paste capable to 245°C, Pin in -Paste capable to 260°C ? RoHS/ELV Compliance History = Always was RoHS not ELV compliant Other: ? Brand = OEG |