










LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		A	REVISED PER ECR-16-004163	29MAR2016	RS	DD
			AI	REVISED PER ECR-16-009104	23JUN2016	RS	DD

NOTES:

1. PACKAGED IN TAPE AND REEL PER IEA-481 SPECIFICATIONS.
2. MATERIAL AND FINISH:
 - HOUSING: THERMAL PLASTIC
 - PIN CONTACT:BRASS
 - SOCKET CONTACT:COPPER ALLOY
 - FINISH:SELECT GOLD OVER NICKEL.
3. SUITABLE FOR SMT PROCESS.
4. TO ENSURE THE FUNCTION OF THE MINIATURE HERMAPHRODITIC B-B CONNECTORS, THE PCB WITH MINIATURE HERMAPHRODITIC B-B CONNECTORS SHOULD BE FIXED ON THE HEAT SINK OR SOME OTHER RIGID SUBSTRATE.
CUSTOMER CAN USE SCREW (SHOW AS APPLICATION VIEW), GLUE, OR SOME OTHER METHOD TO FIX THE PCBs.
FOR DETAIL PLEASE REFER TO INSTRUCTION SHEET 411-106013




2213611-1 (2 MATING PARTS)
SCALE 6:1

2213611-2(2 MATING PARTS)
SCALE 6:1

2213611-3(2 MATING PARTS)
SCALE 6:1

NATURAL	6P	19.0	2213611-3
NATURAL	4P	13.0	2213611-2
NATURAL	2P	7.0	2213611-1
COLOR	POSITION	DIM A	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAVL.S	26DEC2014		 TE Connectivity					
		CHR DONALD DECKER	26DEC2014							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	MINIATURE HERMAPHRODITIC BOARD TO BOARD CONNECTOR					
		APVD DONALD DECKER								
0 PLC ±.5 1 PLC ±0.13 2 PLC ±0.13 3 PLC ±0.13 4 PLC ±0.0001 ANGLES ±.		PRODUCT SPEC 108-106050		SIZE				CAGE CODE	DRAWING NO	RESTRICTED TO
		APPLICATION SPEC 114-106050								
MATERIAL	FINISH	WEIGHT		A200779		G-2213611		-		
-	-			CUSTOMER DRAWING		SCALE	3.1	SHEET 1 OF 2	REV A1	

