



EVERLIGHT ELECTRONICS CO.,LTD.

DATA SHEET

MODEL NO : 28-21SURC/S530-A2/TR8

DATE : 2000.03.08

DEPARTMENT : R&D1

REVISION : 1.1

RECEIVED			
☒ MASS PRODUCTION			
☐ PRELIMINARY			
☐ CUSTOMER DESIGN			
DEVICE NUMBER : DLE-282-084			
PAGE : 5			
CUSTOMER	DESIGNER	CHECKER	APPROVER

1.1	Append new page and data	2000.03.08
1.0	New data sheet approve	-----
REV	DESCRIPTION	RELEASE DATE

OFFICE : NO 25,Lane 76,Chung Yang Rd,Sec.3 Tucheng, Taipei 236, Taiwan, R.O.C.

TEL : 886-2-2267-2000,2266-9936 (22 Lines)

FAX : 886-2-2267-6189

<http://www.everlight.com>



EVERLIGHT ELECTRONICS CO.,LTD.

DEVICE NUMBER : DLE-282-084

REV : 1.1

ECN : 20000456

PAGE : 1/5

1.3 mm Height Subminiature , Axial Flat Top LEDs

MODEL NO : 28-21SURC/S530-A2/TR8

Features :

- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- I.C. compatible.
- EIA std package.
- Mono-color type.


Descriptions :

- The 28-21 SMD taping is much smaller than leaded components. Thusenable smaller board size.Higher packing density. Reduced storage space and finally smaller equipment to be obtained.
- Besides, light weight makes them ideal for miniature application, etc.
- Furthermore by automation assembly machines the accuracy is anticipated.

Applications :

- Small indicator for outdoor appications.
- Flat backlight for LCD, switch and symbol.
- Indicator and backlight in office equipment.
- Indicator and backlight for battery driven equipment.
- Indicator and backlight for audio and video equipment.
- Automotive : backlighting in dashboard and switch.
- Telecommunication : indicator and backlighting in telephone and fax.
- General use.

Package Dimensions :



PART NO.	CHIP		Lens Color
	Material	Emitted Color	
28-21SURC/S530-A2/TR8	AlGaInP	Hyper Red	Water Clear

Office : NO 25,Lane 76, Chung Yang Rd, Sec.3, Tucheng, Taipei 236, Taiwan, R.O.C.

TEL : 886-2-2267-2000,2266-9936(22 Lines)

FAX : 886-2-2267-6189

http: //www.everlight.com



EVERLIGHT ELECTRONICS CO.,LTD.


DEVICE NUMBER : DLE-282-084 REV : 1.1

ECN : PAGE : 2/5


1.3 mm Height Subminiature , Axial Flat Top LEDs

MODEL NO : 28-21SURC/S530-A2/TR8

■ Package Dimensions



■ Loaded Quantity Per Reel 2000 Pcs/Reel



1. All dimensions are in millimeters.
2. Lead spacing is measured where the lead emerge from the package
3. Protruded resin under flange 1.5 mm (0.59") max.



EVERLIGHT ELECTRONICS CO.,LTD.

DEVICE NUMBER : DLE-282-084

REV : 1.1

ECN : _____

PAGE : 3/5

1.3 mm Height Subminiature , Axial Flat Top LEDs

MODEL NO : 28-21SURC/S530-A2/TR8

■ Absolute Maximum Ratings at Ta = 25°C

Parameter	Symbol	Rating	Unit
Reverse Voltage	Vr	5	V
Forward Current	If	25	mA
Operating Temperature	Topr	-40 ~ +85	°C
Storage Temperature	Tstg	-40 ~ +100	°C
Soldering Temperature	Tsol	260 ± 5 for 5 sec	°C
Electrostatic Discharge	ESD	2000	V
Power Dissipation	Pd	60	mW
Peak Forward Current(Duty 1/10 @ 1KHZ)	If(Peak)	160	mA

■ Electronic Optical Characteristics :

Parameter	Symbol	MIN.	TYP.	MAX.	Unit	Condition
Luminous intensity	Iv	---	2	---	mcd	If = 2 mA
Luminous intensity	Iv	12	29	---	mcd	If = 20 mA
Viewing Angle	2θ 1/2	---	150	---	deg	
Peak Wavelength	λ p	---	632	---	nm	
Dominant Wavelength	λ d	---	624	---	nm	
Spectrum Radiation Bandwidth	Δ λ	---	20	---	nm	
Forward Voltage	Vf	---	2.0	2.4	V	Vr=5V
Reverse Current	Ir	---	---	10	μ A	



EVERLIGHT ELECTRONICS CO.,LTD.

DEVICE NUMBER : DLE-282-084

REV : 1.1

ECN :

PAGE : 4/5

1.3 mm Height Subminiature , Axial Flat Top LEDs

MODEL NO : 28-21SURC/S530-A2/TR8

■ Reliability Test Item And Condition

NO.	Item	Test Conditions	Test Hours/ Cycle	Sample Size	Ac/Re
1	Solder Heat	TEMP : 260°C ± 5 °C	5 sec	76 pcs	0/1
2	Temperature Cycle	H : +85°C 30 min ↑ 5 min ↓ L : -55°C 30 min	50 cycle	76 pcs	0/1
3	Thermal Shock	H : +100°C 5 min ↑ 10 sec ↓ L : -10°C 30 min	50 cycle	76 pcs	0/1
4	High Temperature Storage	TEMP. : +100°C	1000 hrs	76 pcs	0/1
5	Low Temperature Storage	TEMP. : -55°C	1000 hrs	76 pcs	0/1
6	DC Operating Life	If = 20 mA	1000 hrs	76 pcs	0/1
7	High Temperature / High Humid	85°C / 85% R.H.	1000 hrs	76 pcs	0/1



EVERLIGHT ELECTRONICS CO.,LTD.

DEVICE NUMBER : DLE-282-084

REV : 1.1

ECN :

PAGE : 5/5

1.3 mm Height Subminiature , Axial Flat Top LEDs

MODEL NO : 28-21SURC/S530-A2/TR8

Typical Electro-Optical Characteristic Curves

