

Surface Mount Voltage Variable Attenuator

1600 to 2200 MHz

VACC-22+ VACC-22



Maximum Ratings

Operating Temperature	-45°C to 85°C
Storage Temperature	-55°C to 100°C
Absolute Max. Control Current	10mA
Absolute Max. RF Input Level	15 dBm

Pin Connections

RF IN	2
V CONTROL 1	8
V CONTROL 2	4
RF OUT	6
GROUND	1,3,5,7


Outline Drawing



Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H	J	
.150	.150	.050	.008	.036	.018	.062	.028	.022	
3.81	3.81	1.27	0.20	0.91	0.46	1.57	0.71	0.56	
K	L	M	N	P	Q	R	S	T	wt
.017	.014	.036	.018	.062	.028	.037	.037	.017	grams
0.43	0.36	0.91	0.46	1.57	0.71	0.94	0.94	0.43	0.06

Demo Board MCL P/N: TB-250 Suggested PCB Layout (PL-148)



CAPACITORS C1,C3: .01 uF, 0803 SIZE
CAPACITORS C2,C4: 6.8 pF, 0803 SIZE
RESISTORS R1,R2: 2 KOhm, 0402 SIZE

- NOTES: 1. COPLANAR WAVEGUIDE PARAMETERS ARE SHOWN FOR ROGERS RO4350 WITH DIELECTRIC THICKNESS .020" ± .0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.
2. IF YOUR PCB DESIGN RULES ALLOW, GROUND VIAS SHOULD BE PLACED UNDER THE LAND PATTERN FOR BETTER RF PERFORMANCE.


- DENOTES PCB COPPER LAYOUT
■ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Features

- frequency range, 1600-2200 MHz
- IP3, 42 dBm typ.
- minimum current at min. attenuation
- low insertion loss

Applications

- variable gain amplifier
- feed forward amps
- ALC circuits



BLUE CELL™

CASE STYLE: GF995
PRICE: \$3.95 ea. QTY (25)

+ RoHS compliant in accordance with EU Directive (2002/95/EC)

See our web site for RoHS Compliance methodologies and qualifications.


Electrical Specifications

FREQ. (MHz)	INSERTION LOSS (dB) at 0V control voltage		ATTENUATION (dB)		IP3* (dBm)		RETURN LOSS (dB)		CONTROL VOLTAGE**
	Min.	Max.	Typ.	Min.	Typ.	Min.	Input Typ.	Output Typ.	
1600-2200		1.2 1.5	25 23		42 38		20	20	0-5

* Input IP3 tested with two tones separated by 1 MHz at 7 dBm each and 0V control voltage.


**Using recommended control port biasing.

recommended control port biasing configuration




R1, R2: 2K OHM CHIP RESISTOR (0402, AS CLOSE AS POSSIBLE TO THE DEVICE)
C1, C2: 0.01 UF CHIP CAPACITOR (0603)
C3, C4: 6.8 PF CHIP CAPACITOR (0603)







equivalent schematic of DUT



VACC-22 ATTENUATION Vs. FREQUENCY Vs. CONTROL VOLTAGE (ENTIRE RANGE)



Performance Curves



Performance Curves

