


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [47018-4000](#)
Status: **Active**
Overview: [Serial ATA Host Receptacles](#)
Description: 1.27mm Pitch Serial ATA Host Receptacle, Mating Height 5.15mm, Gold (Au) Flash, Surface Mount, Light Tin Solder Area, Right Angle, Top Mount Type, 22 Circuits, Lead-Free



Series

image - Reference only

Documents:

3D Model	Product Specification PS-67492-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Receptacles
Series	47018
Application	Board-to-Board, Signal
Comments	Top Mount Type
Overview	Serial ATA Host Receptacles
Product Name	Serial ATA
UPC	822350330817

Physical

Circuits (Loaded)	22
Circuits (maximum)	22
Color - Resin	Black
Durability (mating cycles max)	500
Flammability	94V-0
Glow-Wire Compliant	No
Keying to Mating Part	Yes
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	3.048/g
Number of Rows	1
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Termination	2.032µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-35°C to +85°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	15V DC

Solder Process Data

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[47018Series](#)

Mates With
[877030001](#)

Lead-free Process Capability
Process Temperature max. C

Reflow Capable (SMT only)
230

Material Info

Reference - Drawing Numbers

Electrical Model Document
Product Specification
Sales Drawing

EE-47018-002
PS-67492-001
SD-47018-001

This document was generated on 10/25/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION