


SURFACE MOUNT ALUMINUM ELECTROLYTIC CAPACITORS

67	CA Series	2,000 hrs. at 85°C
74	CB Series	1,000 hrs. at 105°C
81	CE Series	2,000 hrs. at 105°C

REEL DIMENSIONS


Unit : mm



SIZE CODE	A	B	C	D	E	F	G
W	14	14	14	18	18	26	26

TAPING DIMENSIONS

Unit : mm




CASE SIZE	(ØD mm)	W	A	B	P1	F	t2
A	Ø3	12.0	3.4	3.5	8.0	5.5	5.8
B	Ø4	12.0	4.7	4.6	8.0	5.5	5.8
C	Ø5	12.0	5.7	5.7	12.0	5.5	5.8
D	Ø6.3	16.0	7.0	7.0	12.0	7.5	5.8
E	Ø8 x 6.2	16.0	8.7	8.7	12.0	7.5	6.8
F	Ø8 x 10.2	24.0	8.7	8.7	16.0	11.5	11.0
G	Ø10 x 10.2	24.0	10.7	10.7	16.0	11.5	11.0

PACKAGING QUANTITY

CASE SIZE	ØD	INNER PACKAGING (PCS/REEL)	OUTER PACKAGING (PCS/BOX)
A	Ø3	2000	20000
B	Ø4	2000	20000
C	Ø5	1000	10000
D	Ø6.3	1000	10000
E	Ø8 x 6.2	1000	10000
F	Ø8 x 10.2	500	3000
G	Ø10 x 10.2	500	3000




REEL DIMENSIONS

Unit : mm



SIZE CODE	a	b	c
A (Ø3)	0.6	2.2	1.5
B (Ø4)	1.0	2.5	1.6
C (Ø5)	1.5	2.8	1.6
D (Ø6.3)	1.8	3.2	1.6
E (Ø8 x 6.2)	2.2	4.0	1.6
F (Ø8 x 10.2)	3.1	4.0	2.0
G (Ø10 x 10.2)	4.6	4.1	2.0

REFLOW SOLDER ING TEMPERATURE PROFILE

Peak Temperature / Duration [Temp. $\geq 200^{\circ}\text{C}$ (s)]Peak Temperature / Duration [Temp. $\geq 200^{\circ}\text{C}$ (s)]

Surface Mount Aluminum Electrolytic

CA Series




FEATURE


For General Purposes Series with 85°C 2000 Hours

Suitable for AV (TV, Video, Audio), Personal Computer, Home Appliance

MARKING



DIMENSIONS



() Reference Size

Unit : mm

SIZE CODE	DØ	L	A	H	I	W	P	K
A	3.0	5.4	3.3	4.5 Max.	1.5	0.55 ± 0.1	0.6	$0.35^{+0.15}_{-0.20}$
B	4.0	5.4	4.3	5.5 Max.	1.8	0.65 ± 0.1	1.0	$0.35^{+0.15}_{-0.20}$
C	5.0	5.4	5.3	6.5 Max.	2.2	0.65 ± 0.1	1.5	$0.35^{+0.15}_{-0.20}$
D	6.3	5.4	6.6	7.8 Max.	2.6	0.65 ± 0.1	2.2	$0.35^{+0.15}_{-0.20}$
E	8.0	6.2	8.3	9.4 Max.	3.4	0.65 ± 0.1	2.2	$0.35^{+0.15}_{-0.20}$
F	8.0	10.2	8.3	10.0 Max.	3.4	0.90 ± 0.2	3.1	0.70 ± 0.20
G	10.0	10.2	10.3	12.0 Max.	3.5	0.90 ± 0.2	4.6	0.70 ± 0.20

SPECIFICATION

ITEM	CHARACTERISTIC									
Operation Temperature Range	-40 to +85°C									
Rated Working Voltage Range	4 to 100 V.DC									
Capacitance Tolerance	± 20% (120Hz / +25°C)									
Leakage Current (25°C)	Polarized : $I \leq 0.01CV$ or 3 (μA)									
	Whichever is greater after 2 minutes application of DC rated working voltage at 25°C.									
	I : Leakage Current (μA)		C : Rated Capacitance (μF)			V : Working Voltage (V)				
Dissipation Factor (tanδ)	Polarized () : D.F of Downsized									
(120Hz / +25°C)	W V (V)	4	6.3	10	16	25	35	50	63	100
	D.F	Ø3	0.37	0.28 (0.37)	0.22	0.18	0.16	0.14	0.14	—
		Ø4 ~ Ø6.3	0.35	0.26 (0.35)	0.20 (0.30)	0.16 (0.26)	0.14 (0.16)	0.12 (0.14)	0.12 (0.14)	—
		Ø8 ~ Ø10	0.40	0.35	0.26	0.20	0.16	0.14	0.12	0.18
Low Temperature Stability	Impedance Ratio at 120Hz									
	W V (V)	4	6.3	10	16	25	35	50	63	100
	-25 / +20°C	7	4	3	3	2	2	2	3	3
	-40 / +20°C	15	8	6	4	4	3	3	4	4
Load Life	After 2000 hours application of W V at +85°C, the capacitor shall meet following limits.									
	Capacitance Change	$\leq \pm 20\%$ of Initial Value								
	Dissipation Factor	$\leq 200\%$ of Initial Specified Value								
	Leakage Current	$\leq$ Initial Specified Value								
Shelf Life	At +85°C no voltage application after 1000 hours and then through the aging treatment, the capacitor shall meet limits for load life characteristics.									

CASE SIZE & MAX RIPPLE CURRENT

Max. Ripple Current (mA) r.m.s. (120Hz / +85°C)

[illegible]

PARTS NUMBER SYSTEM

Example : 10μF, 16V

CA	016	M	0010	R	E	B	-	0405
Series Name	Voltage Code	Tolerance	Capacitance Code	Package Code	Life Code	Size Code		Case Code

CAPACITANCE TOLERANCE		LIFE CODE		SIZE CODE							
M	±20%	E	2000 Hours	Size Code	A	B	C	D	E	F	G
K	±10%	S	1000 Hours	DØ (mm)	3.0 x 5.4	4.0 x 5.4	5.0 x 5.4	6.3 x 5.4	8.0 x 6.2	8.0 x 10.2	10.0 x 10.2
W	-5% ~ +20%	R	Special								

CAPACITANCE CODE																		
Capacitance	0.1	0.22	0.33	0.47	1.0	2.2	3.3	4.7	6.8	10	22	33	47	100	220	330	470	1000
Code	0R10	0R22	0R33	0R47	1R00	2R20	3R30	4R70	6R80	0010	0022	0033	0047	0100	0220	0330	0470	1000

VOLTAGE CODE									
Voltage	4	6.3	10	16	25	35	50	63	100
Code	004	006	010	016	025	035	050	063	100

PACKAGE CODE		CASE CODE								Unit : mm
R	Embossed Plastic Tape Reel	0305	3.0 x 5.4	0405	4.0 x 5.4	05.5	5.0 x 5.4	0605	6.3 x 5.4	
		0806	8.0 x 6.2	0810	8.0 x 10.2	1010	10.0 x 10.2			

STANDARD PRODUCTS

W V (VD.C)	CAP. (μ F)	SIZE (mm)		PART NO.	D.F Max. 120 Hz	LEAKAGE CURRENT (μ A/2 Min.) Max.	RIPPLE CURRENT (mA) r.m.s. 120 Hz / 85°C
		D Ø	L				
4	22	3	5.4	CA004M0022REA-0305	0.37	3.0	19
	33	4	5.4	CA004M0033REB-0405	0.35	3.0	26
	47	4	5.4	CA004M0047REB-0405	0.35	3.0	34
	100	5	5.4	CA004M0100REC-0505	0.35	4.0	61
	220	6.3	5.4	CA004M0220RED-0605	0.35	8.8	82
6.3	22	3	5.4	CA006M0022REA-0305	0.37	3.0	20
	22	4	5.4	CA006M0022REB-0405	0.26	3.0	29
	33	4	5.4	CA006M0033REB-0405	0.35	3.0	22
	33	5	5.4	CA006M0033REC-0505	0.26	3.0	29
	47	5	5.4	CA006M0047REC-0505	0.26	3.0	46
	100	6.3	5.4	CA006M0100RED-0605	0.26	6.3	71
	330	8	6.2	CA006M0330REE-0806	0.35	20.8	300
	470	8	10.0	CA006M0470REF-0810	0.35	29.6	380
	1000	10	10.0	CA006M1000REG-1010	0.35	63.0	700
10	22	4	5.4	CA010M0022REB-0405	0.20	3.0	28
	33	4	5.4	CA010M0033REB-0405	0.30	3.3	29
	33	5	5.4	CA010M0033REC-0505	0.20	3.3	43
	47	5	5.4	CA010M0047REC-0505	0.30	4.7	43
	47	6.3	5.4	CA010M0047RED-0605	0.20	4.7	43
	100	6.3	5.4	CA010M0100RED-0605	0.20	10.0	70
	220	8	6.2	CA010M0220REE-0806	0.26	22.0	250
	330	8	10.0	CA010M0330REF-0810	0.26	33.0	330
	470	8	10.0	CA010M0470REF-0810	0.26	47.0	330
	470	10	10.0	CA010M0470REG-1010	0.26	47.0	400
	1000	10	10.0	CA010M1000REG-1010	0.26	100.0	580
16	6.8	4	5.4	CA016M6R80REB-0405	0.16	3.0	25
	10	3	5.4	CA016M0010REA-0305	0.18	3.0	20
	10	4	5.4	CA016M0010REB-0405	0.16	3.0	28
	22	4	5.4	CA016M0022REB-0405	0.26	3.5	28
	22	5	5.4	CA016M0022REC-0505	0.16	3.5	39
	33	5	5.4	CA016M0033REC-0505	0.16	5.3	35
	47	5	5.4	CA016M0047REC-0505	0.26	7.5	39
	47	6.3	5.4	CA016M0047RED-0605	0.16	7.5	70
	100	6.3	5.4	CA016M0100RED-0605	0.26	16.0	70
	100	8	6.2	CA016M0100REE-0806	0.20	16.0	200
	220	8	10.2	CA016M0220REF-0810	0.20	35.2	280
	330	8	10.2	CA016M0330REF-0810	0.20	52.8	320
	330	10	10.2	CA016M0330REG-1010	0.20	52.8	380
	470	10	10.2	CA016M0470REG-1010	0.20	75.2	420
25	4.7	3	5.4	CA025M4R70REA-0305	0.16	3.0	12
	4.7	4	5.4	CA025M4R70REB-0405	0.14	3.0	22
	10	4	5.4	CA025M0010REB-0405	0.14	3.0	21
	10	5	5.4	CA025M0010REC-0505	0.14	3.0	28
	22	6.3	5.4	CA025M0022RED-0605	0.14	5.5	55
	33	6.3	5.4	CA025M0033RED-0605	0.14	8.3	65
	47	6.3	5.4	CA025M0047RED-0605	0.16	11.8	80




STANDARD PRODUCTS


W V (VD.C)	CAP. (μ F)	SIZE (mm)		PART NO.	D.F Max. 120 Hz	LEAKAGE CURRENT (μ A/2 Min.) Max.	RIPPLE CURRENT (mA) r.m.s. 120 Hz / 85°C
		DØ	L				
25	100	8	6.2	CA025M0100REE-0806	0.16	25.0	91
	100	8	10.0	CA025M0100REF-0810	0.16	25.0	180
	220	8	10.0	CA025M0220REF-0810	0.16	55.0	140
	220	10	10.0	CA025M0220REG-1010	0.16	55.0	310
	330	10	10.0	CA025M0330REG-1010	0.16	82.5	340
35	2.2	3	5.4	CA035M2R20REA-0305	0.14	3.0	8
	3.3	3	5.4	CA035M3R30REA-0305	0.14	3.0	10
	4.7	4	5.4	CA035M4R70REB-0405	0.12	3.0	22
	10	5	5.4	CA035M0010REC-0505	0.12	3.5	30
	22	6.3	5.4	CA035M0022RED-0605	0.12	7.7	60
	33	6.3	5.4	CA035M0033RED-0605	0.14	11.6	70
	33	8	6.2	CA035M0033REE-0806	0.14	11.6	130
	47	8	6.2	CA035M0047REE-0806	0.14	16.5	165
	100	8	10.0	CA035M0100REF-0810	0.14	35.0	140
	100	10	10.0	CA035M0100REG-1010	0.14	35.0	210
	220	10	10.0	CA035M0220REG-1010	0.14	77.0	310
50	0.1	3	5.4	CA050M0R10REA-0305	0.14	3.0	1
	0.1	4	5.4	CA050M0R10REB-0405	0.12	3.0	1
	0.22	3	5.4	CA050M0R22REA-0305	0.14	3.0	2
	0.22	4	5.4	CA050M0R22REB-0405	0.12	3.0	2
	0.33	3	5.4	CA050M0R33REA-0305	0.14	3.0	3
	0.33	4	5.4	CA050M0R33REB-0405	0.12	3.0	3
	0.47	3	5.4	CA050M0R47REA-0305	0.14	3.0	5
	0.47	4	5.4	CA050M0R47REB-0405	0.12	3.0	5
	1	3	5.4	CA050M1R00REA-0305	0.14	3.0	8
	1	4	5.4	CA050M1R00REB-0405	0.12	3.0	10
	2.2	4	5.4	CA050M2R20REB-0405	0.12	3.0	16
	3.3	4	5.4	CA050M3R30REB-0405	0.12	3.0	16
	4.7	4	5.4	CA050M4R70REC-0505	0.12	3.0	23
	10	6.3	5.4	CA050M0010RED-0605	0.12	5.0	35
	22	6.3	5.4	CA050M0022RED-0605	0.12	11.0	70
	22	8	6.2	CA050M0022REE-0806	0.12	11.0	120
	33	8	6.2	CA050M0033REE-0806	0.12	16.5	65
	33	8	10.0	CA050M0033REF-0810	0.12	16.5	110
	47	8	10.0	CA050M0047REF-0810	0.12	23.5	110
	47	10	10.0	CA050M0047REG-1010	0.12	23.5	130
	100	10	10.0	CA050M0100REG-1010	0.12	50.0	250
63	10	8	6.2	CA063M0010REE-0806	0.18	6.3	35
	22	8	10.0	CA063M0022REF-0810	0.18	13.9	40
	33	8	10.0	CA063M0033REF-0810	0.18	20.8	45
	100	10	10.0	CA063M0100REG-1010	0.18	63.0	60
100	3.3	8	6.2	CA100M3R30REE-0806	0.18	3.3	50
	4.7	8	10.2	CA100M4R70REF-0810	0.18	4.7	80
	10	8	10.2	CA100M0010REF-0810	0.18	10.0	85
	22	10	10.2	CA100M0022REG-1010	0.18	22.0	85
	33	10	10.2	CA100M0033REG-1010	0.18	33.0	90

Note : Extended capacitance and voltage values as well as miniaturized products are available on request.




TEMPERATURE CHARACTERISTICS DATA






LOAD LIFE DATA



FREQUENCY CHARACTERISTICS DATA



TEMPERATURE CHARACTERISTICS DATA



CB Series


Surface Mount Aluminum Electrolytic

FEATURE

For General Purposes Series with 105°C 1000 Hours


Suitable for AV (TV, Video, Audio), Personal Computer, Home Appliance

MARKING



DIMENSIONS

SIZE CODE	DØ	L	A	H	I	W	P	K
B	4.0	5.4	4.3	5.5 Max.	1.8	0.65 ± 0.1	1.0	0.35 ^{+0.15} _{-0.20}
C	5.0	5.4	5.3	6.5 Max.	2.2	0.65 ± 0.1	1.5	0.35 ^{+0.15} _{-0.20}
D	6.3	5.4	6.6	7.8 Max.	2.6	0.65 ± 0.1	2.2	0.35 ^{+0.15} _{-0.20}
E	8.0	6.2	8.3	9.5 Max.	3.4	0.65 ± 0.1	2.2	0.35 ^{+0.15} _{-0.20}
F	8.0	10.2	8.3	10.0 Max.	3.4	0.90 ± 0.2	3.1	0.70 ± 0.20
G	10.0	10.2	10.3	12.0 Max.	3.5	0.90 ± 0.2	4.6	0.70 ± 0.20



ITEM	CHARACTERISTIC								
Operation Temperature Range	-40 to +105°C								
Rated Working Voltage Range	6.3 to 100V. DC								
Capacitance Tolerance	± 20% (120Hz / +25°C)								
Leakage Current (25°C)	Polarized : I ≤ 0.01CV or 3 (μA) Whichever is greater after 2 minutes application of DC rated working voltage at 25°C. I : Leakage Current (μA) C : Rated Capacitance (μF) V : Working Voltage (V)								
Dissipation Factor (tanδ) (120Hz / +25°C)	Polarized () : D.F of Downsized W V (V) 6.3 10 16 25 35 50 63 100 D.F Ø4 ~ Ø6.3 0.30 0.22 0.16 0.14 0.12 0.12 0.12 (0.35) (0.30) (0.26) (0.18) (0.14) Ø8 ~ Ø10 0.35 0.26 0.20 0.16 0.14 0.12 0.18 0.18								
Low Temperature Stability	Impedance Ratio at 120Hz W V (V) 6.3 10 16 25 35 50 63 100 -25 / +20°C 4 3 2 2 2 2 3 3 -40 / +20°C 8 6 4 4 3 3 4 4								
Load Life	After 1000 hours application of W V at 105°C, the capacitor shall meet following limits. Capacitance Change ≤ ± 20% of Initial Value Dissipation Factor ≤ 200% of Initial Specified Value Leakage Current ≤ Initial Specified Value								
Shelf Life	At +105°C no voltage application after 1000 hours and then through the aging treatment, the capacitor shall meet limits for load life characteristics.								

Max. Ripple Current (mA) r.m.s. (120Hz / +105°C)

[illegible]

PARTS NUMBER SYSTEM

Example : 10 μ F, 16V

CB	016	M	0010	R	S	B	-	0405
Series Name	Voltage Code	Tolerance	Capacitance Code	Package Code	Life Code	Size Code		Case Code

CAPACITANCE TOLERANCE

M	$\pm 20\%$
K	$\pm 10\%$
W	-5% ~ +20%

LIFE CODE

E	2000 Hours
S	1000 Hours
R	Special

SIZE CODE

Size Code	A	B	C	D	E	F	G
D $\varnothing$ (mm)	3.0 x 5.4	4.0 x 5.4	5.0 x 5.4	6.3 x 5.4	8.0 x 6.2	8.0 x 10.2	10.0 x 10.2

CAPACITANCE CODE

Capacitance	0.1	0.22	0.33	0.47	1.0	2.2	3.3	4.7	10	22	33	47	100	220	330	470
Code	0R10	0R22	0R33	0R47	1R00	2R20	3R30	4R70	0010	0022	0033	0047	0100	0220	0330	0470

VOLTAGE CODE

Voltage	6.3	10	16	25	35	50	63	100
Code	006	010	016	025	035	050	063	100

PACKAGE CODE

R	Embossed Plastic Tape Reel
---	----------------------------

CASE CODE

									Unit : mm
0305	3.0 x 5.4	0405	4.0 x 5.4	05.5	5.0 x 5.4	0605	6.3 x 5.4		
0806	8.0 x 6.2	0810	8.0 x 10.2	1010	10.0 x 10.2				



STANDARD PRODUCTS


W V (V.D.C)	CAP. (μ F)	SIZE (mm)		PART NO.	D.F Max. 120 Hz	LEAKAGE CURRENT (μ A/2 Min.) Max.	RIPPLE CURRENT (mA) r.m.s. 120 Hz / 85°C
		DØ	L				
6.3	22	4	5.4	CB006M0022RSB-0405	0.30	3.0	29
	47	5	5.4	CB006M0047RSC-0505	0.30	3.0	46
	100	6.3	5.4	CB006M0100RSD-0605	0.30	6.3	71
	330	8	10.2	CB006M0330RSF-0810	0.35	20.8	230
10	33	5	5.4	CB010M0033RSC-0505	0.22	3.3	43
	100	6.3	5.4	CB010M0100RSD-0605	0.30	10.0	70
	100	8	6.2	CB010M0100RSE-0806	0.26	10.0	110
	220	8	10.2	CB101M0220RSF-0810	0.26	22.0	160
	470	10	10.2	CB010M0470RSG-1010	0.26	47.0	270
16	10	4	5.4	CB016M0010RSB-0405	0.16	3.0	28
	22	5	5.4	CB016M0022RSC-0505	0.16	3.5	39
	47	6.3	5.4	CB016M0047RSD-0605	0.16	7.5	70
	100	6.3	5.4	CB016M0100RSD-0605	0.26	16.0	100
	220	10	10.2	CB016M0220RSG-1010	0.20	35.2	210
	330	10	10.2	CB016M0330RSG-1010	0.20	52.8	230
	470	10	10.2	CB016M0470RSG-1010	0.20	75.2	340
25	4.7	4	5.4	CB025M4R70RSB-0405	0.14	3.0	22
	10	4	5.4	CB025M0010RSB-0405	0.16	3.0	25
	10	5	5.4	CB025M0010RSC-0505	0.14	3.0	28
	22	6.3	5.4	CB025M0022RSD-0605	0.14	5.5	55
	33	6.3	5.4	CB025M0033RSD-0605	0.14	8.3	65
	47	6.3	5.4	CB025M0047RSD-0605	0.18	11.8	80
	47	8	6.2	CB025M0047RSE-0806	0.16	11.8	91
	100	8	10.2	CB025M0100RSF-0810	0.16	25.0	130
	220	10	10.2	CB025M0220RSG-1010	0.16	55.0	190
	330	10	10.2	CB025M0330RSG-1010	0.16	82.5	340
35	4.7	4	5.4	CB035M4R70RSB-0405	0.12	3.0	22
	10	5	5.4	CB035M0010RSC-0505	0.12	3.5	30
	22	6.3	5.4	CB035M0022RSD-0605	0.12	7.7	60
	33	8	6.2	CB035M0033RSE-0806	0.14	11.6	84
	47	8	10.2	CB035M0047RSF-0810	0.14	16.5	98
	100	10	10.2	CB035M0100RSG-1010	0.14	35.0	160
	220	10	10.2	CB035M0220RSG-1010	0.14	77.0	210

STANDARD PRODUCTS


W V (V.D.C)	CAP. (μ F)	SIZE (mm)		PART NO.	D.F Max. 120 Hz	LEAKAGE CURRENT (μ A/2 Min.) Max.	RIPPLE CURRENT (mA) r.m.s. 120 Hz / 85°C
		D Ø	L				
50	0.1	4	5.4	CB050M0R10RSB-0405	0.12	3.0	1
	0.22	4	5.4	CB050M0R22RSB-0405	0.12	3.0	2
	0.33	4	5.4	CB050M0R33RSB-0405	0.12	3.0	3
	0.47	4	5.4	CB050M0R47RSB-0405	0.12	3.0	5
	1	4	5.4	CB050M1R00RSB-0405	0.12	3.0	10
	2.2	4	5.4	CB050M2R20RSB-0405	0.12	3.0	16
	3.3	4	5.4	CB050M3R30RSB-0405	0.12	3.0	16
	4.7	5	5.4	CB050M4R70RSB-0405	0.12	3.0	23
	10	6.3	5.4	CB050M0010RSD-0605	0.12	5.0	35
	22	8	6.2	CB050M0022RSE-0806	0.12	11.0	70
	33	8	10.2	CB050M0033RSF-0810	0.12	16.5	91
	47	10	10.2	CB050M0047RSG-1010	0.12	23.5	100
	100	10	10.2	CB050M0100RSG-1010	0.12	50.0	120
63	10	8	6.2	CB063M0010RSE-0806	0.18	6.3	25
	22	8	10.2	CB063M0022RSF-0810	0.18	13.9	30
	33	10	10.2	CB063M0033RSG-1010	0.18	20.8	45
	47	10	10.2	CB063M0047RSG-1010	0.18	29.6	50
100	3.3	8	6.2	CB100M3R30RSE-0806	0.18	3.3	30
	4.7	8	10.2	CB100M4R70RSF-0810	0.18	4.7	50
	10	8	10.2	CB100M0010RSF-0810	0.18	10	55
	22	10	10.2	CB100M0022RSG-1010	0.18	22	60
	33	10	10.2	CB100M0033RSG-1010	0.18	33	65

Note : Extended capacitance and voltage values as well as miniaturized products are available on request.


TEMPERATURE CHARACTERISTICS DATA




LOAD LIFE DATA



FREQUENCY CHARACTERISTICS DATA




1μF/50V V 4.0 x 5.4
 10μF/16V V 4.0 x 5.4
 22μF/6.3V V 4.0 x 5.4




10μF/50V V 6.3 x 5.4
 22μF/35V V 6.3 x 5.4
 47μF/16V V 6.3 x 5.4

TEMPERATURE CHARACTERISTICS DATA



1μF/50V V 4.0 x 5.4
 10μF/16V V 4.0 x 5.4
 22μF/6.3V V 4.0 x 5.4



10μF/50V V 6.3 x 5.4
 22μF/35V V 6.3 x 5.4
 33μF/25V V 6.3 x 5.4

Surface Mount Aluminum Electrolytic

CE Series




FEATURE


For General Purposes Series with 105°C 2000 Hours

Suitable for AV (TV, Video, Audio), Personal Computer, Home Appliance

MARKING



DIMENSIONS



() Reference Size

Unit : mm

SIZE CODE	DØ	L	A	H	I	W	P	K
B	4.0	5.4	4.3	5.5 Max.	1.8	0.65 ± 0.1	1.0	0.35 ^{+0.15} _{-0.20}
C	5.0	5.4	5.3	6.5 Max.	2.2	0.65 ± 0.1	1.5	0.35 ^{+0.15} _{-0.20}
D	6.3	5.4	6.6	7.8 Max.	2.6	0.65 ± 0.1	2.2	0.35 ^{+0.15} _{-0.20}
E	8.0	6.2	8.3	9.5 Max.	3.4	0.65 ± 0.1	2.2	0.35 ^{+0.15} _{-0.20}
F	8.0	10.2	8.3	10.0 Max.	3.4	0.90 ± 0.2	3.1	0.70 ± 0.20
G	10.0	10.2	10.3	12.0 Max.	3.5	0.90 ± 0.2	4.6	0.70 ± 0.20

SPECIFICATION

ITEM	CHARACTERISTIC							
Operation Temperature Range	-40 to +105°C							
Rated Working Voltage Range	4 to 50V. DC							
Capacitance Tolerance	± 20% (120Hz / +25°C)							
Leakage Current (25°C)	Polarized : $I \leq 0.01CV$ or 3 (μA)							
	Whichever is greater after 2 minutes application of DC rated working voltage at 25°C.							
	I : Leakage Current (μA)		C : Rated Capacitance (μF)		V : Working Voltage (V)			
Dissipation Factor (tanδ)	Polarized () : D.F of Downsized							
(120Hz / +25°C)	W V (V)	4	6.3	10	16	25	35	50
	D.F	Ø4 ~ Ø6.3	0.50	0.30 (0.35)	0.22 (0.26)	0.16 (0.20)	0.14 (0.18)	0.12 (0.14)
		Ø8 ~ Ø10	0.40	0.35	0.26	0.20	0.16	0.14
Low Temperature Stability	Impedance Ratio at 120Hz							
	W V (V)	4	6.3	10	16	25	35	50
	-25 / +20°C	7	4	3	2	2	2	2
	-40 / +20°C	15	8	6	4	4	3	3
Load Life	After 2000 hours application of W V at 105°C, the capacitor shall meet following limits.							
	Capacitance Change	≤ ± 20% of Initial Value						
	Dissipation Factor	≤ 200% of Initial Specified Value						
	Leakage Current	≤ Initial Specified Value						
Shelf Life	At +105°C no voltage application after 1000 hours and then through the aging treatment, the capacitor shall meet limits for load life characteristics.							

CASE SIZE & MAX RIPPLE CURRENT

Max. Ripple Current (mA) r.m.s. (120Hz / +105°C)

POLARIZED															
μF	CODE	V (CODE)													
		4 (004)		6.3 (006)		10 (010)		16 (016)		25 (025)		35 (035)		50 (050)	
0.1	0R10												4.0 x 5.4	1	
0.22	0R22												4.0 x 5.4	2	
0.33	0R33												4.0 x 5.4	3	
0.47	0R47												4.0 x 5.4	5	
1.0	1R00												4.0 x 5.4	10	
2.2	2R20												4.0 x 5.4	16	
3.3	3R30												4.0 x 5.4	16	
4.7	4R70									4.0 x 5.4	22		5.0 x 5.4	23	
6.8	0068									4.0 x 5.4	25		5.0 x 5.4	23	
10	0010							4.0 x 5.4	28	4.0 x 5.4	28	5.0 x 5.4	28	6.3 x 5.4	35
22	0022			4.0 x 5.4	26			5.0 x 5.4	39			6.3 x 5.4	55	8.0 x 6.2	70
33	0033			4.0 x 5.4	29	5.0 x 5.4	43			6.3 x 5.4	65	8.0 x 6.2	84	8.0 x 10.2	91
47	0047	4.0 x 5.4	34	5.0 x 5.4	46			6.3 x 5.4	70	6.3 x 5.4 8.0 x 6.2	80 91	8.0 x 10.2	98	10 x 10.2	100
100	0100	5.0 x 5.4	61	6.3 x 5.4	71	6.3 x 5.4 8.0 x 6.2	70 110	8.0 x 10.2	120	8.0 x 10.2	130	10 x 10.2	160		
150	0150	6.3 x 5.4	82												
220	0220	6.3 x 5.4	82	8.0 x 10.2	150	8.0 x 10.2	160	10 x 10.2	210	10 x 10.2	190				
330	0330			8.0 x 10.2	230			10 x 10.2	230						
470	0470					10 x 10.2	270							Size	R.C

PARTS NUMBER SYSTEM

Example : 10μF, 16V

CE	016	M	0010	R	E	B	-	0405
Series Name	Voltage Code	Tolerance	Capacitance Code	Package Code	Life Code	Size Code		Case Code

CAPACITANCE TOLERANCE		LIFE CODE		SIZE CODE							
M	±20%	E	2000 Hours	Size Code	A	B	C	D	E	F	G
K	±10%	S	1000 Hours	DØ (mm)	3.0 x 5.4	4.0 x 5.4	5.0 x 5.4	6.3 x 5.4	8.0 x 6.2	8.0 x 10.2	10.0 x 10.2
W	-5% ~ +20%	R	Special								

CAPACITANCE CODE																		
Capacitance	0.1	0.22	0.33	0.47	1.0	2.2	3.3	4.7	6.8	10	22	33	47	100	220	330	470	1000
Code	0R10	0R22	0R33	0R47	1R00	2R20	3R30	4R70	6R80	0010	0022	0033	0047	0100	0220	0330	0470	1000

VOLTAGE CODE									
Voltage	4	6.3	10	16	25	35	50	63	100
Code	004	006	010	016	025	035	050	063	100


PACKAGE CODE		CASE CODE								Unit : mm
R	Embossed Plastic Tape Reel	0305	3.0 x 5.4	0405	4.0 x 5.4	05.5	5.0 x 5.4	0605	6.3 x 5.4	
		0806	8.0 x 6.2	0810	8.0 x 10.2	1010	10.0 x 10.2			

STANDARD PRODUCTS


W V (VD.C)	CAP. (μF)	SIZE (mm)		PART NO.	D.F Max. 120 Hz	LEAKAGE CURRENT (μA/2 Min.) Max.	RIPPLE CURRENT (mA) r.m.s. 120 Hz / 85°C
		D Ø	L				
4	47	4	5.4	CE004M0047REB-0405	0.50	34	34
	100	5	5.4	CE004M0100REC-0505	0.50	4.0	61
	150	6.3	5.4	CE004M0150RED-0605	0.50	6.0	82
	220	6.3	5.4	CE004M0220RED-0605	0.50	8.8	82
6	22	4	5.4	CE006M0022REB-0405	0.30	3.0	26
	33	4	5.4	CE006M0033REB-0405	0.30	3.0	29
	47	5	5.4	CE006M0047REC-0505	0.30	3.0	46
	100	6.3	5.4	CE006M0100RED-0605	0.35	6.3	71
	220	8	10.2	CE006M0220REF-0810	0.35	13.8	150
	330	8	10.2	CE006M0330REF-0810	0.35	20.8	230
10	33	5	5.4	CE010M0033REC-0505	0.22	3.3	43
	100	6.3	5.4	CE010M0100RED-0605	0.26	10.0	70
	100	8	6.2	CE010M0100REE-0806	0.22	10.0	110
	220	8	10.2	CE010M0220REF-0810	0.26	22.0	160
	470	10	10.2	CE010M0470REG-1010	0.26	47.0	270
16	10	4	5.4	CE016M0010REB-0405	0.16	3.0	28
	22	5	5.4	CE016M0022REC-0505	0.16	3.5	39
	47	6.3	5.4	CE016M0047RED-0605	0.16	7.5	70
	100	6.3	5.4	CE016M0100RED-0605	0.20	16.0	120
	220	10	10.2	CE016M0220REG-1010	0.20	35.2	210
	330	10	10.2	CE016M0330REG-1010	0.20	52.8	230
25	4.7	4	5.4	CE025M4R70REB-0405	0.14	3.0	22
	6.8	4	5.4	CE025M6R80REB-0405	0.14	3.0	25
	10	4	5.4	CE025M0010REB-0405	0.14	3.0	28
	33	6.3	5.4	CE025M0033RED-0605	0.14	8.2	65
	47	6.3	5.4	CE025M0047RED-0605	0.18	11.7	80
	47	8	6.2	CE025M0047REE-0806	0.16	11.7	91
	100	8	10.2	CE025M0100REF-0810	0.16	25.0	130
	220	10	10.2	CE025M0220REG-1010	0.16	55.0	190
35	10	5	5.4	CE035M0010REC-0505	0.12	3.5	28
	22	6.3	5.4	CE035M0022RED-0605	0.12	7.7	55
	33	8	6.2	CE035M0033REE-0806	0.14	11.6	84
	47	8	10.2	CE035M0047REF-0810	0.14	16.5	98
	100	10	10.2	CE035M0100REG-1010	0.14	35.0	160
50	0.1	4	5.4	CE050M0R10REB-0405	0.12	3.0	1
	0.22	4	5.4	CE050M0R22REB-0405	0.12	3.0	2
	0.33	4	5.4	CE050M0R33REB-0405	0.12	3.0	3
	0.47	4	5.4	CE050M0R47REB-0405	0.12	3.0	5
	1	4	5.4	CE050M1R00REB-0405	0.12	3.0	10
	2.2	4	5.4	CE050M2R20REB-0405	0.12	3.0	16
	3.3	4	5.4	CE050M3R30REB-0405	0.12	3.0	16
	4.7	5	5.4	CE050M4R70REC-0505	0.12	3.0	23
	6.8	5	5.4	CE050M6R80REC-0505	0.12	3.4	23
	10	6.3	5.4	CE050M0010RED-0605	0.12	5.0	35
	22	8	6.2	CE050M0022REE-0806	0.12	11.0	70
	33	8	10.2	CE050M0033REF-0810	0.12	16.5	91
	47	10	10.2	CE050M0047REG-1010	0.12	23.5	100

Note : Extended capacitance and voltage values as well as miniaturized products are available on request.


TEMPERATURE CHARACTERISTICS DATA




LOAD LIFE DATA



FREQUENCY CHARACTERISTICS DATA




1μF/50V V 4.0 x 5.4
 10μF/16V V 4.0 x 5.4
 22μF/6.3V V 4.0 x 5.4




10μF/50V V 6.3 x 5.4
 22μF/35V V 6.3 x 5.4
 47μF/16V V 6.3 x 5.4

TEMPERATURE CHARACTERISTICS DATA



1μF/50V V 4.0 x 5.4
 10μF/16V V 4.0 x 5.4
 22μF/6.3V V 4.0 x 5.4



10μF/50V V 6.3 x 5.4
 22μF/35V V 6.3 x 5.4
 33μF/25V V 6.3 x 5.4