


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	35150-0609
Status:	Active
Overview:	VersaBlade™ Wire-to-Wire Connector System
Description:	Wire-to-Wire VersaBlade™ Hybrid Plug Housing, without Mounting Ears, 6 Circuits, Polyester Carbonate UL94V-0, Natural, Glow Wire Compatible

Documents:	
3D Model	Packaging Specification PK-35150-005 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
TUV	R72090206
UL	E29179
General	
Product Family	Crimp Housings
Series	35150
Application	Power, Wire-to-Wire
Comments	Polarized to Mating Part, Positive Lock<P><P>This Molex product is manufactured from material that has the following ratings, tested by independent agencies :. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A G
Overview	VersaBlade™ Wire-to-Wire Connector System
Product Name	VersaBlade™
UPC	756054256732
Physical	
Circuits (maximum)	6
Color - Resin	Natural
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester Alloy
Net Weight	5.026/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.20mm, 8.90mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +120°C
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-35150-005
Sales Drawing	SD-35150-060



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
35150Series

Mates With
35151 Receptacle Housing

Use With
VersaBlade™ Crimp Terminals, 35745 , 35746 , 35747

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[35150-0609](#)