

16-3P-Series Pushbutton Switches



The 16-3P-Series pushbutton switches are single pole and AC rated up to 3 amps. These momentary action switches have a slow-make, slow-break contact mechanism and require only light actuation force (4 oz. - 1 lb.). These switches are typically used in general purpose applications requiring finger actuation.

Dielectric Strength

UL/CSA: 1000V-live to dead metal parts

Electrical Life


25,000 cycles



Mechanical Life


100,000 cycles

Operating Temperature

32°F to 185°F (0°C to 85°C)



	
SOLDER LUG	INTEGRATED WIRE LEAD (no exposed conductors)
TERMINAL TYPE	



16-3POFF - 4 - CBL

¹
Base Part Number

²
Bushing

³
Actuator Style

1 BASE PART NUMBER: SERIES/POLES/CIRCUITRY/RATING/TERMINATION
Single Pole
3A 125VAC

OFF - (ON)

OFF - (ON) with overtravel ¹

ON - OFF

1A 125VAC

ON - ON

ON - ON with overtravel ¹

1 ON - 1 OFF (2 circuit)

1 ON - 1 OFF with overtravel ¹ (2 circuit)

solder lug

16-3POFF

16-3POFF-OV

16-3PON

116-P

116-P-OV

516-P

516-P-OV

wire leads

16-3APOFF

16-3APOFF-OV

16-3APON

116-AP

116-AP-OV

516-AP

516-AP-OV

2 BUSHING STYLE

2 .312 length

4 .562 length

3 ACTUATOR STYLE²

CBL black plastic color cap

CRD red plastic color cap

NOTES

¹ Overtravel only available with #4 bushing.

² When selection 3 is left blank, a standard nickel plated plunger is supplied.

() Indicates momentary function.