


FOR	Company	
	ATTN	

保密宣告
(Classified Info.)

本文列為機密文件，受雙方 **NDA(Non-Disclose Agreement)**所規範。
基此，請妥善保管文件，不可外洩給與合約無關之第三者造成雙方之損失。
The information contained herein is the exclusive property of Airwave Technologies Inc. and shall not be distributed, reproduced, or disclosed in whole or in part without prior written permission of Airwave Technologies Inc.



AWM650G RX

2.4 GHz Wideband FM Receiver Module

承認	承認	品保	工程
Dr. T.H. Chen Approve	Ben Huang Approve	Sandy Chen QA	Shih Chuan Lin E/E

Low Power Radio Solutions Ltd.



0

Revision History

[illegible]

Low Power Radio Solutions Ltd.

Contents

1. Descriptions	4
2. Feature	4
3. Application	4
4. Function block	4
5. Pin define	5
6. Pin descriptions	5
7. Absolute maximum ratings	6
8. DC/AC Electrical characteristic	6
9. Reference circuit	7
10. Dimension	8

1. Descriptions:

Airwave 2.4GHz Audio/Video wireless RF module contains one Transmitter and one Receiver. Using of the most popular 2.4GHz ISM band and designed with high reliability. Airwave RF module is compliance with the criteria of FCC and R&TTE which can transmit/receive a wide band audio & video signals up to 300 feet in open area.


2. Feature:

- Worldwide 2.4GHz ISM band (2400MHz~2483MHz).
- Conform to R&TTE & FCC stipulation.
- Compatible with both PAL and NTSC video formats.
- Compact size and low power consumption.
- Highly efficient FM-FM modulation/demodulation scheme.
- Integrating Audio/Video input and output into one module base band PCB

3. Application:

- AV Sender
- Baby monitor
- Surveillance
- Wireless Camera

4. Function block:



Two Rivers Industrial Estate, Station Lane, Witney, OX28 4BH TEL : 01993 709415 Fax 01993 705415

www.tprs.co.uk

Copyright © 2008 by Airwave Technologies Inc.

All Specification are subject to change without notice.

CH1 CH2 CH3

Channel Select

5. PIN Define (Top View)

Pin 01 **VCC**
 Pin 02 **Bypass**
 Pin 03 **GND**
 Pin 04 **Audio_R**
 Pin 05 **Audio_L**
 Pin 06 **Video**
 Pin 07 **CH3**
 Pin 08 **CH2**
 Pin 09 **CH1**



GND Pin 10
RF IN Pin 11
GND Pin 12

6. PIN Descriptions:

PIN	NAME	Descriptions
01	VCC	DC +5V power supply in ¹ .
02	BYPASS	Bypass capacitor.
03	GND	Ground.
04	Audio_R	Right sound signal output.
05	Audio_L	Left sound signal output.
06	Video	Video signal output.
07	CH3	Channel select. (See table 1).
08	CH2	Channel select. (See table 1).
09	CH1	Channel select. (See table 1).
10	GND	Ground.
11	RF IN	RF received signal input

Low Power Radio Solutions Ltd.

0

12	GND	Ground
----	-----	--------

Channel selection is four channels and default value is ch4. Other channel can be selected by pulling low to enable.

Pin9 CH1	Pin8 CH2	Pin7 CH3	Descriptions	Received Frequency (Channel)
0	0	0	Pin 9, Pin8, Pin7 connect to GND.	2414MHz (CH1)
0	0	1	Pin 9 and Pin 8 connect to GND, Pin 7 OPEN.	2414MHz (CH1)
0	1	0	Pin 9 and Pin 7 connect to GND, Pin 8 OPEN.	2414MHz (CH1)
0	1	1	Pin 9 connect to GND, Pin 8 and Pin 7 OPEN.	2414MHz (CH1)
1	0	0	Pin 8 and Pin 7 connect to GND, Pin 9 OPEN.	2432MHz (CH2)
1	0	1	Pin 8 connect to GND, Pin 9 and Pin 7 OPEN.	2432MHz (CH2)
1	1	0	Pin 7 connect to GND, Pin 9 and Pin 8 OPEN.	2450MHz (CH3)
1	1	1	Pin 9, Pin 8 and Pin 7 are OPEN.	2468MHz (CH4)

7. Absolute Maximum Ratings:

Parameters	Min.	Typ.	Max.	Unit
Storage Temperature Range	-25	-	85	°C
Supply voltage	-0.5	-	5.5	V

The maximum rating must not be exceeded at any time. Do not operate the device under conditions outside the above.


8. DC/AC Electrical characteristic:

(1) DC Electrical Characteristic:

RF/ DC Parameters	Min.	Typ.	Max.	Unit
Supply voltage	4.9	5	5.1	V
Supply current	150	160	175	mA
RF Input Level	-90		-10	dBm
Operating temperature	-10	-	60	°C
Operation Frequency Range	2400		2483	MHz
Channel Selection	PLL Synthesizer, 4CH (See Tab1)			
Channel Frequency	CH1 : 2414 MHz, CH2 : 2432 MHz CH3 : 2450 MHz, CH4 : 2468 MHz			


Low Power Radio Solutions Ltd.

Output Signal Level	1V _{P-P} , typ. (+/-0.2Volt)
Frequency Response	+/-5 dB, max. 50Hz~5.5MHz
S/N Ratio(100KHz, 1V _{P-P} Sine Wave)	40dB, min.
Audio	
Output Frequency Range	50Hz ~ 20KHz
Output Signal Level (Modulation Signal: 50Hz~15KHz Sine Wave)	2V _{P-P} , typ. (+/-0.3Volt)
S/N Ratio (50Hz ~ 15KHz)	50dB, typ. (+/-3dB)




10. Dimension:

With PIN




Low Power Radio Solutions Ltd.

0



Two Rivers Industrial Estate, Station Lane, Witney, OX28 4BH TEL : 01993 709418 Fax 01993 705415
Copyright © 2008 by Airwave Technologies Inc. All Specification are subject to change without notice.

0

Without PIN**Low Power Radio Solutions Ltd.**

Two Rivers Industrial Estate, Station Lane, Witney, OX28 4BH TEL : 01993 709418 Fax 01993 705415
Copyright © 2008 by Airwave Technologies Inc. All Specification are subject to change without notice.