

M62015L,FP

M62016L,FP

LOW POWER 2 OUTPUT SYSTEM RESET IC

DESCRIPTION

The M62015, M62016 are semiconductor integrated circuits whose optimum use is for the detection of the rise and fall in the power supply to a microcomputer system in order to reset or release the microcomputer system.

The M62015, M62016 carry out voltage detection in 2 steps and have 2 output pins. As Bi-CMOS process and low power dissipating circuits are employed, they output optimum signals through each output pin to a system that requires RAM backup.

These ICs also support the backup mode of Mitsubishi microcomputer the M16C.

FEATURES

- Bi-CMOS process realizes a configuration of low current dissipating circuits.

Circuit current

$I_{CC}=3\mu A$ (Typ. , normal mode, $V_{CC}=3.0V$)

$I_{CC}=1\mu A$ (Typ. , backup mode, $V_{CC}=2.5V$)

- Two-step detection of supply voltage

Detection voltage in normal mode $V_S=2.7V$ (Typ.)

Detection voltage in backup mode $V_{BATT}=2.0V$ (Typ.)

- Two outputs

Reset output (\overline{RESET}) : Output of compulsive reset signal


Interruption output (\overline{INT}) : Output of interruption signal

- Output forms


CMOS output : M62015

Open drain : M62016

PIN CONFIGURATION (TOP VIEW)



Outline 5P5T




Outline 8P2S-A

NC : NO CONNECTION

APPLICATION

Prevention of malfunction of microcomputer systems in electronic, equipment such as OA equipment, industrial equipment, and home-use electronic appliances.

BLOCK DIAGRAM



MITSUBISHI <Dig./Ana.INTERFACE>
M62015L,FP / M62016L,FP

LOW POWER 2 OUTPUT SYSTEM RESET IC


ABSOLUTE MAXIMUM RATINGS ($T_a=25^{\circ}\text{C}$, unless otherwise noted.)

Symbol	Parameter	Conditions	Ratings	Unit
V_{CC}	Supply voltage		8	V
I_{sink}	Output sink voltage		4	mA
P_d	Power dissipation		440	mW
K_{θ}	Thermal derating	($T_a \geq 25^{\circ}\text{C}$)	4.4	mW/ $^{\circ}\text{C}$
T_{opr}	Operating temperature		-20 to +75	$^{\circ}\text{C}$
T_{stg}	Storage temperature		-40 to +125	$^{\circ}\text{C}$

ELECTRICAL CHARACTERISTICS ($T_a=25^{\circ}\text{C}$, unless otherwise noted.)

Symbol	Parameter	Test Conditions	Limits			Unit
			Min	Typ	Max	
V_S	Supply voltage	Interruption level during V_{CC} drop	2.55	2.70	2.85	V
V_{BATT}	Battery voltage	Reset level at backup	1.85	2.00	2.15	V
ΔV_S	Hysteresis voltage	$\Delta V_S = V_{SH} - V_{SH}$		60		mV
I_{CC}	Circuit current	$V_{CC}=3.0\text{V}$: In normal mode		3.0	12	μA
		$V_{CC}=2.5\text{V}$: In backup mode		1.0	4.0	μA
V_{sat}	Sink ability	$V_{CC}=2.5\text{V}$, $I_{sink}=2\text{mA}$		0.4	0.6	V
t_d	Delay time	External capacitance $C_d=0.33\mu\text{F}$		50		ms
t_{RESET}	Reset output response time	When V_{CC} falling		50		μs
t_{INT}	Interruption output response time	When V_{CC} falling		40		μs

APPLICATION EXAMPLE




* : A pull-up resistor is required only in the case of open-drain output.

MITSUBISHI <Dig./Ana.INTERFACE>
M62015L,FP / M62016L,FP

LOW POWER 2 OUTPUT SYSTEM RESET IC

OPERATION DESCRIPTION



- ① . If VCC rises to VSH(2.76V), the $\overline{\text{INT}}$ output is set to high level.
- ② . $\overline{\text{RESET}}$ goes high t_d (s) after VSH
 $\cdot \star t_d = 1.52 \times 10^5 \times C$ (sec)
- ③ . If VCC drops to VSH (2.70V), $\overline{\text{INT}}$ goes low.
 $\cdot \star \overline{\text{RESET}}$ output continues to be held high.
- ④ . If VCC returns to VSH, the $\overline{\text{INT}}$ output is set to high level.

- ⑤ . Same as ③
- ⑥ . If VCC becomes lower than VBATT (2.00V), the $\overline{\text{RESET}}$ output is set to low thereby resetting the microcomputer and initializing system.
- ⑦ . Same as ①
- ⑧ . Same as ②
- ⑨ . Same as ③ and ⑤
- ⑩ . Same as ⑥