

MATERIALS AND FINISHES

BODY ZINC ALLOY
PLATED NICKEL

CENTER CONTACT PHOSPHOR BRONZE
PLATED GOLD



INSULATOR POLYPROPYLENE

MOUNTING POST BRASS
PLATED TIN


SOLDER TAIL STEEL
PLATED TIN

WASHER PHOSPHOR BRONZE
PLATED NICKEL




JAM NUT BRASS
PLATED NICKEL




NOTE: THESE LEADS ADJUSTABLE TO FIT
PCB PATTERN DURING INSTALLATION



RECOMMENDED PCB LAYOUT



RECOMMENDED MOUNTING HOLE
MAXIMUM PANEL THICKNESS: 5.4mm (.213)
RECOMMENDED MOUNTING TORQUE:
1.36 N-M (12 INCH-POUNDS MAX)



PART NUMBER: 73205-5033

CHG: CONVERT TO SD
EC NO: URF2009-0148
DRWN: JWIENER 2008/09/24
CHKD: SSHAH 2008/09/24
APPR: JWIENER 2008/09/24

QUALITY
SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .005	± .0005
2 PLACES	± .005	± .0005
1 PLACE	± .005	± .0005

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY	DATE
JOE	96/07/11

CHECKED BY	DATE

APPROVED BY	DATE
	96/07/11

MATERIAL NO.
732055033

SIZE
C

SCALE
DESIGN UNITS
METRIC

THIRD ANGLE
PROJECTION

TITLE
TNC JACK R/A PCB
50 OHM
TNC - J/RA/PCB

MOLEX INCORPORATED

DOCUMENT NO.
SD-73205-5033

SHEET NO.
1 OF 1