

OptiMOS[®] -P Trench Power-Transistor




Features

- P-channel - Logic Level - Enhancement mode
- Automotive AEC Q101 qualified
- MSL1 up to 260°C peak reflow
- 175°C operating temperature
- Green package (RoHS Compliant)
- Ultra low Rds(on)
- 100% Avalanche tested
- Intended for reverse battery protection

Product Summary

V_{DS}	-30	V
$R_{DS(on),max}$ (SMD version)	4	mΩ
I_D	-100	A


PG-TO263-3-2




PG-TO262-3-1



PG-TO220-3-1



Type	Package	Marking
IPB100P03P3L-04	PG-TO263-3-2	3P03L04
IPI100P03P3L-04	PG-TO262-3-1	3P03L04
IPP100P03P3L-04	PG-TO220-3-1	3P03L04



Maximum ratings, at $T_j=25^\circ\text{C}$, unless otherwise specified

Parameter	Symbol	Conditions	Value	Unit
Continuous drain current ¹⁾	I_D	$T_C=25^\circ\text{C}$, $V_{GS}=-10\text{V}$	-100	A
		$T_C=100^\circ\text{C}$, $V_{GS}=-10\text{V}^{2)}$	-100	
Pulsed drain current ²⁾	$I_{D,pulse}$	$T_C=25^\circ\text{C}$	-400	
Avalanche energy, single pulse	E_{AS}	$I_D=-80\text{A}$	450	mJ
Gate source voltage	V_{GS}		-16 / +5	V
Power dissipation	P_{tot}	$T_C=25^\circ\text{C}$	200	W
Operating and storage temperature	T_j, T_{stg}		-55 ... +175	°C
IEC climatic category; DIN IEC 68-1			55/175/56	

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	

Thermal characteristics²⁾

Thermal resistance, junction - case	R_{thJC}		-	-	0.65	K/W
Thermal resistance, junction - ambient, leaded	R_{thJA}		-	-	62	
SMD version, device on PCB	R_{thJA}	minimal footprint	-	-	62	
		6 cm ² cooling area ³⁾	-	-	40	

Electrical characteristics, at $T_j=25^\circ\text{C}$, unless otherwise specified

Static characteristics

Drain-source breakdown voltage	$V_{(BR)DSS}$	$V_{GS}=0V, I_D=-250\mu A$	-30	-	-	V
Gate threshold voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=-475\mu A$	-1	-1.5	-2.1	
Zero gate voltage drain current	I_{DSS}	$V_{DS}=-30V, V_{GS}=0V, T_j=25^\circ\text{C}$	-	-0.1	-1	μA
		$V_{DS}=-30V, V_{GS}=0V, T_j=125^\circ\text{C}^{2)}$	-	-10	-100	
Gate-source leakage current	I_{GSS}	$V_{GS}=-16V, V_{DS}=0V$	-	-10	-100	nA
Drain-source on-state resistance	$R_{DS(on)}$	$V_{GS}=-4.5V, I_D=-50A$	-	4.8	7.6	m Ω
		$V_{GS}=-4.5V, I_D=-50A, \text{SMD version}$	-	4.5	7.3	
		$V_{GS}=-10V, I_D=-80A$	-	3.3	4.3	
		$V_{GS}=-10V, I_D=-80A, \text{SMD version}$	-	3.0	4	

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	

Dynamic characteristics²⁾

Input capacitance	C_{iss}	$V_{GS}=0V, V_{DS}=-25V,$ $f=1MHz$	-	7150	9300	pF
Output capacitance	C_{oss}		-	2150	2800	
Reverse transfer capacitance	C_{rss}		-	1650	2500	
Turn-on delay time	$t_{d(on)}$	$V_{DD}=-15V,$ $V_{GS}=-10V, I_D=-50A,$ $R_G=6\Omega$	-	30	-	ns
Rise time	t_r		-	45	-	
Turn-off delay time	$t_{d(off)}$		-	200	-	
Fall time	t_f		-	180	-	

Gate Charge Characteristics²⁾

Gate to source charge	Q_{gs}	$V_{DD}=-24V,$ $I_D=-80A,$ $V_{GS}=0 \text{ to } -10V$	-	25	33	nC
Gate to drain charge	Q_{gd}		-	55	82.5	
Gate charge total	Q_g		-	150	200	
Gate plateau voltage	$V_{plateau}$		-	-3.0	-	V

Reverse Diode

Diode continuous forward current ²⁾	I_S	$T_A=25^\circ C$	-	-	-100	A
Diode pulse current ²⁾	$I_{S,pulse}$	$T_A=25^\circ C$	-	-	-400	
Diode forward voltage	V_{SD}	$V_{GS}=0V, I_F=-80A$	-0.6	-1	-1.2	V
Reverse recovery time ²⁾	t_{rr}	$V_R=-15V, I_F=-50A,$ $di_F/dt=100A/\mu s$	-	50	-	ns
Reverse recovery charge ²⁾	Q_{rr}		-	55	-	nC


¹⁾ Current is limited by bondwire; with an $R_{thJC} = 0.65 \text{ K/W}$ the chip is able to carry $I_D=-195A$ at $25^\circ C$. For detailed information see Application Note ANPS071E at www.infineon.com/optimos

²⁾ Defined by design. Not subject to production test.

³⁾ Device on 40 mm x 40 mm x 1.5 mm epoxy PCB FR4 with 6 cm² (one layer, 70 μm thick) copper area for drain connection. PCB is vertical in still air.


1 Power dissipation

$$P_{\text{tot}} = f(T_C); V_{\text{GS}} \leq -4 \text{ V}$$



2 Drain current


$$I_D = f(T_C); V_{\text{GS}} \leq -4 \text{ V}$$



3 Safe operating area

$$I_D = f(V_{\text{DS}}); T_C = 25^\circ\text{C}; D = 0$$


parameter: t_p



4 Max. transient thermal impedance


$$Z_{\text{thJC}} = f(t_p)$$

parameter: $D = t_p / T$




5 Typ. output characteristics

 $I_D = f(V_{DS}); T_j = 25^\circ\text{C}$

parameter: V_{GS}



6 Typ. drain-source on-state resistance

 $R_{DS(on)} = f(I_D); T_j = 25^\circ\text{C}$


parameter: V_{GS}


7 Typ. transfer characteristics

 $I_D = f(V_{GS}); V_{DS} = 4\text{ V}$

parameter: T_j



8 Typ. drain-source on-state resistance

 $R_{DS(on)} = f(T_j); I_D = -80\text{ A}; V_{GS} = 10\text{ V}$


9 Typ. gate threshold voltage


$$V_{GS(th)} = f(T_j); V_{GS} = V_{DS}$$

parameter: I_D



10 Typ. capacitances


$$C = f(V_{DS}); V_{GS} = 0 V; f = 1 MHz$$



11 Typical forward diode characteristics

$$I_F = f(V_{SD})$$


parameter: T_j



12 Typ. avalanche characteristics

$$I_{AV} = f(t_{AV})$$


parameter: $T_{j(start)}$



13 Typical avalanche energy


$$E_{AS} = f(T_j)$$

parameter: I_D



14 Drain-source breakdown voltage


$$V_{BR(DSS)} = f(T_j); I_D = 1 \text{ mA}$$




15 Typ. gate charge

$$V_{GS} = f(Q_{gate}); I_D = 80 \text{ A pulsed}$$

parameter: V_{DD}



16 Gate charge waveforms



Published by
Infineon Technologies AG
81726 Munich, Germany

© Infineon Technologies AG 2007
All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie"). With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies Office.
Infineon Technologies Components may only be used in life-support devices or systems with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Revision History

Version	Date	Changes
Rev 1.1	25.09.2007	Type on page 1 changed from IP_100P06P3L-04 to IP_100P03PL04