

Date: 10/27/2008

VARISTOR SPECIFICATION SHEET

MAIDA STYLE NUMBER D65ZOV301RA150

MAIDA ITEM NUMBER 01-0102

Electrical Specifications

Continuous AC Voltage	300 VAC
Continuous DC Voltage	390 VDC
Maximum DC Leakage @ 390 VDC	200 uA
Low Varistor Voltage Limit	425 VDC
High Varistor Voltage Limit	518 VDC
Nominal Varistor Voltage	472 VDC
Current for Varistor Voltage	1 mA
Maximum Clamp Voltage	790 V
Maximum Clamp Voltage Test Current	100 A
Peak Current Rating (1 Pulse)	10000 A
Peak Current Rating (2 Pulse)	6500 A
Energy Rating (8X20us)	350 J
Energy Rating (10X1000us)	350 J
Typical Capacitance	1020 pF
Impulse Response Time	< 50 ns
Minimum Hipot of Coating	2500 VDC
Minimum I.R. of Coating	1000 MΩ


Thermal Specifications

Minimum Operating Temperature	-40 °C
Maximum Operating Temperature	85 °C
Varistor Voltage Temperature Coeff	-0.05 %/°C
Minimum Storage Temperature	-50 °C
Maximum Storage Temperature	125 °C
Current/Energy Derating Above 85°C	-2.5 %/°C

Notes

Physical Specifications

Lead Style	082J1D
X Nominal	0.3 in.
X Tolerance	0.04 in.
Lead Length Nominal	1.00 in.
Lead Length Tolerance	min. in.
Y Nominal	0.147 in.
Y Tolerance	0.03 in.
d Nominal	0.032 in.
Wire Gauge	20 AWG
Minimum Marking	Z301-150UL
Nominal Disk Size	20 mm
D Maximum	0.905 in.
T Maximum	0.268 in.
H Maximum	1.03 in.



* Contact Maida for a more detailed configuration drawing.

Safety Agency Recognitions

UL 1449 File Number	E86730
UL 1414 File Number	E38785
CSA File Number	LR33468
VDE File Number	40017480
SEV File Number	96.7 70250.01



DEVELOPMENT COMPANY

P.O. Box 3529

Hampton, Virginia 23663

(757) 723-0785 Fax (757) 722-1194