


MODEL TYPE

- ☐ VLM-635-08 LPA / VLM-635-08 LPT
- ☐ VLM-650-08 LPA / VLM-650-08 LPT

OUTLINE DIMENSIONS (UNITS: mm)



1. Basic model for general laser sighting applications.
2. This model integrated optic, laser diode into a patented solid zinc alloy structure for the most economical and the best choice of laser pointer applications.
3. Provides an adjustable focus function by request.
4. Options: Connection type: Spring / Lead wire (Spring type: by order).
Output power: Class II - less than 1mW / Class IIIa - less than 5mW.
5. E.S.D. protection 15KV.

SPECIFICATIONS	635-08	650-08
Operating voltage (Vop) ☐	3 ~ 5V	
Operating current (Iop) ☐	40 $\pm$ 15mA	
Cw output power (Po)	$\leq$ 3mW	
Wavelength at peak emission (λ p)	630 ~ 645nm	645 ~ 665nm
Collimating lens ☐	Aspherical plastic ($\phi 7$)	
Housing ☐	Zinc alloy	
Spot size at 5m ☐	6 $\pm$ 2mm	
Divergence ☐	1.6 mrad	
Mean time to failure (MTTF) 3mW 25°C ☐	5000 hrs	10000 hrs
Operating temp. range ☐	+10°C ~ +40°C	
Storage temp. range ☐	-20°C ~ +65°C	