





REV.	DATE	DESCRIPTION
A	01/23/04	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S



RECOMMENDED
MOUNTING HOLES



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex						
8						DRAWN	G.R.S.	01/23/04								
7						CHECKED										
6	FERRULE	COPPER	GOLD	1			ISSUED				PART DESCRIPTION					
5	LOCK WASHER	BRASS	GOLD	1			SHEET	1 OF 1				SMA BULKHEAD CRIMP JACK (FOR RG-58C/U, 58/U CABLE)				
4	HEX NUT	BRASS	GOLD	1								PART NO.				
3	CONTACT PIN	BER. COPPER	GOLD	1								132118				
2	INSULATOR	TEFLON	NATURAL	1												
1	BODY	BRASS	GOLD	1												
DESCRIPTION					MATERIAL	FINISH	QTY	CAD FILE			DWG. NO.		REV.	SIZE	SCALE	
								C:/132/132118.DWG			132118.DWG		A	A	NA	

APPROVALS

DATE

Amphenol Connex

DRAWN

G.R.S.

01/23/04

PART DESCRIPTION

SMA BULKHEAD CRIMP JACK
(FOR RG-58C/U, 58/U CABLE)

PART NO.

132118

CAD FILE

C:/132/132118.DWG

DWG. NO.

132118.DWG

REV. A

SIZE A

SCALE NA