




LOC	DIST	REVISIONS					
IR	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B3	ECR-13-005824	27OCT2014	GG	RRP



CONTACTS PLATING :

OVERALL: Ni 2µm MIN, ALL OVER THE CONTACTS.
SOLDER ZONE: Sn 2.5µm MIN ON THE SOLDER ZONE OF THE CONTACTS.
MATING ZONE: PLATING CONFIRMS TO PRODUCT REQUIREMENTS
AS PER SPECIFICATION 108-15174.

MATERIAL :

HOUSING: PBT-GF, BLACK UL 94V0.
CONTACTS: PHOSPHOR BRONZE.

3 TE SMART CARD RECEPTACLE DESIGNED TO ACCEPT ISO 7810-7816 TYPE
INTEGRATED CIRCUIT SMART CARDS (0.76MM REF. THICKNESS) SEE SHEET 2/2

4 UL STYLE 2651 RIBBON CABLE AND,
10 POSITIONS MICRO-MATCH CONNECTOR;
TO BE MATED WITH
1-215079-0 THROUGH HOLE VERSION OR 1-188275-0 SMT VERSION.

	OBSOLETE		-	-	-	FERRITE CORE (SEE SHEET 2)	3
		I	-	-	-	RIBBON CABLE ASS'Y, L = 80mm	2
		-	I	-	-	RIBBON CABLE ASS'Y, L = 150mm	2
		-	-	I	-	RIBBON CABLE ASS'Y, L = 305mm	2
		-	-	-	I	RIBBON CABLE ASS'Y, L = 100mm	2
		I	I	I	I	SMART CARD READER ASS'Y 8 POS. WITH METAL STRAIN RELIEF	1
ASS'Y P/N 5953131	-5	-4	-3	-2	-1	DESCRIPTION	ITEM
	Qty per ASS'Y						

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. Coolen	30-Nov-04		TE Connectivity	
DIMENSIONS: mm		CHK W. Jansen	-			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD P. Jaeger	-	NAME	SMART CARD READER WITH RIBBON CABLE 8 POSITIONS	
0 PLC ±0,3 1 PLC ±0,3 2 PLC ±0,3 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-15174				
		APPLICATION SPEC -		SIZE	CAGE CODE	DRAWING NO
MATERIAL		WEIGHT -		A2		G-5953131
FINISH						RESTRICTED TO -
		CUSTOMER DRAWING		SCALE	SHEET	OF 2 REV B3

