




- NOTES:
1. RECOMMENDED BOARD THICKNESS (1.60±0.13)/.063±.005.
 2. TERMINAL USED, MOLEX 08-(30 THRU 35)-*.
 3. MAXIMUM WIRE SIZE-18 AWG WITH (0.8)/.03 INSULATION.
 4. PARTS TO BE MOISTURIZED AND SEALED IN A PLASTIC BAG.
 5. FOR PACKAGING INFORMATION: SEE PK-42242-001.

MATERIAL: NYLON, TYPE 6/6, 94V-2

ADD PKG SPECS EC NO: UCP2012-3608 DRAWN: AELHAG 2012/05/04 CHKD: J.BELL 2012/05/04 APPR: F.S.MITH 2012/05/29	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± .005 ± .005 3 PLACES ± .005 ± .010 2 PLACES ± .005 ± .014 1 PLACE ± .005 ± .036 0 PLACE ± ± ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE IN/MM DRAWN BY DATE ES 1989/02/07 CHECKED BY DATE GF 1989/02/07 APPROVED BY DATE	SCALE 4:1 DESIGN UNITS INCH	THIRD ANGLE PROJECTION	TITLE HOUSING (RIGHT ANGLE P.C. BOARD)	molex	DOCUMENT NO. SD-42242-1000	SHEET NO. 1 OF 1