




NOTES:

1. MATERIAL:
'A' = NYLON V-0 LOW HALOGEN; COLOR: BLACK
'B' = NYLON V-2 GLOW WIRE CAPABLE; COLOR: BLACK
2. FINISH: NONE
3. PRODUCT SPECIFICATION: PS-172718-0000 and 2029880001-PS
APPLICATION SPECIFICATION: AS-172718-0000
4. PACKAGING SPECIFICATION: BULK
1727080001-PK
REFER TO AS-45499-001 FOR MOISTURIZING NYLON CONNECTOR PARTS.
5. THIS PART TO BE USED WITH FEMALE TERMINAL SERIES 172718, 202988 AND TPA SERIES 172709.
6. THIS PART MATES WITH SERIES 5559, 5566, 5569 AND 172767.
7. THIS PART CONFORMS TO CLASS 'B' REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.
8. THIS PRODUCT MUST BE USED WITH THE TPA INSTALLED.
9. SEE DRAWING 1727090001-SD FOR OTHER TPA INFORMATION.
10. SEE DRAWINGS SD-172718-0000 and 2029880001-PSD FOR OTHER CRIMP TERMINAL INFORMATION.

PART NUMBER	CKTS	DIM C	DIM D	MATERIAL
1727080014	14	30.60	34.40	A
1727080114				B
1727080016	16	34.80	38.60	A
1727080116				B
1727080018	18	39.00	42.80	A
1727080118				B
1727080020	20	43.20	47.00	A
1727080120				B
1727080022	22	47.40	51.20	A
1727080122				B
1727080024	24	51.60	55.40	A
1727080124				B

14 CKT

20 CKT

16 CKT

22 CKT

18 CKT

24 CKT

14 CKT

20 CKT

16 CKT

22 CKT

18 CKT

24 CKT

14 CKT

20 CKT

16 CKT

22 CKT

18 CKT

24 CKT

14 CKT

20 CKT

16 CKT

22 CKT

18 CKT

24 CKT

14 CKT

20 CKT

16 CKT

22 CKT

18 CKT

24 CKT

14 CKT

20 CKT

16 CKT

22 CKT

18 CKT

24 CKT

14 CKT

20 CKT

16 CKT

22 CKT

18 CKT

24 CKT

14 CKT

20 CKT

16 CKT

22 CKT

18 CKT

24 CKT

14 CKT

20 CKT

16 CKT

22 CKT

18 CKT

24 CKT

14 CKT

20 CKT

16 CKT

22 CKT

18 CKT

24 CKT

14 CKT

20 CKT

16 CKT

22 CKT

18 CKT

24 CKT

14 CKT

20 CKT

16 CKT

22 CKT

18 CKT

24 CKT

14 CKT

20 CKT

16 CKT

22 CKT

18 CKT

24 CKT

14 CKT

20 CKT

16 CKT

22 CKT

18 CKT

24 CKT

14 CKT

20 CKT

16 CKT

22 CKT

18 CKT

24 CKT

14 CKT

20 CKT

16 CKT

22 CKT

18 CKT

24 CKT

14