


RECOMMENDED PANEL LAYOUT





TERMINAL DETAIL
SCALE 2X

NOTES:



1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING: 4A @125VAC/28VDC, 2A @250VAC
5. DIELECTRIC STRENGTH: 1KV RMS min. at sea level
6. ELECTRICAL LIFE: 10,000 make-and-break cycles
at full load.

7. MATERIALS:

CONTACTS: Silver Plated Cu (Q Contact material)
TERMINALS: Gold Flash Plated Cu
MOUNTING NUT: Nickel Plated zinc alloy
CONTACT SPRING: Piano Wire
KEYS: (QTY. 2) Brass with code no. A126
LOCK: Bright Ni plated zinc alloy with NI facing
TUMBLER Mechanism: 4-disc tumbler cylinder.



Pos. 1 Ref.



CIRCUIT: DP (45° INDEXING)
CONTACT CONFIGURATION

SWITCH FUNCTION	
CONNECTED TERMINAL #	
POS. 1	POS. 2
8-1	1-2

LEGEND

- =Detent Positions (45°)
- ⊙ =Key pull possible in these positions
- ▲ =MOMENTARY POS.

E-SWITCH®

C	21037	TERMINAL PLATING WAS SILVER	2/14/13	EBP
---	-------	-----------------------------	---------	-----

B	13688	CORRECT SWITCH FUNCTION	1/9/04	AR
---	-------	-------------------------	--------	----

A	11566	RELEASE FOR PRODUCTION	8/5/02	CJB
---	-------	------------------------	--------	-----

REV.	ECN No.	DESCRIPTION	DATE	CHKD
------	---------	-------------	------	------

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

TITLE				
K0129E-A126				
SCALE	DATE	DR	DWG	REV
1:1.5	8/5/02	CB	K200309	C