


## NLP110 Series

### Single and Triple Output

**Total Power:** 80-110 Watts  
**Input Voltage:** 90-264 VAC  
**# of Outputs:** Single, Triple



Rev. 02.10.09\_152  
 NLP110 Series  
 1 of 4



## Electrical Specifications

| Input                                |  |  |
|--------------------------------------|--|--|
| Input range:                         | Universal input<br>(See Note 6)  | 90-264 Vac   |
| Frequency:                           |  | 47-63 Hz   |
| Input surge current:<br>(cold start) | 120 Vac<br>230 Vac   | 18 A max.<br>35 A max.                                   |
| Safety ground<br>leakage current:    | 120 Vac, 60 Hz<br>230 Vac, 50 Hz                                       | 0.45 mA<br>0.75 mA                                       |
| Input current:                       | 120 Vac @ 80 W<br>120 Vac @ 110 W<br>230 Vac @ 80 W<br>230 Vac @ 110 W | 0.9 A rms<br>1.3 A rms<br>0.48 A rms<br>0.7 A rms        |
| Input fuse:                          | UL/IEC127  | F3.15A H, 250 Vac  |
| Output                               |  |  |
| Total regulation:<br>(line and load) | Main output<br>Auxiliary outputs                                       | ±2.0%<br>±5.0%   |
| Rise time:                           | At turn-on   | 1.0 s, max.  |
| Transient response:                  | Main output<br>75% to 100%<br>step at 0.1 A $\mu$ s                    | 5.0% or 250 mV<br>max. dev., 1 ms max.<br>recovery to 1% |
| Temperature coefficient:             |  | ±0.02%/°C  |
| Overvoltage protection:              | Main outputs   | 125%, ±10%   |
| Short circuit protection:            | Cyclic operation   | Continuous   |
| Minimum output current:              | Single and multiple  | See table  |

All specifications are typical at nominal input, full load at 25 °C unless otherwise stated.

### EMC Characteristics

|                                       |                      |           |
|---------------------------------------|----------------------|-----------|
| Conducted emissions:                  | EN55022, FCC part 15 | Level B   |
| Radiated emissions:                   | EN55022, FCC part 15 | Level A   |
| Harmonic current emission correction: | EN61000-3-2          | Compliant |
| ESD air:                              | EN61000-4-2          | Level 3   |
| ESD contact:                          | EN61000-4-2          | Level 3   |
| Surge:                                | EN61000-4-5          | Level 3   |
| Fast transients:                      | EN61000-4-4          | Level 3   |
| Radiated immunity:                    | EN61000-4-3          | Level 3   |
| Conducted immunity:                   | EN61000-4-6          | Level 3   |

### General Specifications


|                                  |   |                      |
|----------------------------------|---|----------------------|
| Hold-up time:                    | 120 Vac, 60 Hz                                      | 16.7 ms @ 110 W      |
| Efficiency:                      | 120 Vac. 80 W (-9905J)                              | 75% min.             |
| Isolation voltage:               | Input/output<br>Input/chassis                       | 3000 Vac<br>1500 Vac |
| Approvals and standards pending: | EN60950, VDE0805, IEC950, UL1950, CSA C22.2 No. 950 |                      |
| Weight:                          |   | 283 g (10 oz)        |
| MTBF demonstrated:               | MIL-HDBK-217F                                       | 220,000 hours min.   |

## Environmental Specifications

|                         |   |                    |
|-------------------------|---|--------------------|
| Thermal performance:    | Operating, ambient<br>(see derating curve)  | 0° C to +50 °C     |
|                         | Non-operating                               | -40 °C to +85 °C   |
|                         | 50 °C to 70 °C ambient convection cooled    | Derate to 50% load |
|                         | 0 °C to +50 °C, ambient convection cooled   | 80 W               |
|                         | 0 °C to +50 °C, ambient, 150 LFM forced air | 110 W              |
|                         | Peak (0 °C to +50 °C, 60 s)                 | (See Note 3)       |
| Relative humidity:      | Non-condensing                              | 5% to 95% RH       |
| Altitude:               | Operating                                   | 10,000 feet max.   |
|                         | Non-operating                               | 30,000 feet max.   |
| Vibration (See Note 5): | 5-500 Hz                                    | 2.4 G rms peak     |
| Shock                   | per MIL-STD-810E                            | 516.4 Part IV      |

### DERATING CURVE

Output Power (Watts)




## Ordering Information

| Output Voltage | Min <sup>(6)</sup> | Max <sup>(1)</sup> | 150 LFM <sup>(2)</sup> | 300 LFM <sup>(3)</sup> | Peak <sup>(4)</sup> | Ripple <sup>(5)</sup> | Total Regulation | Model Numbers <sup>(7, 14, 15)</sup> |
|----------------|--------------------|--------------------|------------------------|------------------------|---------------------|-----------------------|------------------|--------------------------------------|
| +5 V           | 0.5 A              | 15 A               | 22 A                   | 22 A                   | 22 A                | 50 mV                 | ± 2.0%           | NLP110-9605J                         |
| +12 V          | 0.3 A              | 6.4 A              | 9.2 A                  | 9.2 A                  | 11.5 A              | 120 mV                | ± 2.0%           | NLP110-9612J                         |
| +48 V          | 0 A                | 1.6 A              | 2.3 A                  | 2.3 A                  | 2.5 A               | 240 mV                | ± 2.0%           | NLP110-9617J                         |
| +24 V          | 0.2 A              | 3.2 A              | 4.6 A                  | 4.6 A                  | 6.0 A               | 240 mV                | ± 2.0%           | NLP110-9624J                         |
| +5 V (A)       | 0.5 A              | 13 A               | 16 A                   | 18 A                   | 18 A                | 50 mV                 | ± 2.0%           | NLP110-9693J                         |
| +3.3 V (B)     | 0.2 A              | 13 A               | 16 A                   | 20 A                   | 20 A                | 50 mV                 | ± 2.0%           |                                      |
| +12 V          | 0 A                | 0.65 A             | 1 A                    | 1 A                    | 1 A                 | 120 mV                | ± 5.0%           |                                      |
| +3.3 V (A)     | 0.5 A              | 13 A               | 16 A                   | 20 A                   | 22 A                | 50 mV                 | ± 2.0%           | NLP110-9694J                         |
| +2.5 V (B)     | 0.1 A              | 13 A               | 16 A                   | 20 A                   | 22 A                | 50 mV                 | ± 2.0%           |                                      |
| +12 V          | 0 A                | 0.65 A             | 1 A                    | 1 A                    | 1 A                 | 120 mV                | ± 5.0%           |                                      |
| +12 V (A)      | 0.2 A              | 6.5 A              | 8.5 A                  | 8.5 A                  | 10 A                | 120 mV                | ± 2.0%           | NLP110-9695J                         |
| +3.3 V (B)     | 0.5 A              | 13 A               | 16 A                   | 20 A                   | 22 A                | 50 mV                 | ± 2.0%           |                                      |
| -12 V          | 0 A                | 0.65 A             | 1 A                    | 1 A                    | 1 A                 | 120 mV                | ± 5.0%           |                                      |
| +12 V (A)      | 0.2 A              | 6.5 A              | 8.5 A                  | 8.5 A                  | 10 A                | 120 mV                | ± 2.0%           | NLP110-9608J                         |
| +5 V (B)       | 0.2 A              | 13 A               | 16 A                   | 18 A                   | 22 A                | 50 mV                 | ± 2.0%           |                                      |
| -12 V          | 0 A                | 0.65 A             | 1 A                    | 1 A                    | 1 A                 | 120 mV                | ± 5.0%           |                                      |

### Notes

- 1 Free air convection.  
Multiple output units: maximum continuous output power not to exceed 80 W.  
For -9693J;  $I_{3.3V} = 13 \text{ A max.}$ ;  $I_{5.0V} = 13 \text{ A max.}$ ;  $I_{3.3V} + I_{5.0V}^2 \leq 16 \text{ A}$ .  
For -9694J;  $I_{3.3V} = 13 \text{ A max.}$ ;  $I_{12V} = 13 \text{ A max.}$ ;  $I_{3.3V} + I_{12V}^2 \leq 16 \text{ A}$ .  
For -9695J;  $I_{3.3V} = 13 \text{ A max.}$ ;  $I_{12V} = 6.5 \text{ A max.}$ ;  $I_{3.3V} + I_{12V}^2 \leq 16 \text{ A}$ .  
For -9608J;  $I_{5.0V} = 13 \text{ A max.}$ ;  $I_{12V} = 6.5 \text{ A max.}$ ;  $I_{5.0V} + I_{12V}^2 \leq 16 \text{ A}$ .  
Single output units: maximum continuous output power not to exceed; 75 W on -9905J; 76.8 W on -9912J, -9924J, and -9917J.
- 2 150 LFM forced air cooling from L4 side.  
Multiple output units: maximum continuous output power not to exceed 105 W.  
For -9693J;  $I_{3.3V} = 16 \text{ A max.}$ ;  $I_{5.0V} = 16 \text{ A max.}$ ;  $I_{3.3V} + I_{5.0V}^2 \leq 20 \text{ A}$ .  
For -9694J;  $I_{3.3V} = 16 \text{ A max.}$ ;  $I_{12V} = 16 \text{ A max.}$ ;  $I_{3.3V} + I_{12V}^2 \leq 20 \text{ A}$ .  
For -9695J;  $I_{3.3V} = 16 \text{ A max.}$ ;  $I_{12V} = 8.5 \text{ A max.}$ ;  $I_{3.3V} + I_{12V}^2 \leq 20 \text{ A}$ .  
For -9608J;  $I_{5.0V} = 16 \text{ A max.}$ ;  $I_{12V} = 8.5 \text{ A max.}$ ;  $I_{5.0V} + I_{12V}^2 \leq 20 \text{ A}$ .  
Single output units: maximum continuous output power not to exceed 110 W for all models.
- 3 300 LFM forced air cooling from L4 side.  
Multiple output units: maximum continuous output power not to exceed 110 W.  
For -9693J;  $I_{3.3V} = 20 \text{ A max.}$ ;  $I_{5.0V} = 18 \text{ A max.}$ ;  $I_{3.3V} + I_{5.0V}^2 \leq 22 \text{ A}$ .  
For -9694J;  $I_{3.3V} = 20 \text{ A max.}$ ;  $I_{12V} = 20 \text{ A max.}$ ;  $I_{3.3V} + I_{12V}^2 \leq 22 \text{ A}$ .  
For -9695J;  $I_{3.3V} = 20 \text{ A max.}$ ;  $I_{12V} = 8.5 \text{ A max.}$ ;  $I_{3.3V} + I_{12V}^2 \leq 22 \text{ A}$ .  
For -9608J;  $I_{5.0V} = 20 \text{ A max.}$ ;  $I_{12V} = 8.5 \text{ A max.}$ ;  $I_{5.0V} + I_{12V}^2 \leq 22 \text{ A}$ .  
Single output units: maximum continuous output power not to exceed 110 W for all models.
- 4 Peak output current lasting less than 30 seconds with duty cycle less than 5%. During peak loading, output voltage may exceed total regulation limits.
- 5 Figure is peak-to-peak for convection power rating. Output noise measurements are made across a 20 MHz bandwidth using a 6' twisted pair, terminated with a 10  $\mu\text{F}$  electrolytic capacitor and a 0.1  $\mu\text{F}$  ceramic capacitor.
- 6 Minimum load required for correct start-up and operation on single outputs and on main output of multiple versions. Failure to observe minimum load on main output will not allow the supply to start-up correctly. Some electronic test loads have a large delay time before they start drawing current even though the voltage from the supply is present. During this time delay, there is no load on the output and as a result, the supply cannot start-up properly and maintain its correct output voltage. In these instances, a dummy resistive load across the output may be necessary to load the output of the supply until the test load can function correctly and draw the intended minimum load. Minimum load required on auxiliary outputs to maintain regulation.

- 7 For models NLP110-9608J and NLP110-9695J, the 12 V output is floating. For -12 V output, pin 11 on J2 has to be connected to Return making pin 12 the -12 V output
- 8 Three orthogonal axes, random vibration 10 minutes for each axes, 2.4 G rms 5 Hz to 500 Hz.
- 9 For optimum reliability, no part of the heatsink should exceed 110 °C, and no semiconductor case temperature should exceed 120 °C.
- 10 CAUTION: Allow a minimum of 1 second after disconnecting line power when making thermal measurements.
- 11 This product is only for inclusion by professional installers within other equipment and must not be operated as a stand alone product.
- 12 The EMI specifications reference measurements made with the power supply mounted on a grounded metal sheet extending 1 inch beyond each edge, using an unshielded cable. No external filtering required during conducted emissions testing but some applications may require additional filtering to achieve system compliance. A line choke, (ac input cords looped twice through an EMI suppression toroid) was used during radiated emissions testing. Considerable radiated testing in 1U six-sided boxes has shown that units can meet level B in typical systems. Application support is available from the factory to assist with EMI compliance.
- 13 All models require a minimum mounting stand-off of 6.35 mm (0.25 inches) in the end use product.
- 14 The 'J' suffix indicates that these parts are Pb-free (RoHS 6/6) compliant.
- 15 NOTICE: Some models do not support all options. Please contact your local Emerson Network Power representative or use the on-line model number search tool at <http://www.PowerConversion.com/products>.



#### Input Pin Connections

| J1    |               |
|-------|---------------|
| Pin 1 | AC Neutral    |
| Pin 2 | No Connection |
| Pin 3 | AC Line       |
| J3    |               |
| Pin 1 | V (A) Sense + |
| Pin 2 | V (A) Sense - |
| J4    |               |
| Pin 1 | Safety Earth  |
| J5    |               |
| Pin 1 | V (B) Sense + |
| Pin 2 | V (B) Sense - |

#### Output Pin Connections

| J2     | Single        | Triple           |
|--------|---------------|------------------|
| Pin 1  | No Connection | V (B)            |
| Pin 2  | No Connection | V (B)            |
| Pin 3  | No Connection | V (B)            |
| Pin 4  | Return        | Return           |
| Pin 5  | Return        | Return           |
| Pin 6  | Return        | Return           |
| Pin 7  | Return        | Return           |
| Pin 8  | V (A)         | V (A)            |
| Pin 9  | V (A)         | V (A)            |
| Pin 10 | V (A)         | V (A)            |
| Pin 11 | No Connection | V (C)            |
| Pin 12 | No Connection | V (C) Return (7) |

#### Input and output connectors

|  |   |
|--|---|
| <b>AC (J1) connector type</b><br>Molex 26-60-4030 or equivalent.                       | <b>Mating connectors</b>  |
| <b>DC (J2) connector type</b><br>12 position Molex Spox type 26-48-1125 or equivalent. | <b>AC (J1) mating connector type</b><br>Molex 09-50-3031 or equivalent with Molex 08-50-0105 or equivalent crimp terminals. |
| <b>Sense (J3) connector type</b><br>Molex 22-23-2021 or equivalent.                    | <b>DC (J2) mating connector type</b><br>Molex Spox type 26-03-3121 and contact 08-52-0113.                                  |
| <b>Earth (J4) connector type</b><br>Male 0.250 quick disconnect.                       | <b>Sense (J3) mating connector type</b><br>Molex 22-01-3027 and contact 08-50-0113.   |
| <b>Sense (J5) connector type</b><br>Leoco 2421P02H000.                                 | <b>Earth (J4) mating connector type</b><br>Molex 90028.   |

#### Americas

5810 Van Allen Way  
Carlsbad, CA 92008  
USA  
Telephone: +1 760 930 4600  
Facsimile: +1 760 930 0698

#### Europe (UK)

Waterfront Business Park  
Merry Hill, Dudley  
West Midlands, DY5 1LX  
United Kingdom  
Telephone: +44 (0) 1384 842 211  
Facsimile: +44 (0) 1384 843 355

#### Asia (HK)

14/F, Lu Plaza  
2 Wing Yip Street  
Kwun Tong, Kowloon  
Hong Kong  
Telephone: +852 2176 3333  
Facsimile: +852 2176 3888

For global contact, visit:

[www.PowerConversion.com](http://www.PowerConversion.com)  
[techsupport.embeddedpower@emerson.com](mailto:techsupport.embeddedpower@emerson.com)

While every precaution has been taken to ensure accuracy and completeness in this literature, Emerson Network Power assumes no responsibility, and disclaims all liability for damages resulting from use of this information or for any errors or omissions.

**Emerson Network Power.**  
The global leader in enabling  
business-critical continuity.

- AC Power
- Connectivity
- DC Power
- Embedded Computing
- **Embedded Power**
- Monitoring
- Outside Plant
- Power Switching & Controls
- Precision Cooling
- Racks & Integrated Cabinets
- Services
- Surge Protection

[EmersonNetworkPower.com](http://EmersonNetworkPower.com)

Emerson Network Power and the Emerson Network Power logo are trademarks and service marks of Emerson Electric Co.  
©2008 Emerson Electric Co.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Emerson Network Power:

[NLP110-9905J](#) [NLP110-9908J](#) [NLP110-9912J](#) [NLP110-9917J](#) [NLP110-9924J](#) [NLP110-9993J](#) [NLP110-9994J](#)  
[NLP110-9995J](#) [NLP110-9605J](#) [NLP110-9608J](#) [NLP110-9612J](#) [NLP110-9617J](#) [NLP110-9624J](#) [NLP110-9693J](#)