




LOC		DIST		REVISEMENTS			
AA		23		REV	DESCRIPTION	DATE	OWN
				C	REVISED; EC 0510-0128-01	27JUN01	DLD/KLK

△ HOUSING: NYLON MOLDING COMPOUND, BLACK.

TERMINALS: 0.3[.012] THICK PH05 BRONZE.

PLATING: NICKEL UNDERPLATE OVER ENTIRE TERMINAL. 2.54μm[.000100] MINIMUM THICKNESS.

LOCALIZED PLATING AREA: 0.254μm[.000010] THICK GOLD OVER 1.016μm[.000040] MINIMUM THICK PALLADIUM NICKEL (OVER 0.051μm[000002] MINIMUM THICK GOLD WHEN REQUIRED BY PROCESS CONDITIONS).

2. 558666-1 KEY1 (CLOSED) AS SHOWN.

KEY 5	558666-5
KEY 4	558666-4
KEY 3	558666-3
KEY 2	558666-2
KEY 1	558666-1
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RK Barker	10/31/94	AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK B. FOX	10/31/94	NAME CONNECTOR ASSEMBLY, CABLE, 15 POSITION, INFOPORT, SERIES III	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. WOLLA	10/31/94	SIZE A1	
0 PLC ±.00 1 PLC ±.00 2 PLC ±.00 3 PLC ±.00 4 PLC ±.00 ANGLES		PRODUCT SPEC	—	CAGE CODE 00779	
MATERIAL △		APPLICATION SPEC	—	DRAWING NO 558666	
FINISH △		WEIGHT	—	RESTRICTED TO —	
CUSTOMER DRAWING		SCALE 10:1		SHEET 1 OF 1	
				REV C	