



Popular Combinations : Inlet pressure 10 bar, Secondary pressure 6.3 bar, 1 bar pressure drop.




**Filter + Regulator + Lubricator Combinations + Poly bowl
5 micron element, 8 bar Regulator + Gauge and Wall Mounting Brackets**

Port size	Flow dm ³ /s	Flow (scfm)	Manual Drain	Weight	Auto Drain	Weight
1/4"	20	42	P32CB12GEMNGLNW	1.29 kg (2.84 lbs)	P32CB12GEANGLNW	1.29 kg (2.84 lbs)
3/8"	32	68	P32CB13GEMNGLNW	1.29 kg (2.84 lbs)	P32CB13GEANGLNW	1.29 kg (2.84 lbs)
1/2"	40	85	P32CB14GEMNGLNW	1.29 kg (2.84 lbs)	P32CB14GEANGLNW	1.29 kg (2.84 lbs)




**Filter/Regulator + Lubricator Combinations + Poly bowl
5 micron element, 8 bar Regulator + Gauge and Wall Mounting Brackets**

Port size	Flow dm ³ /s	Flow (scfm)	Manual Drain	Weight	Auto Drain	Weight
1/4"	22	45	P32CA12GEMNGLNW	1.03 kg (2.27 lbs)	P32CA12GEANGLNW	1.03 kg (2.27 lbs)
3/8"	33	70	P32CA13GEMNGLNW	1.03 kg (2.27 lbs)	P32CA13GEANGLNW	1.03 kg (2.27 lbs)
1/2"	43	90	P32CA14GEMNGLNW	1.03 kg (2.27 lbs)	P32CA14GEANGLNW	1.03 kg (2.27 lbs)



**Slide Valve + Filter/Regulator Combinations + Poly bowl
5 micron element, 8 bar Regulator + Gauge and Wall Mounting Brackets**

Port size	Flow dm ³ /s	Flow (scfm)	Manual Drain	Weight	Auto Drain	Weight
1/4"	22	45	P32YA12GEMNGLNW	1.5 kg (3.3 lbs)	P32YA12GEANGLNW	1.5 kg (3.3 lbs)
3/8"	33	70	P32YA13GEMNGLNW	1.5 kg (3.3 lbs)	P32YA13GEANGLNW	1.5 kg (3.3 lbs)
1/2"	43	90	P32YA14GEMNGLNW	1.5 kg (3.3 lbs)	P32YA14GEANGLNW	1.5 kg (3.3 lbs)



**Slide Valve + Filter/Regulator Combinations + Poly bowl
5 micron element, 8 bar Regulator + Gauge and Wall Mounting Brackets**

Port size	Flow dm ³ /s	Flow (scfm)	Manual Drain	Weight	Auto Drain	Weight
1/4"	22	45	P32YN12GEMNGW	1.1 kg (2.42 lbs)	P32YN12GEANGW	1.1 kg (2.42 lbs)
3/8"	33	70	P32YN13GEMNGW	1.1 kg (2.42 lbs)	P32YN13GEANGW	1.1 kg (2.42 lbs)
1/2"	43	90	P32YN14GEMNGW	1.1 kg (2.42 lbs)	P32YN14GEANGW	1.1 kg (2.42 lbs)

P 3 2						
Combination						
Combination	C					
Shut off + Combination ¹	Y					
Combination type						
F/R+L	A					
F+R+L	B					
F/R	N					
Thread type						
BSPP	1					
NPT	9					
Port size						
1/4	2					
3/8	3					
1/2	4					
E						
Drain type						
Auto drain	A					
Manual drain	M					
N						
Adjustment range						
With round gauge						
0-2 bar; 0-30 psi; 0.2 MPa					Z	
4 bar; 60 psi; 0.4 MPa					M	
8 bar; 125 psi; 0.8 MPa					G	
LN						
Add only for options with Lubricator						
Bowl type						
Poly bowl with bowl guard		G				
Metal bowl with sight glass		S				

¹ Option not available with F+R+L

Note: All bowl types are the same for each component

Example: If a "G" is specified for a F+L, both units would get a poly bowl with bowl guard.