

(1,27mm) .050"

SEAF SERIES

SEAF-30-05.0-S-08-2-A-LP-K-TR

SEAF-30-05.0-S-08-2-A-K-TR

HIGH SPEED/HIGH DENSITY OPEN PIN FIELD

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?SEAF

Insulator Material:

Black LCP

Contact Material:

Copper Alloy

Solder Charge:

95.5% Sn, 3.8% Ag, 0.7% Cu

(Tin/Lead also available.

Call Samtec.)

Operating Temp Range:

-55°C to +125°C

Plating:

Au or Sn over 50µ" (1,27µm) Ni

Contact Resistance:

5.5 mΩ

Working Voltage:

240 VAC

RoHS Compliant:


Yes

Lead-Free Solderable:

Yes



Mates with:
SEAM, SEAMP,
SEAR, SEAMI,
SEAC (Requires -LP)



Up to 500 Pins

5, 8 and 10 row footprint compatible with SamArray®. Samples recommended.

Solder charges

SEAM/SEAF 7mm Stack Height	Rated @ 3dB Insertion Loss	
	with PCB effects*	w/o PCB effects**
Single-Ended Signaling	9.5 GHz / 19 Gbps	12.5 GHz / 25 Gbps
Differential Pair Signaling	10.5 GHz / 21 Gbps	13 GHz / 26 Gbps

*Performance data includes effects of a non-optimized PCB.
**Test board losses de-embedded from performance data.
Performance data for other stack heights and complete test data available at www.samtec.com?SEAF or contact sig@samtec.com

CURRENT RATING	
AMBIENT TEMP	SEAM/SEAF
20°C	2.3A
40°C	2A
60°C	1.75A
95°C	1.14A
30 ADJACENT POSITIONS POWERED	

Low Insertion/Extraction Forces

SEAF - NO. PINS PER ROW - LEAD STYLE - PLATING OPTION - NO. OF ROWS - 2 - A - OPTION - K - TR

-10, -15, -20,
-30, -40, -50

(-10 only available in 04 row)
(-15 only available in 10 row)

Specify
LEAD
STYLE
from
chart

-L
= 10µ"
(0,25µm)
Gold on
contact area,
Matte Tin on
solder tail

-S
= 30µ"
(0,76µm)
Gold on
contact area,
Matte Tin on
solder tail

-04
= Four
Rows

-05
= Five
Rows

-06
= Six
Rows

-08
= Eight
Rows


-10
= Ten
Rows

-2
= Lead-Free
Solder Charge

-LP
= Latch Post
(-LP required
for SEAC mate only)
(Available with -05.0
lead style and -04, -05,
-08 & -10 rows only)

LEAD STYLE	A	NO. OF ROWS	B
-05.0	(5,05) .199	-04	(5,61) .221
-06.0	(6,05) .238	-05, -06	(8,20) .323
-06.5	(6,55) .258	-08	(10,69) .421
		-10	(13,23) .521


DIFFERENTIAL



ARRAY	PAIR COUNT
50x10	125
50x8	100
40x10	100

ARRAY	PAIR COUNT
40x8	80
40x6	60
30x10	75
30x8	60
30x6	45
20x10	50
20x8	40
20x5	25

Note: Some sizes, styles and options are non-standard, non-returnable.



SEAM LEAD STYLE	MATED HEIGHTS		
	-05.0	-06.0	-06.5
-02.0	7mm	8mm	8.5mm
-03.0	8mm	9mm	9.5mm
-03.5	8.5mm	9.5mm	10mm
-06.5	11.5mm	12.5mm	13mm
-07.0	12mm	13mm	13.5mm
-09.0	14mm	15mm	15.5mm
-11.0	16mm	17mm	17.5mm

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
 SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
 SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292
 SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-6083 3766
 SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683