

LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	REVISED PER 063B-0047-02	04-FEB-02	KW	CJ

D

C

B






A

D

C

B

A



- 1 MATERIAL: CONTACTS - BRASS
HOUSING - UL 94V-0 RATED HIGH TEMP NYLON, COLOR BLACK.
HOLDDOWNS: - PHOSPHOR BRONZE.
- 2 PLATING: CONTACTS - 2.54 μm MINIMUM TIN-LEAD OVER 1.27 μm MINIMUM NICKEL.
HOLDDOWNS: 2.54 μm MINIMUM TIN-LEAD OVER 1.27 μm MINIMUM NICKEL.
- 4 RECOMMENDED PC BOARD THICKNESS OF 1.57.
- 5 KAPTON VACUUM PICK UP BUTTON.

33.00	40.41	40.00	12	1-1445053-2
30.00	37.41	37.00	11	1-1445053-1
27.00	34.41	34.00	10	1-1445053-0
24.00	31.41	31.00	9	1445053-9
21.00	28.41	28.00	8	1445053-8
18.00	25.41	25.00	7	1445053-7
15.00	22.41	22.00	6	1445053-6
12.00	19.41	19.00	5	1445053-5
9.00	16.41	16.00	4	1445053-4
6.00	13.41	13.00	3	1445053-3
3.00	10.41	10.00	2	1445053-2
DIM Z	DIM V	DIM W	NO. OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN J. ROOT 07OCT2000	AMP Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK K. WHITAKER 20-FEB-2001		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. JONES 20-FEB-2001	NAME VERTICAL SURFACE MOUNT HEADER ASSY, TIN CONTACTS, SURF MOUNT HOLDDOWNS, SINGLE ROW, MICRO MATE-N-LOK™	
0 PLC $\pm$ 1 PLC $\pm$ 2 PLC ± 0.13 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm$ FINISH $\pm$		PRODUCT SPEC -	SIZE A2	
MATERIAL -		APPLICATION SPEC -	CAGE CODE 00779	
		WEIGHT -	DRAWING NO 1445053	
		CUSTOMER DRAWING	SCALE 5:1 SHEET 1 OF 1 REV A	

METRIC