




ELECTRICAL CHARACTERISTICS

- Impedance: 50 Ohm
- Working frequency: 1GHz max
- Dielectric with standing voltage: 600V
- Insulation resistance 5000: 14 Ohm
- Contact resistance < 5 mOhm
- Insertion lost: < 0.2 dB

MECHANICAL CHARACTERISTICS

- Mating force per set of contact 0.4 N to 9 N
- Mating endurance 500
- Temperature -55° to +125 °C

TOOLING

- Coaxial contact extraction tool 8630-07A

DM537415000NCLF	RIGHT ANGLE MALE COAXIAL CONTACT	1.00	1.75	2.32	3.20	RG 178 B/U RG 196 A/U KX 21 A
PART NUMBER	DESIGNATION	$\phi A^{+0.10}_0$	$\phi B^{\pm 0.05}$	$\phi C^{+0.10}_0$	$\phi D^{\pm 0.10}$	CABLE REF.

NOTE:RoHS INFORMATIONS

- The "LF" product meets European union Directives and other country regulations as described in GS-22-008.
- The product is not intended to be exposed to a manufacturing solder process.
- Packaging spec: see GS-14-920.

rev	ecn no	dr	date
A	LS05-0086	MPE	2005/10/12
B	LS05-0107	MPE	2005/12/20
C	LS07-0001	MPE	2007/01/09
D	LS07-0114	MPE	2007/04/24
E	F10-0086	LSA	2010/08/20
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302 ✓		tolerance std ISO 406 ISO 1101		projection 		 mm	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	PESSON	2005/10/12	ANGULAR	LINEAR	0.X	±0.1	size	A3	Scale	
Eng	PESSON	2005/10/12			0.XX	±0.1			5	
Chr	LEGARE	2005/10/12	0.XX		±2	0.XXX	±0.1	ECN		F10-0086
Appr	LEGARE	2005/10/12	Product family			D-SUB		Spec ref -		
			RIGHT ANGLE MALE COAXIAL CONTACT				dwg no	C01-8639-2148		Rev
			SOLDER TO CABLE							E
catalog no			-				CUSTOMER		sheet 1 of 1	