

GEM600

600 Watt Single Output Economy Technology Switchers



Commercial & Medical

2 Year Warranty

- 600W Single Output Power Supply
- Universal Input 90-264 VAC
- Standard: Active PFC, OVP, Power Fail and Inhibit (low)
- Modified and Custom Designs also Available
- Complies with EMI/RFI Regulations
- CE compliant (LVD, EMC, RoHS)



International Safety Standard Approvals



CE RoHS cULus

CONDOR

Specifications

Unless otherwise noted, all parameters are nominal values measured at 120 VAC @25°C and 0-95% relative humidity, non-condensing. For limits at unusual operating conditions, consult factory.

Output Specifications	
Combined Line and Load Voltage Regulation	±1%
Ripple	1% Vp-p max.
Transient Response	500µs max. for 50% load change, slew rate of 0.2A/µs
Protection	cycle-by-cycle current limiting, automatic recovery for overload or short circuit
Voltage adjustable	± 5%

General Specifications	
Topology	Half Bridge
Efficiency	≥ 80% at full rated load
Certifications	DEMKO-EN60950-1, IEC60950-1, UL/CSA 60950-1 & 60601-1
Hold-up Time	≥20ms at 120V input
Weight	3.75 lbs. (1.70 Kg)
MTBF	208,000 hours
Enclosure Dimensions	11.81L X 5.00W X 2.79H (in), 30.00L X 12.70W X 7.09H (cm)

Input Specifications	
AC Input Voltage Range	90-264VAC nominal
Line Frequency	47-63Hz
AC Input Current	9.0A max.
Protection	Input fuse, inrush limited

EMI / EMC Compliance Performance Requirement	
RF emissions	EMC Standard
Static Discharge immunity	EN55011/22 radiated Class A, conducted Class B
Radiated RF immunity	FCC Part 15 radiated Class A, conducted Class B
EFT/Burst immunity	EN61000-4-2, 6kV Contact Discharge, 8kV Air Discharge
Line Surge immunity	EN61000-4-3, 3V/m
Conducted RF immunity	EN61000-4-4, 2kV/5kHz
Power frequency magnetic field immunity	EN61000-4-5, 1kV Differential, 2kV Common-mode
Voltage dip immunity	EN61000-4-6, 3V
Line frequency harmonics	EN61000-4-8, 3A/m
Voltage fluctuations/flicker	EN61000-4-11 - see note 1
	EN61000-3-2, Class A
	EN61000-3-3, Complies (clause 5b)

Environmental Specifications	
Thermal Performance	Operating Temperature
Cooling	0° - 50° C with no derating Fan integrated into power supply cover with thermal shutdown
Relative Humidity	5-95% non-condensing
Altitude	0-10,000 feet
Storage Temperature Range	-40° C to +85° C

GEM600

600 Watt Single Output Economy Technology Switchers

Commercial & Medical

Model	Output (V)	Peak Current	Max Power	Peak Power (1)
GEM600-24	24V@25.0A	27.0A	600W	650W
GEM600-28	28V@21.5A	23.5A	600W	650W
GEM600-36	36V@16.7A	18.0A	600W	650W
GEM600-48	48V@12.5A	13.5A	600W	650W

Note

1. Peak for 1 minute, 10% duty cycle

EN60601-1-2-2001

Voltage Sags Compliance:

Voltage Test Level Input Voltage	Voltage Dip Input Voltage	Duration Periods	Output Voltage Deviation
100VAC	< 5VAC	10mS	<3.5%
100VAC	40VAC	100mS	<3.5%
100VAC	70VAC	500mS	<3.5%
240VAC	<12VAC	10mS	<3.5%
240VAC	96VAC	100mS	<3.5%
240VAC	168VAC	500mS	<3.5%

Optional Features

Current share and Power good signal

Multiple options available for input and output connectors. See mechanical drawing or consult factory.

Note: During 100mS voltage dip (5 cycles at 40%VAC), AC Power Fail warning may trigger. During low line 100mS voltage dip, reduced loading to 50% is required to meet deviation requirement and regulation.

Leakage Current

The leakage current is as follows:


Input	Normal		Single Fault	
	Typical	Maximum	Typical	Maximum
120VAC @ 60Hz	55uA	75uA	96uA	120uA
264VAC @ 60Hz	140uA	160uA	255uA	300uA

GEM600

600 Watt Single Output Economy Technology Switchers

Commercial & Medical

Mechanical Specifications



INPUT

TB1 - EBY 6002-03-N-01

PIN 1) AC LINE
PIN 2) AC NEUTRAL
PIN 3) GROUND

OUTPUT

TB2 - EBY 6002-03-N-01

PIN 1) +Vout
PIN 2) +Vout
PIN 3) +Vout

TB3 - EBY 6002-03-N-01

PIN 1) -Vout
PIN 2) -Vout
PIN 3) -Vout

J4 - AMP 640456-4

PIN 1) POWER GOOD
PIN 2) POWER FAIL
PIN 3) N/C
PIN 4) INHIBIT

GEM600-VV WXY-ZZ G

ROHS COMPLIANT

VALUE ADDED CONFIGURATIONS

OPTIONAL DIODE:
BLANK - NONE
D - N+1 OR-ing DIODE

OUTPUT CONNECTOR:
A - EBY P/N: 6002-03-N-01
B - BUSS BARS 10-32UNC X .375 SCREWS
C - PHOENIX CONTACT P/N: 1998959
D - PHOENIX CONTACT P/N: 1731721

INPUT CONNECTOR:
A - EBY P/N: 6002-03-N-01
T - PHOENIX CONTACT P/N: 1706785

OUTPUT VOLTAGE
24 - 24Vdc @ 25.0A
28 - 28Vdc @ 21.5A
36 - 36Vdc @ 16.7A
48 - 48Vdc @ 12.5A

Connector Information

Input 3-Terminal, Class I (ground) with screw terminals on 0.375 inch centers (see diagram above)

Output 6-Terminal with screw terminals on 0.375 inch centers (see diagram above)

Signal 0.100 connector (see diagram above)