


R4F MM Plug / R4F MM Plug Patchcord 5m

Issue
24/02/2010Page
1/1

Dimension in mm

**GENERAL****Type:**

End1
R4F Plug, for 4 Multimode channels.
Screw thread coupling device
(to be installed with a 100 Ncm torque
wrench).
Vinyl protective cap.

End2
R4F Plug, for 4 Multimode channels.
Screw thread coupling device
(to be installed with a 100 Ncm torque
wrench).
Vinyl protective cap.

Cable:

Field cable MM 50/125

Identification:

Self-laminated label, RADIALL / F760 888 640-05 /MO nb.

CHARACTERISTICS*(depending on cable construction)*

Optical : Cable assembly
Insertion Loss (@ 850 nm)
acc. to IEC 61300-3-4

End 1 (R4F)

1.50 dB (method 6)

End 2 (R4F)

Mechanical :
Endurance
Tensile load
Vibration

500 mating cycles
up to 800 N (depending on cable)
Acc. To IEC 61300.2.1

500 mating cycles
up to 800 N (depending on cable)
Acc. To IEC 61300.2.1

Environmental:
Protection
Operating temperature

IP67 (plugged)
-40°C to + 85°C

IP67 (plugged)
-40°C to + 85°C

2002/95/EC (RoHS)

Compliant

CREATION
N°PEN :
Name: MM
Date: 24/02/2010
Appr.: FP

Issue	Revisions	Name	Appr.
-------	-----------	------	-------

RADIALL®
101, rue P. Hoffmann
93116 ROSNY/BOIS
FRANCE
Tel : (33) 0149353535
Fax : (33) 0148546363