







P	LTR	DESCRIPTION	DATE	DWN	APVD
P8		REVISED PER ECR-17-018148	13DEC2017	SC	BH

3-DIMENSIONAL MODEL
NTSDETAIL A
OPTIONAL CONSTRUCTIONS

1 MATES WITH HOUSING 350865.
 2 DIMENSIONS IN BRACKETS ARE IN INCHES.
 3 DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
 4 FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
 5 CSA LOGO LOCATED APPROXIMATELY AS SHOWN
 6 MATERIAL: PA66, UL94 V-0, GWIT 775°C

6	NATURAL	1-350866-1
	RED	350866-2
	NATURAL	350866-1
	COLOR	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.	K. WHITAKER	8-12-91
DIMENSIONS:	CHK	8-12-91
mm [INCHES]	R. SWING	
0 PLC	D. SELF	8-12-91
1 PLC	PRODUCT SPEC	
2 PLC	—	
3 PLC	APPLICATION SPEC	
4 PLC	—	
ANGLES	WEIGHT	
MATERIAL	CUSTOMER DRAWING	
NYLON, UL94 V-0	A2 00779 C=350866	
FINISH	SCALE 5:1	
—	RESTRICED TO	

CAP,SINGLE CIRCUIT,
UNIVERSAL MATE-N-LOK TM