


COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				
APPLICABLE STANDARD									
RATING	OPERATING TEMPERATURE RANGE	-10 °C TO 60 °C			STORAGE TEMPERATURE RANGE	-10 °C TO 60 °C			
	VOLTAGE	AC 100 V, DC 140 V							
	CURRENT	1 A			APPLICABLE CABLE				
S P E C I F I C A T I O N S									
ITEM		TEST METHOD			REQUIREMENTS			QTAT	
CONSTRUCTION									
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.			○ ○	
MARKING		CONFIRMED VISUALLY.						○ ○	
ELECTRICAL CHARACTERISTICS									
CONTACT RESISTANCE		CONTACT SHALL BE MEASURED AT DC 1 A.			10 mΩ MAX.			○ ○	
INSULATION RESISTANCE		100 V DC			200 MΩ MIN.			○ ○	
VOLTAGE PROOF		300 V AC FOR 1 min			NO FLASHOVER OR BREAKDOWN.			○ ○	
MECHANICAL CHARACTERISTICS									
CONTACT INSERTION AND WITHDRAWAL FORCES		0 φ0.610 -0.003 BY STEEL GAUGE.			INSERTION AND WITHDRAWAL FORCES: 0.2 N MIN.			○ -	
CONNECTOR INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR, WITHOUT LOCKING DEVICE.			INSERTION AND WITHDRAWAL FORCES: 30 N MAX.			○ -	
MECHANICAL OPERATION		1000 TIMES INSERTIONS AND EXTRACTIONS			CONTACT RESISTANCE: 15 mΩ MAX.			○ -	
VIBRATION		FREQUENCY 10 TO 55 Hz, AMPLITUDE 0.75 mm, m/s² AT 2 h FOR 3 DIRECTIONS.			① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			○ -	
SHOCK		490 m/s² DURATION OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.			① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			○ -	
ENVIRONMENTAL CHARACTERISTICS									
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 °C, 90 TO 95 %, 96 h.			① INSULATION RESISTANCE: 2 MΩ MIN (AT HIGH HUMIDITY). ② INSULATION RESISTANCE: 20 MΩ MIN (AT DRY). ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			○ -	
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -30 → R/T → +85 → R/T °C TIME 30 → 10 TO 15 → 30 → 10 TO 15 min UNDER 5 CYCLES.			① INSULATION RESISTANCE: 200 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			○ -	
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h			NO HEAVY CORROSION.			○ -	
DRY HEAT		EXPOSED AT + 85 °C, 96 h.			NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			○ -	
COLD		EXPOSED AT - 30 °C, 96 h.			NO DAMAGE, CRACK AND LOOSENESS OF PARTS.			○ -	
RESISTANCE TO SOLDERING HEAT		SOLDER TEMPERATURE, +350 ± 10 °C FOR IMMERSION, DURATION, 3~4 s.			NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.			○ -	
SOLDERABILITY		SOLDERED AT SOLDER TEMPERATURE, +350 ± 10 °C FOR IMMERSION DURATION, 2~3 s.			NO DEFECT AS PINHOLE, NON-WETTING AND DE-WETTING OF SOLDER EXIST OR NOT ON THE SURFACE IMMersed.			○ -	
FOR REFERENCE ONLY Subject to change without notice									
REMARKS				DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED	
				H.Y. KOMIZO	M. SATOH		Am. Ogasawara	HRS 5.19.03 USA	
NOTE: " " ROOM TEMPERATURE. Unless otherwise specified, refer to JIS C 5402.				97.8.18	97.8.18		97.8.23		
Note QT: Qualification Test AT: Assurance Test ○: Applicable Test									
HRS HIROSE ELECTRIC CO., LTD.				SPECIFICATION SHEET			PART NO. KMC9BRD-4S		
CODE NO. (OLD) CL		DRAWING NO. ELC4-007490			CODE NO. CL 110-0015-3			1/1	

TO
R
VS

1					2					3					4				
COUNT	DESCRIPTION OF REVISIONS				BY	CHKD	DATE			COUNT	DESCRIPTION OF REVISIONS				BY	CHKD	DATE		
△										△									
△										△									
△										△									



Note:
 1 Recommended tightening torque for No.6:1.5 to 2N·m
 Recommended adhesive to prevent looseness of the screw for No.1 & No.6:LOCTITE CO.,LTD/Product No. LOCTITE 271

FOR REFERENCE ONLY
 Subject to change without notice

4	Synthetic rubber	(Black)		7	Beryllium copper	Nickel plating
3	Polyacetal	(White)		6	Steel	Nickel plating
2	Phosphor bronze	Gold plating		5	Steel	Nickel plating
1	Zinc alloy	Nickel plating				
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS	

CODE NO. (OLD)		DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
		H. YOKOMIZO	M. Satoh		M. Yoshida	HRS 5.19.03 USA
		97.8.6	97.8.18		97.8.23	
DRAWING NO. EDC4-007490		PART NO. KMC9BRD-4S				
SCALE 2:1		CODE NO. CL110-0015-3				
UNITS mm		1/1				

TO
R
US