

THIS DRAWING IS UNPUBLISHED.
VERTRAULICHE UNVERÖFFENTLICHTE ZEICHNUNG

© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION.

RELEASED FOR PUBLICATION
FREI FÜR VERÖFFENTLICHUNG

ALL INTERNATIONAL RIGHTS RESERVED.
ALLE RECHTE VORBEHALTEN

LOC
A1

DIST
—

REVISIONS
ÄNDERUNGEN

P	LTR	DESCRIPTION BESCHREIBUNG	DATE	DWN	APVD
	C4	REVISION PER EG00-2081-00 (TEXT TO ENGLISH TRANSLATED)	06-SEP-00	R.S	G.F
	D1	966899-1 and 966899-2 OBSOLETE - PER PCN EG00-0641-04	03-JUN-04	STOLZ	G.F
	D2	REVISED PER ECR-09-018681	20AUG09	VKH	RRP

STRIP FORM ON MIDDLE REEL (CARDBOARD REEL, DIA. ABOUT 450mm)
BANDWARE AUF MITTELSPULE (PAPPSPULE, Ø CA. 450mm)

4

ORDER NO. BESTELL-NR.	CROSS SECTION QUERSCHNITT	STRIP LENGTH ABISOLIER-LÄNGE	TYPE AUSFÜHRUNG	COLOUR FARBE	L ₁	L ₂	d ₁	s ₁	d ₂	COLOUR TYPE FARBREIHE	PACKING UNIT VERPACKUNGSEINHEIT	
	mm ² 1	AWG 2			/mm	/mm	/mm	/mm	/mm		PARTS/STÜCK REEL/SPULE	
966 899-1	0.25/0.34	23/22	10	NORMAL GRÜN	12 ±1.5	8 ±0.4	0.8 ^{+0.14}	0.15 ±0.05	2.0 ±0.2	1	10000	OBSOLETE
966 899-2	0.25/0.34	23/22	10	NORMAL TÜRKIS	12 ±1.5	8 ±0.4	0.8 ^{+0.14}	0.15 ±0.05	2.0 ±0.2	2	10000	OBSOLETE
966 900-1	0.50	20	10	NORMAL ORANGE	14 ±1.5	8 ±0.4	1.0 ^{+0.14}	0.15 ±0.05	2.8 ±0.2	2	10000	
966 900-2	0.50	20	10	NORMAL WHITE	14 ±1.5	8 ±0.4	1.0 ^{+0.14}	0.15 ±0.05	2.8 ±0.2	DIN/1	10000	
966 901-1	0.75	18	10	NORMAL HELLBLAU	14 ±1.5	8 ±0.4	1.2 ^{+0.14}	0.15 ±0.05	2.8 ±0.2	1	10000	
966 901-2	0.75	18	10	NORMAL WEIß	14 ±1.5	8 ±0.4	1.2 ^{+0.14}	0.15 ±0.05	2.8 ±0.2	2	10000	
966 901-3	0.75	18	10	NORMAL GRAU	14 ±1.5	8 ±0.4	1.2 ^{+0.14}	0.15 ±0.05	2.8 ±0.2	DIN	10000	
966 902-1	1.00	17	10	NORMAL GELB	14 ±1.5	8 ±0.4	1.4 ^{+0.14}	0.15 ±0.05	3.3 ±0.2	2	7500	
966 902-2	1.00	17	10	NORMAL ROT	14 ±1.5	8 ±0.4	1.4 ^{+0.14}	0.15 ±0.05	3.3 ±0.2	DIN/1	7500	
966 903-1	1.50	16	10	NORMAL ROT	14 ±1.5	8 ±0.4	1.7 ^{+0.25}	0.15 ±0.05	3.3 ±0.2	2	7500	OBSOLETE
966 903-2	1.50	16	10	NORMAL SCHWARZ	14 ±1.5	8 ±0.4	1.7 ^{+0.25}	0.15 ±0.05	3.5 ±0.2	DIN/1	7500	
966 903-3	1.50	16	10	NORMAL SCHWARZ	14 ±1.5	8 ±0.4	1.7 ^{+0.25}	0.15 ±0.05	3.5 ±0.2	DIN/1	7500	SUPERSEDED BY -2
966 904-1	2.50	14	10	NORMAL GRAU	14 ±1.5	8 ±0.4	2.2 ^{+0.25}	0.15 ±0.05	4.2 ±0.2	1	5000	
966 904-2	2.50	14	10	NORMAL BLAU	14 ±1.5	8 ±0.4	2.2 ^{+0.25}	0.15 ±0.05	4.2 ±0.2	DIN/2	5000	

1 THE AWG CROSS-SECTION CAN SLIGHT DEVIATING OF THE DIN-STANDARD CROSS-SECTION VALUES

2 RECOMMENDED STRIP LENGTH

3 MAX. INSULATION-DIA. OF WIRE: d₂ MIN.— 0.1

4 COLOUR TYPE 1: COLOUR PER TELEMECANIQUE STANDARD
COLOUR TYPE 2: COLOUR PER WEIDMÜLLER STANDARD
DIN COLOUR TYPE: COLOUR PER DIN 46228 PART 4

5 TUBULAR END-SLEEVE WITH PLASTIC SLEEVE ACCORDING TO DIN 46228 PART 4

PLASTIC SLEEVE
KUNSTSTOFFHÜLSE

COPPER SLEEVE
KUPFERHÜLSE

3

d₂

d₁

s₁

L₁

L₂

NOMINAL SIZE
NENNGRÖßE
/mm

R
/mm

0.25/0.34	2.7
0.5 — 0.75	3.6
1 — 1.5	4.2
2.5	5.0

R ±0.4

THIS DRAWING IS A CONTROLLED DOCUMENT.
DIESE ZEICHNUNG IST EIN KONTROLLIERTES DOKUMENT.

DIMENSIONS:
MASSENGEHEITEN:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
TOLERANZEN UNLESS OTHERWISE SPECIFIED:
ALLGEMEINTOLERANZEN

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES /WINKEL ± —

MATERIAL
PP/E-Cu

FINISH/OBERFLÄCHE/FARBE
Sn (SEE TABLE)

DWN
E.WERNER
29-APR-96

CHK
R.SCHMIDT
29-APR-96

APVD
G.FELDMER
12-SEP-00

PRODUCT SPEC
PRODUKTSPEZ.
—

APPLICATION SPEC
VERARBEITUNGSSPEZ.
—

WEIGHT
GEWICHT
—

Tyco
Electronics

Tyco Electronics AMP GmbH
D — 64625 Bensheim

NAME
TUBULAR END-SLEEVE WITH PLASTIC SLEEVE, STRIP FORM, MIDDLE REEL
ADERENDHÜLSE MIT KUNSTSTOFFHÜLSE , BANDWARE, MITTELSPULE

5

SIZE
A3

CAGE CODE
00779

DRAWING NO
ZEICHNUNGS-NR.
C-966899

RESTRICTED TO
NUR FÜR
—

CUSTOMER DRAWING/KUNDENZEICHNUNG

SCALE
MASSSTAB —

SHEET
BLATT 1

OF
VON 1

REV
D2

1470-19 (1/08)