

TB 600V/30A CHNL CLAMP



Features

- Accepts 10-22 AWG
- Rated at 600 V, 30 amp
- Withstands temperatures up to +150° C max
- Centerline Spacing: .375" Pitch
- Gray markable surface eliminates need for painted marking surface
- Suggested Screw Torque: 8 in-lb
- Housing: Polyester (gray), UL 94V-0 rated

Models

Description	Catalog #
TB 600V/30A CHNL CLAMP	0925