

LOC		DIST		REVISIONS					
—		—		P	LTR	DESCRIPTION	DATE	DWN	APVD
NUMMER 829822					01	S.P.C. MAB ENTFÄLLT	07.12.94	—	A.HO
VERWENDET FÜR E91-52529					02	REVISED PER ECO-09-023929	15OCT09	—	AEG
WAR NR. E91-52529					03	ECR-10-026307	13JAN11	KK	HMR

POLZ. PRO REIHE	L±0.4	BESTELL-NR.
—	—	—
2	5.08	—2
3	7.62	—3
4	10.16	—4
5	12.70	—5
6	15.24	—6
7	17.78	829 822 -7
8	20.32	—8
9	22.86	—9
10	25.40	1- -0
11	27.94	1- -1
12	30.48	1- -2
13	33.02	1- -3
14	35.56	1- -4
15	38.10	1- -5
16	40.64	1- -6
17	43.18	1- -7
18	45.72	1- -8
19	48.26	1- -9
20	50.80	2- -0
21	53.34	2- -1
22	55.88	2- -2
23	58.42	2- -3
24	60.96	2- -4
25	63.50	2- -5
26	66.04	2- -6
27	68.58	2- -7
28	71.12	2- -8
29	73.66	2- -9
30	76.20	2- -0
31	78.74	3- -1
32	81.28	3- -2
33	83.82	3- -3
34	86.36	3- -4
35	88.90	3- -5
36	91.44	3- -6
37	93.98	3- -7
38	96.52	3- -8
39	99.06	3- -9
40	101.60	4- -0
41	104.14	4- -1
42	106.68	4- -2
43	109.22	4- -3
44	111.76	4- -4
45	114.30	4- -5
46	116.84	4- -6
47	119.38	4- -7
48	121.92	4- -8
49	124.46	4- -9
50	127.00	5- 829 822 -0

1 STECKSEITE: IM BEREICH "F" 0.8 µm GOLD ÜBER 1.27 µm NICKEL
LÖTSEITE: MIN. 2.5 µm ZINN ÜBER 1.27 µm NICKEL

2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

3 OBSOLETE

KONTAKT	Cu Sn	1
STIFTGEHÄUSE	PBTP GV	GRÜN
BENENNUNG	WERKSTOFF	OBERFLÄCHE
		FARBE

ZEICHNUNG GÜLTIG AB KW 50./94.

DIMENSIONS:		DWN	12.03.91	MATERIAL	FINISH
mm		A.HO		—	—
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2 mm		CHK	13.03.91		
		M.SCHAARSCHMIDT			
		APVD	—		
		PRODUCT SPEC	—		
		APPLICATION SPEC	—		
		WEIGHT	—		

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± *

TE Connectivity

NAME: SPEZ. AMPMODU II STIFTELEISTE ZWEIREIHIG

SIZE: A4 CAGE CODE: 00779 DRAWING NO: 829822 RESTRICTED TO: —

CUSTOMER DRAWING SCALE: 4:1 SHEET: 1 OF 1 REV: 03

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

By —

COPYRIGHT —

THIS DRAWING IS UNPUBLISHED.