


AD6025 SERIES



External Dimensions



Frame:Plastic(UL:94V-0)
Impeller:Plastic(UL:94V-0)
Lead wire:UL1007AWG24

Specifications(Nominal)


*:Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM) (CFM)	Maximum Pressure (InAq) (mmAq)	*Noise Level (dB/A)	Weight (g)
60x60x25	AD06012DB257100	◎ ※ ●	12	0.03	0.36	2000	0.280 9.980	0.050 1.240	12.4	53.0
	AD06012LB257100	◎ ※ ●	12	0.05	0.60	2500	0.360 12.710	0.080 1.930	15.9	
	AD06012MB257100	◎ ※ ●	12	0.08	0.96	3500	0.490 17.340	0.130 3.330	26.9	
	AD06012HB257100	◎ ※ ●	12	0.12	1.44	4500	0.660 23.340	0.230 5.920	33.8	
	AD06012UB257100	◎ ※ ●	12	0.17	2.04	5000	0.740 25.970	0.280 7.190	37.1	
	AD06012XB257100	◎ ※ ●	12	0.26	3.12	6000	0.890 31.380	0.370 9.300	42.8	
	AD06012VB257100	◎	12	0.33	3.96	6600	0.980 34.700	0.440 11.130	46.8	
	AD06024LB257100	◎ ※ ●	24	0.04	0.96	2500	0.360 12.710	0.080 1.930	15.9	
	AD06024MB257100	◎ ※ ●	24	0.05	1.20	3500	0.490 17.340	0.130 3.330	26.9	
	AD06024HB257100	◎ ※ ●	24	0.08	1.92	4500	0.660 23.340	0.230 5.920	33.8	
	AD06024UB257100	◎ ※ ●	24	0.10	2.40	5000	0.740 25.970	0.280 7.190	37.1	
	AD06024XB257100	◎ ※ ●	24	0.14	3.36	6000	0.890 31.380	0.370 9.300	42.8	
	AD06024VB257100	◎	24	0.20	4.80	6600	0.980 34.700	0.440 11.130	46.8	

Specifications subject to change without notice.

The specification for bearing type is for reference only , for more bearing types information, please contact with your ADDA sales representative, thanks!!
(網頁上呈現產品軸承資訊均以2Ball為主, 若需其他產品資訊請聯絡您在ADDA的業務代表, 謝謝!!)



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
	✓	✓	✓					✓		✓

*Safety approvals

✓	✓		✓	✓