

Customer Information Sheet

DRAWING No.: M80-705XXXX

SHEET 2 OF 2

IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

ORDER CODE:

M80-705XXXX

TOTAL No. OF CONTACTS

27, 36, 45, 51, 63


FINISH:

05 - GOLD BODY, GOLD CLIP

POTTING WALLS

BLANK - POTTING WALLS

A = REMOVE POTTING WALLS

CONTACT No. 1
(SEE NOTE 1)

SPECIFICATION:

MATERIALS:

MOULDING = POLYAMIDE 46 UL94V-0

CONTACTS:

SHELL = COPPER ALLOY

CLIP = BERYLLIUM COPPER

JACKSCREWS, CIRCLIPS = STAINLESS STEEL

FINISH:

05 = 0.30µ CLIP, 0.25 - 0.30µ GOLD SHELL

ELECTRICAL:

CURRENT RATING AT 25°C = 3.0A MAX

CURRENT RATING AT 85°C = 2.2A MAX

VOLTAGE PROOF = 360V AC/DC

CONTACT RESISTANCE (INITIAL) = 20mΩ MAX

CONTACT RESISTANCE (AFTER CONDITIONING) = 25mΩ MAX

INSULATION RESISTANCE (INITIAL) = 1000MΩ MIN

INSULATION RESISTANCE (AFTER CONDITIONING) = 100MΩ MIN

MECHANICAL:

DURABILITY = 500 OPERATIONS

INSERTION FORCE = 2.8N MAX, 1.0N MIN


WITHDRAWAL FORCE = 1.8N MAX, 0.2N MIN

ENVIRONMENTAL:


TEMPERATURE RANGE = -55°C TO +125°C

PACKING:

TRAYS

FOR COMPLETE SPECIFICATION, SEE COMPONENT
SPECIFICATION C017XX (LATEST ISSUE)

SECTION X-X

2 x 2.0
A/F HEX

NOTES:

1. FROM No. 1 POSITION, CONTACTS NUMBERED IN SEQUENCE FROM LEFT TO RIGHT AND FROM BOTTOM ROW TO TOP ROW (LOOKING ON MATING FACE).
2. RECOMMENDED WIRE TYPE = BS 3G 210 TYPE A, PTFE INSULATED, 24 - 28AWG. MAX INSULATION DIAMETER = Ø1.10mm. STRIP WIRE BY 2.00mm.
3. RECOMMENDED HAND CRIMP TOOL = M22520/2-01, WITH POSITIONER T5747. REFER TO CRIMPING INSTRUCTION SHEET IS-01 FOR COMPLETE CRIMPING INSTRUCTIONS.
4. CONNECTOR SUPPLIED WITH CONTACTS LOOSE.
5. CONTACT INSERTION AND EXTRACTION TOOL = Z80-280. REFER TO INSTRUCTION SHEET IS-25 FOR ASSEMBLY INSTRUCTIONS.

SB	7	17.02.12	11650
NAME	ISS.	DATE	C/NOTE
APPROVED: S.BENNETT			
CHECKED: S.FLOWER			
DRAWN: I. SANDY			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWINwww.harwin.com
technical@harwin.comTHIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm

ANGLES = ±5°

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²TITLE: 3-ROW DATAMATE
FEMALE CRIMP SOCKET ASSY
(SMALL BORE) WITH JACKSCREWS

DRAWING NUMBER:

M80-705XXXXSHT
2 OF 2