






FCIconnect.com

Copyright FCI

PRODUCT NUMBER
SEE TABLE



mat'l. code NOTE 4				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HPC			
ltr	ecr	no	dr	date	tolerances unless otherwise specified				INCH/MM 	title			
K	V40941	PDP		6/1/94	angles linear	.XX±.01/.3				4 ROW VERTICAL HEADER			
L	V90018	HTB		1/8/99		.XXX±.005/.13			W/SOLDER TAIL PINS, 0 G.P.				
M	V00272	JWS		2/1/00		.XXXX±.0020/.051			scale 1:1				
N	V05-0475	DAI		7/20/05	dr	D.INGRAM	7/20/05		dwg no		sheet 1 of 4 size		
P	V05-0723	HTB		7/20/05	enrg	D.HORCHLER	7/20/05		50015		A3		
R	V05-1039	DAI		11/11/05	chr	T.BREWBAKER	7/20/05						
S	M06-0283	MHT		7/27/06	appd	D.HORCHLER	7/20/05						
sheet	revision	S	S	S	S	S							
index	sheet	1	2	3	4								
				4					5	6			

form: A3




FCIconnect.com



Copyright FCI

PRODUCT NUMBER
SEE TABLE

SECTION U-U



SECTION X-X



RECOMMENDED PCB LAYOUT
(ALL HOLES LOCATED ON .100/2.54 GRID
UNLESS OTHERWISE SPECIFIED)

mat'l. code NOTE 4				surface ISO 1302 ☒	tolerance ISO 406 ISO 1101	projection 	product family HPC
ltr	ecr	no	dr	date	tolerances unless otherwise specified	INCH/MM scale 1:1 	title
S					angles linear .XX $\pm$.01/.3		4 ROW VERTICAL HEADER
					0' $\pm$ 2' .XXX $\pm$.005/.13		W/SOLDER TAIL PINS, 0 G.P.
					.XXXX $\pm$.0020/.051		dwg no
				dr	D.INGRAM 7/20/05		sheet 2 of 4 size
				enr	D.HORCHLER 7/20/05		50015 A3
				chr	T.BREWBAKER 7/20/05		type
				app	D.HORCHLER 7/20/05		Product Customer Drawing
sheet index	revision sheet						

form: A3

	1	5	10	15	20	25	30	32	
D									
C									
B	B	B							
A	B								

1. ALL POSITIONS ARE LOADED WITH "A" EXCEPT WHERE NOTED.
2. COLUMN 1, ROW A IS DESIGNATED AS SIGNAL PIN 1, AS VIEWED FROM THE MATING FACE.
3. SIGNAL DATA FOR 50015-XX022 AND 50015-XX022LF:
SIZE 4 x 32
TOTAL NO. OF POSITIONS - 128
NO. OF POSITIONS LOADED - 128


ITEM KEY	QTY.	MATING LENGTH
A	113	.180/4.57
B	11	.260/6.60
C	4	.220/5.59

[illegible]


PRODUCT NUMBER	NUMBER OF POSITIONS NOTE 3	TAIL LENGTH ±.015/0.38	CONTACT PLATING
50015-1YYYA	YYY	.177/4.50	30u"/.76u Au
50015-1YYYC	YYY	.533/13.54	30u"/.76u Au
50015-1YYYD	YYY	.733/18.62	30u"/.76u Au
50015-1YYYG	YYY	.250/6.35	30u"/.76u Au
50015-1YYYJ	YYY	.120/3.05	30u"/.76u Au
50015-3YYYA	YYY	.177/4.50	50u"/1.27u Au
50015-3YYYC	YYY	.533/13.54	50u"/1.27u Au
50015-3YYYD	YYY	.733/18.62	50u"/1.27u Au
50015-3YYYG	YYY	.250/6.35	50u"/1.27u Au
50015-3YYYJ	YYY	.120/3.05	50u"/1.27u Au
50015-5YYYA	YYY	.177/4.50	30u"/.76u GXT
50015-5YYYALF	YYY	.177/4.50	30u"/.76u GXT
50015-5YYYC	YYY	.533/13.54	30u"/.76u GXT
50015-5YYYCLF	YYY	.533/13.54	30u"/.76u GXT
50015-5YYYD	YYY	.733/18.62	30u"/.76u GXT
50015-5YYYDLF	YYY	.733/18.62	30u"/.76u GXT
50015-5YYYG	YYY	.250/6.35	30u"/.76u GXT
50015-5YYYGLF	YYY	.250/6.35	30u"/.76u GXT
50015-5YYYJ	YYY	.120/3.05	30u"/.76u GXT
50015-5YYYJLF	YYY	.120/3.05	30u"/.76u GXT
50015-XX022	128	.250/6.35	30u"/.76u Au
50015-XX022LF	128	.250/6.35	30u"/.76u GXT

NOTES:

1. PRODUCT NUMBERING CODE



PRODUCT NUMBERING CODE FOR SELECT LOAD



- MANUFACTURE'S LOGO, PN, AND LOT CODE TO APPEAR ON THIS SURFACE.
- THIS PRODUCT IS CONFIGURED IN SIZES OF 6 THRU 80 COLUMNS IN INCREMENTS OF ONE, i.e. 6, 7, 8, 9,79, 80.
- MATERIAL:
HOUSING - GLASS AND MINERAL FILLED HIGH TEMPERTURE THERMOPLASTIC, FLAME RETARDANT PER UL94V-0. COLOR-BLACK
CONTACT - PHOS BRONZE
- PLATING:
CONTACT AREA - SEE PRODUCT NUMBER TABLE
TAILS-EITHER TIN OR TIN LEAD, SEE PRODUCT NUMBER TABLE
- DIMENSION "A" CALCULATION = .100 (2.54) X NO. OF COLUMNS + .75 (19.1)
- DIMENSION "B" CALCULATION = .100 (2.54) X NO. OF COLUMNS + .450(11.43)
- DIMENSION "C" CALCULATION = .100 (2.54) X NO. OF COLUMNS - .100(2.54)
- ALL POSITIONS ARE LOADED EXCEPT FOR -XXYYY ASSEMBLIES WHICH HAVE SELECTIVE LOADING.
- THIS PRODUCT (WITH "LF" SUFFIX) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- THIS HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10-30 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

mat'l. code NOTE 4				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HPC
ltr	ecr	no	dr	date	tolerances unless otherwise specified		title
S					angles linear .XX±.01/.3 .XXX±.005/.13 .XXXX±.0020/.05	INCH/MM	4 ROW VERTICAL HEADER W/SOLDER TAIL PINS, 0 G.P.
					0'±2'	scale 1:1	dwg no sheet 4 of 4 size
				dr	D.INGRAM 7/20/05	FCI	A3
				enr	D.HORCHLER 7/20/05		
				chr	T.BREWBAKER 7/20/05		
				appd	D.HORCHLER 7/20/05		
sheet index	revision sheet						type Product Customer Drawing

form: A3