


M67755H

150-175MHz, 7.2V, 7W, FM PORTABLE RADIO


OUTLINE DRAWING

Dimensions in mm



H12

BLOCK DIAGRAM



PIN :

- ①Pin : RF INPUT
- ②Vcc1 : 1st. DC SUPPLY
- ③VBB : BASE BIAS SUPPLY
- ④Vcc2 : 2nd. DC SUPPLY
- ⑤Po : RF OUTPUT
- ⑥GND : FIN

ABSOLUTE MAXIMUM RATINGS (T_c = 25 °C unless otherwise noted)

Symbol	Parameter	Conditions	Ratings	Unit
V _{cc}	Supply voltage	V _{BB} ≤ 5V	9.2	V
V _{BB}	Base bias		5.5	V
I _{cc}	Total current		4	A
P _{in(max)}	Input power	Z _G = Z _L = 50 Ω, V _{cc1} ≤ 7.2V	4	mW
P _{o(max)}	Output power	Z _G = Z _L = 50 Ω	10	W
T _{C(OP)}	Operation case temperature		- 30 to 110	°C
T _{stg}	Storage temperature		- 40 to 110	°C

Note. Above parameters are guaranteed independently.


ELECTRICAL CHARACTERISTICS (T_c = 25 °C unless otherwise noted)

Symbol	Parameter	Test conditions	Limits		Unit
			Min	Max	
f	Frequency range	P _{in} = 2mW V _{BB} = 5V V _{cc} = 7.2V Z _G = Z _L = 50 Ω	150	175	MHz
P _o	Output power		7		W
η _T	Total efficiency		40		%
2f _o	2nd. harmonic			- 25	dBc
3f _o	3rd. harmonic			- 30	dBc
ρ _{in}	Input VSWR			3.5	-
-	Load VSWR tolerance	V _{cc2} = 9V, V _{BB} = 5V, P _{in} = 2mW P _o = 7W (V _{cc1} : controlled) Load VSWR=20:1 (All phase), 2sec. Z _G = 50 Ω	No degradation or destroy		-


Note. Above parameters, ratings, limits and conditions are subject to change.

TYPICAL PERFORMANCE DATA


OUTPUT POWER, TOTAL CURRENT, INPUT VSWR
VS. FREQUENCY CHARACTERISTICS




OUTPUT POWER, TOTAL CURRENT,
FIRST CURRENT VS. INPUT POWER




OUTPUT POWER, TOTAL CURRENT,
FIRST CURRENT VS. INPUT POWER



OUTPUT POWER, TOTAL CURRENT,
FIRST CURRENT VS. INPUT POWER



OUTPUT POWER, TOTAL CURRENT,
FIRST CURRENT VS. SUPPLY VOLTAGE



OUTPUT POWER, TOTAL CURRENT,
FIRST CURRENT VS. SUPPLY VOLTAGE

