

Type MJS

Lightning Surge Withstand Fuse

5 x 15mm Glass Tube
RoHS 6 Compliant

HF Pb MJS Series, 5 x 15mm Lightning Surge Withstand Fuse



Description

MJS fuses have been used for Tip and Ring protection in telecommunication circuits. And they continue to be used in legacy designs. However, with advent of new issues of IEC/UL 60950 and Telcordia GR-1089 (Issue 3), MJS fuses may no longer meet all test requirements, depending on the end product circuit design. It is recommended that Types RJS and SMP be evaluated for all new telecommunication applications.

Electrical Characteristics (UL / CSA STD.248-14)

Testing current	Blow Time	
	Minimum	Maximum
100%	4 hrs.	N/A
135%	N/A	1 hr
200%	3 sec	20 sec
500%	100 msec	1.5 sec
1000%	30 msec	300 msec

Features

- Meet UL and CSA standard 248-14
- Wide operating temperature range
- Bulk and Tape & Reel packing available
- RoHS6 compliant
- Halogen Free
- Leadfree

Safety Agency Approvals

SAFETY AGENCY	SAFETY AGENCY CERTIFICATE NUMBER	AMPERE RANGE / VOLT @ I.R.ABILITY
c UL us	E20624	100mA - 7A / 125V AC @10,000A
SP	LR39772	100mA - 7A / 250V AC @200A
PS E	JET 1037-31003-1011	1A - 5A / 125V AC @500A
CE		100mA - 7A / 125V AC @10,000A 100mA - 7A / 250V AC @200A

Applications

Provide individual protection for components or internal circuits.

- Power Supplies
- Battery Charger
- Monitor
- Adapter
- Telecom Protection

LEAD FREE =

HALOGEN FREE =

Specifications subject to change without notice




FIG A




FIG B

Type MJS Lightning Surge Withstand Fuse

5 x 15 mm Glass Tube
RoHS 6 Compliant



bel

MJS Apr2013D


Electrical Specifications

Catalog Number	Ampere Rating	Typical Cold Resistance (ohm)	Volt-drop @100% In (Volt) Max.	Voltage Rating (V)	Interrupting Rating	Melting I ₂ T <10 m Sec (A ² Sec)	Melting I ₂ T @ 10 In (A ² Sec)	Peak Surge Current (Amp)		Maximum Power Dissipation (W)	Agency Approvals			
								(Fig A) 25 Pulses 10uS x 1000uS	(Fig B) 50 Pulses 10uS x 560uS		UL	SP	PSE	CE
MJS 100-R	100mA	12.5	1.88	125	100mA - 7A / 125V AC @10,000A	0.068	0.088	4.5	6.0	0.22	Y	Y		Y
MJS 125-R	125mA	7.8	1.44	125		0.107	0.138	5.6	7.5	0.24	Y	Y		Y
MJS 150-R	150mA	5.3	1.17	125		0.167	0.216	6.8	9	0.27	Y	Y		Y
MJS 200-R	200mA	3.7	1.02	125		0.26	0.34	9	12	0.30	Y	Y		Y
MJS 250-R	250mA	2.27	0.89	125		0.41	0.53	12	16	0.34	Y	Y		Y
MJS 300-R	300mA	1.57	0.78	125		0.60	0.83	15	17	0.36	Y	Y		Y
MJS 350-R	350mA	1.10	0.72	125		0.8	1.0	18	24	0.40	Y	Y		Y
MJS 400-R	400mA	0.875	0.67	125		1.0	1.3	20	27	0.42	Y	Y		Y
MJS 500-R	500mA	0.630	0.59	125		1.6	2.0	26	35	0.47	Y	Y		Y
MJS 600-R	600mA	0.440	0.53	125		2.2	2.3	29	33	0.49	Y	Y		Y
MJS 700-R	700mA	0.341	0.49	125	100mA - 7A / 250V AC @200A	3.0	4.0	38	50	0.54	Y	Y		Y
MJS 750-R	750mA	0.326	0.48	125		3.0	4.0	38	50	0.55	Y	Y		Y
MJS 800-R	800mA	0.250	0.42	125		5.0	7.0	50	66	0.60	Y	Y		Y
MJS 1-R	1A	0.195	0.39	125		5.9	7.8	56	75	0.64	Y	Y	Y	Y
MJS 1.25-R	1.25A	0.130	0.34	125		9.3	12	75	100	0.71	Y	Y	Y	Y
MJS 1.5-R	1.5A	0.100	0.29	125		15	19	94	125	0.80	Y	Y	Y	Y
MJS 2-R	2A	0.061	0.26	125		23	30	120	160	0.89	Y	Y	Y	Y
MJS 2.5-R	2.5A	0.046	0.22	125		35	47	150	200	0.99	Y	Y	Y	Y
MJS 3-R	3A	0.037	0.19	125		55	73	195	260	1.10	Y	Y	Y	Y
MJS 3.5-R	3.5A	0.029	0.18	125		69	91	225	300	1.16	Y	Y	Y	Y
MJS 4-R	4A	0.024	0.17	125		86	114	255	340	1.22	Y	Y	Y	Y
MJS 5-R	5A	0.019	0.15	125		135	179	330	440	1.36	Y	Y	Y	Y
MJS 6-R	6A	0.015	0.13	125		211	279	428	570	1.51	Y	Y		Y
MJS 7-R	7A	0.012	0.12	125		263	350	488	650	1.60	Y	Y		Y

Consult manufacturer for other ratings

Soldering Parameters

Lead-free Wave Soldering Profile	
Wave Soldering Parameter	
Average ramp-up rate	200°C / second
Heating rate during preheat	typical 1 - 2 °C / second Max. 4°C/ second
Final preheat temperature	within 125°C of soldering temperature
Peak temperature T _p	260°C
Time within +0 °C / -5°C of actual peak temperature	10 seconds
Ramp-down rate	5 °C / second max.



Type MJS Lightning Surge Withstand Fuse


5 x 15 mm Glass Tube
RoHS 6 Compliant



bel


MJS Apr2013C

Temperature Derating Curve



Average Time Current Curve

MJS - TIME CURRENT CHARACTERISTIC CURVE



Environmental Specifications

Shock Resistance	MIL-STD-202G, Method 213B, Test Condition I (100 G's peak for 6 milliseconds; Sawtooth Waveform)
Vibration Resistance	MIL-STD-202G, Method 201A (10-55 Hz, 0.06 inch, total excursion).
Salt Spray Resistance	MIL-STD-202G, Method 101E, Test condition B (48 hrs).
Insulation Resistance	MIL-STD-202G, Method 302, Test Condition A (After Opening) 10,000 ohms minimum.
Solderability	MIL-STD-202G, Method 208H
Resistance to solder Heat	MIL-STD-202G Method 210F, Test Condition B. (260+/-5 °C, 10+/-1 sec)
Thermal Shock	MIL-STD-202G, Method 107G, Test Condition B (-65 °C to +125 °C).
Operating Temperature	-55 °C to +125 °C
Terminal Strength	IEC-68-2-21

Type MJS

Lightning Surge Withstand Fuse

5 x 15 mm Glass Tube
RoHS 6 Compliant



bel

MJS Apr2013D

Physical Specifications

Materials	Body : Glass
	Cap : Nickel Plated Brass Caps
	Leads: Matte Tin Plated Copper, Diameter 0.032"
Marking	On Fuse:
	"bel", "MJS", "Current Rating", "Voltage Rating",
	"Appropriate Safety Logos", "✓" (RoHS 6 compliant)
	On label:
	"bel", "MJS", "Current Rating", "Voltage Rating", "Interrupting Rating", "Appropriate Safety Logos" and "M", "e" (China RoHS compliant).


Fuse FGNO Explanation

06XX-XXXXX-XX, [XXXXX]=Ampere Rating

Fraction	Decimal	Milliamps	Bel FGNO[XXXX]
1/32	.032	32	0032
1/25	.040	40	0040
1/20	.050	50	0050
1/16	.063	63	0063
8/100	.080	80	0080
1/10	.100	100	0100
1/8	.125	125	0125
15/100	.150	150	0150
	.160	160	0160
2/10	.200	200	0200
1/4	.250	250	0250
3/10	.300	300	0300
	.315	315	0315
3/8	.375	375	0375
4/10	.400	400	0400
1/2	.500	500	0500
6/10	.600	600	0600
	.630	630	0630
7/10	.700	700	0700
3/4	.750	750	0750
8/10	.800	800	0800

Fraction	Decimal	Amps	Bel FGNO[XXXX]
	1.0	1	1000
1-1/4	1.25	1.25	1250
1-1/2	1.50	1.5	1500
	1.60	1.6	1600
	2.0	2	2000
2-1/4	2.25	2.25	2250
2-1/2	2.5	2.5	2500
	3.0	3	3000
	3.15	3.15	3150
3-1/2	3.5	3.5	3500
	4.0	4	4000
	5.0	5	5000
	6.0	6	6000
	6.3	6.3	6300
	7.0	7	7000
7-1/2	7.5	7.5	7500
	8.0	8	8000
		10	9100
		12	9120
		15	9150
		20	9200
		25	9250
		30	9300

Mechanical Dimensions



* Diameter lead 0.032" for all ratings

Ordering Information

FUSE TYPE	0653
R	R = RoHS Compliant
AMPERE RATING	Refer to fuse FGNO explanation table
MECHANICAL CODE	1 = Standard Axial Lead Pigtail 4 = with VW Insulating Sleeve
PACKAGING CODE	1 = Bulk 500/Box 2 = T&R, 1500/Reel

Specifications subject to change without notice

Packaging

Packaging Option	Packaging Specification	Quantity	Packaging Code	Inside Tape Spacing
Bulk (Pigtail Type)	N/A	500	11	N/A
Bulk (Pigtail Type) with Insulation Sleeve	N/A	500	41	N/A
Tape & Reel, 10 mm Pitch	EIA-296-F	1500	12	53
Tape & Reel with Insulation Sleeve, 10 mm Pitch	EIA-296-F	1500	42	53

CORPORATE OFFICE

Bel Fuse Inc.
206 Van Vorst Street
Jersey City, NJ 07302
Tel 201-432-0463
Fax 201-432-9542
E-Mail: belfuse@belf.com
Website: www.belfuse.com

FAR EAST OFFICE

Bel Fuse Ltd.
8/F Luk Hop Industrial Building
8 Luk Hop Street
San Po Kong
Kowloon, Hong Kong
Tel 852-2328-5515
Fax 852-2352-3706

EUROPE OFFICE

Bel Fuse Europe Ltd.
Preston Technology Management Centre
Marsh Lane, Suite F15
Preston, Lancashire, PR1 8UQ
United Kingdom
Tel 44-1772-556601
Fax 44-1772-561008

EUROPE

Bel Stewart GmbH
Industriestrasse 20
61381 Friedrichsdorf
Germany
Tel 49-6172-9552-0
Fax 49-6172-9552-40