



ONLY 5-1241961-7, 1-1241961-9, 7-1241961-7, 2345753-1




ALL OTHER DIMENSIONS SEE SHEET 1 OF 3

KEY LAYOUT DESCRIPTION



PAY ATTENTION !
DIFFERENT CAVITY GEOMETRY AND LOCKING LATCHE OVERHANG
Bitte beachten !
Unterschiedliche Kammergeometrie und Rasthakenuberstand.

FOR 2 POS. AND 3 POS.



ALL OTHER DIMENSIONS SEE SHEET 1 OF 3
Alle anderen Masse siehe Seite 1 von 3

SPECIAL MATERIAL: UL94 V0								
2345753-1	3	6	1	15	10	PA66	NATURAL	C

SPECIAL MATERIAL								
1955507-4	4	6	1	20	15	PA66	NATURAL	1
9-1955506-2	2	6	1	10	5	UL 94 V0	NATURAL	1

PART NO	POS.	DIM C	DIM D	DIM A	DIM B	MATERIAL	COLOUR Farbe	REV./Rev.
6-1241961-7	3			15	10	PA 6 UL94V-2	NATURAL	1
4-1241961-7	3			15	10	PA 6 UL94V-2	NATURAL	A
3-1241961-7	3	4	0.5	15	10	PA 6 UL94V-2	NATURAL	A
1-1955422-7	3			15	10	PA 66 UNFILLED UL94 V0	NATURAL	A
5-1955422-7	3			15	10	PA 66 UNFILLED UL94 V0	NATURAL	A
4-1955422-3	2	6	1	10	5	PA 66 UNFILLED UL94 V0	NATURAL	A
2-1241817-3	3	4 or 6	0.5 or 1	15	10	PA 66 UL94 V-2	Green	E
0-1955422-6	3			15	10	PA 66 UNFILLED UL94 V0	NATURAL	A
8-1241961-8	3			15	10	PA 6 UL94V-2	natural	C
0-1241961-8	3			15	10			A
8-1241961-3	2	4	0.5	10	5	PA 6 UL94V-2	natural	C
3-1241961-1	2			10	5			C
0-1955422-1	2			10	5	PA 66 UNFILLED UL94 V0	NATURAL	A

LOC	DIST	P	LTR	REVISIONS	DESCRIPTION	DATE	DWN	APVD
				SSE ISHER T-01				
0-1241959-5	5			25	20			B
4-1241959-4	4	4	0.5	20	15	PA 6	Natural/natur	A
2-1241959-4	4			20	15	UL94V-2		B
0-1241959-4	4			20	15			
2-1241817-5	5	6	1	25	20	PA 6.6	Natural/natur	C
0-1241817-5	4	0.5		25	20	UL94V-2	Black/schwarz	
3-1241817-4	4			20	15		Violet/violett	
2-1241817-4	4	6	1	20	15		Grey/grau	
0-1241817-4	4	4	0.5	20	15		Natural/natur	
2-1241983-2				10	5	PA 6 UL94V-2	Green/grün	C
1-1241983-2				10	5		Violet/violett	
0-1241983-2	2	4	0.5	10	5		TARGET RAL 4001	
8-1241983-2				10	5		Yellow/gelb	
5-1241983-3				10	5		Black/schwarz	
6-1241983-2				10	5		Blue/blau	
6-1241983-2				10	5		Red/rot	
9-1241961-7		4	0.5	15	10	PA 6 UL94V-2	Natural/natur	C
9-1241961-8		4	0.5	15	10			
6-1241961-8		4	0.5	15	10			
5-1241961-8		4 or 6	0.5 or 1	15	10			
4-1241961-8		4	0.5	15	10			
7-1241961-8		4	0.5	15	10			
1-1241961-8		4 or 6	0.5 or 1	15	10			
3-1241961-8		6	1	15	10			
2-1241961-8				15	10			
2-1241961-7				15	10			
1-1241961-7		4	0.5	15	10			
9-1241961-9				15	10			
0-1241961-6				15	10			
3-1241961-3				10	5			
2-1241961-2				10	5			
5-1241961-2				10	5			
4-1241961-3				10	5			
7-1241961-2				10	5			
7-1241961-3				10	5			
6-1241961-3				10	5			
3-1241961-2		2	4	0.5	10	5		
5-1241961-3				10	5			
6-1241961-2				10	5			
0-1241961-3				10	5			
8-1241961-2				10	5			
9-1241961-2				10	5			
0-1241961-1				10	5			
9-969484-9	3	6	1	15	10	PA 6.6	Yellow/gelb	H
2-969484-8				15	10	UL94V-2		
4-969484-8		4 or 6	0.5 or 1	15	10			
0-969484-8				15	10			
9-969484-7				15	10			
8-969484-7		4	0.5	15	10			
7-969484-7				15	10			
6-969484-7				15	10			
5-969484-7		4	0.5	15	10			
4-969484-7				15	10			
3-969484-7		4	0.5	15	10			
2-969484-7		4	0.5	15	10			
1-969484-7		3	4	0.5	15	10		
0-969484-7				15	10			
9-969484-6				15	10			
8-969484-6		6	1	15	10			
7-969484-6				15	10			
6-969484-6				15	10			
5-969484-6				15	10			
4-969484-6				15	10			
3-969484-6				15	10			
2-969484-6		6	1	15	10			
1-969484-6				15	10			
0-969484-6				15	10			
9-969484-3				10	5	PA 6.6 UL94V-2	Natural/natur	H
7-969484-3				10	5			
6-969484-3		4	0.5	10	5			
5-969484-3				10	5			
4-969484-3				10	5			
3-969484-3				10	5			
2-969484-3				10	5			
1-969484-3				10	5			
0-969484-3				10	5			
9-969484-2				10	5			
8-969484-2				10	5			
7-969484-2				10	5			
6-969484-2		4	0.5	10	5			
5-969484-2				10	5			
4-969484-2				10	5			
3-969484-2				10	5			
2-969484-2				10	5			
1-969484-2				10	5			
0-969484-2				10	5			
9-969484-1				10	5			
8-969484-1		6	1	10	5			
7-969484-1				10	5			
6-969484-1		4	1	10	5			
5-969484-1				10	5			
4-969484-1		6	1	10	5			
3-969484-1				10	5			
2-969484-1		4	0.5	10	5			
1-969484-1				10	5			
0-969484-1				10	5			

THIS DRAWING IS A CONTROLLED DOCUMENT. DWN: Kishor M. 18-10-07
CHK: K.Mundz. 18-10-07

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±0.2
1 PLC ±0.2
2 PLC ±0.2
3 PLC ±0.2
4 PLC ±0.2
ANGLES ±°

STANDARD TIMER HSG. RAST 5 MARK II
Standard Timer Gehäuse RAST 5 Mark II

SIZE: A1 CAGE CODE: 00779 DRAWING NO: 1241961
RESTRICTED TO: -

MATERIAL: SEE TABLES, SHEETS PAGE 2 AND 3 OF 4. WEIGHT: -

Customer Drawing SCALE: 5:1 SHEET 2 OF 4 REV: 4

LOC	DIST	REVISIONS			
P	LTN	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

SPECIAL VERSION: UL94 V0 & GWEPT 750°C NF									
△15	2364739-5	5	4	0.5	25	20	PA66 △13 △17	BLUE	2
△16	2364739-4	4			20	15		BLUE	2
△15	1-2364739-3	3			15	10		BLUE	2
△15	2364739-3	3			15	10		BLUE	2
△15	1-2364739-2	2			10	5		BLUE	2
△15	2364739-2	2			10	5		BLUE	2
△16	3-2364739-2	2	10	5	BLUE	2			
△15	2-2364739-2	2	10	5	BLUE	2			

SPECIAL VERSION: UL94 V0 & GWT 750 NF & CTI 350									
	5-1241961-7	3	6	1	15	10	PA66 △13	NATURAL	A
	1-1241961-9	3			15	10		NATURAL	A
	7-1241961-7	3			15	10		NATURAL	A

SPECIAL VERSION: UL94 V0 & GWT 750 NF									
△15	2322164-1	4	4	0.5	20	15	PA66 △13	NATURAL	1


SPECIAL VERSION: UL94 V2 & GWT 750 NF									
	6-2178575-7	3	4	0.5	15	10	PA6 GF15 △13	NATURAL	A

SPECIAL VERSION: UL94 V0 & GWT 750 NF									
△15	3-2178412-7	3	6	1	15	10	PA66 △13 UL94 V0 & GWT 750 NF	NATURAL	1
△15	4-2178412-7	3			15	10		NATURAL	1
△15	8-2178412-2	2			10	5		NATURAL	1


UL94 V0 & GWT 750 NF									
	2322917-4	4	4	0.5	20	15	PA66 △13 UL94 V0 & GWT 750 NF	NATURAL	C
	2322917-2	2			10	5		NATURAL	C
	2315717-1	2	4	0.5	10	5		NATURAL	C
	2315717-2	2			10	5		NATURAL	C
	2315717-3	2			10	5		NATURAL	C
	2315717-4	4			20	15		NATURAL	C
	2315717-5	4			20	15		NATURAL	C
	2315717-6	3			15	10		NATURAL	C
	2315717-7	3			15	10		NATURAL	C
PART NO.	POS	DIM C △12	DIM D △12	DIMA △12	DIM B △12	MATERIAL	COLOUR	REV.	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. Kishor M 18-10-07	 TE Connectivity
DIMENSIONS: mm		CHK K. MUNDZ 18-10-07	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD Tb. Klenner 18-10-07	NAME STANDARD TIMER HSG. RAST 5 MARK II Standard Timer Gehäuse RAST 5 Mark II
0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±- 4 PLC ±- ANGLES ±° FINISH -		PRODUCT SPEC 108-18049	SIZE A1
MATERIAL SEE TABLES, SHEETS PAGE 2 AND 3 OF 4		APPLICATION SPEC	CAGE CODE 00779
		WEIGHT -	DRAWING NO 1241961
		Customer Drawing	RESTRICTED TO -
		SCALE 5:1	SHEET 3 OF 4
			REV 47


2 POSITION VARIANTS




3 POSITION VARIANTS



4 POSITION VARIANTS



5 POSITION VARIANTS



LOC	DIST	REVISIONS			
		REV	DATE	BY	APPV
		1			
		2			
		3			
		4			
		5			
		6			
		7			
		8			
		9			
		10			
		11			
		12			
		13			
		14			
		15			
		16			
		17			
		18			
		19			
		20			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	OWN: K. Kishor M. 18-10-07	CHK: K. Mundz 18-10-07
mm	0 PLC ±0.2 1 PLC ±0.2 2 PLC ±0.2 3 PLC ±0.2 4 PLC ±0.2 ANGLES ±°	APV: T. Klenner 18-10-07	NAME: STANDARD TIMER HSG. RAST 5 MARK II Standard Timer Gehäuse RAST 5 Mark II
MATERIAL: SEE TABLES. SHEETS PAGE 2 AND 3 OF 4	FINISH: -	WEIGHT: -	SIZE: A1 CAGE CODE: 00779 DRAWING NO: 1241961
		Customer Drawing	RESTRICTED TO: - SCALE: 5:1 SHEET: 4 OF 4 REV: 47