


ISO metric pressed nuts

Size	A		B	
	Max	Min	Max	Min
M2.5	5.00	4.82	1.60	1.35
M3	6.50	5.32	1.80	1.35
M4	7.00	6.78	2.00	1.75
M5	8.00	7.78	2.50	2.26
M6	10.00	8.78	3.00	2.75
M8	13.00	12.73	4.00	3.70
M10	17.00	16.73	5.00	4.70


to BS 4183 issued in 1967.



ISO metric bolts and nuts


On the bolt the rounded crest is good for plating (deposits build up on sharp corners) and transportation. It also makes for ease of manufacture. The truncated crest in the nut is to facilitate tapping, but a rounded root is permitted.

Bolt (external thread)



Design form of ISO Metric Thread.

Nut (internal thread)



Design form of ISO Metric Thread.