




PRODUCT NO.	PCB ATTACHMENT	P.C.B THICKNESS
63734-101	PRESS-PEG	2.4

NOTE 7

PRESS-FIT HOLES	
HOLE DIAMETER	
AFTER PLATING	0.65-0.80
DRILLED HOLE	0.81-0.86
COPPER PLATING	0.025 MIN.
SnPb OR Sn PLATING	0.005-0.015




NOTES:

- ① BODY MATERIAL: LCP, 30% GLASS-FILLED, FLAME RETARDENT, ACC, UL94-V0
- ② TERMINAL MATERIAL: BeCu
- ③ PLATING SOLDER TAILS: 2.5µm SnPb
- ④ PLATING CONTACT AREA: 0.80µm Au OVER 1.3µm Ni.
- ⑤ INDICATED HOLES ARE UNPLATED
- ⑥ PRODUCT MARKING: PART NUMBER & BATCH I.D.
- ⑦ ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- ⑧ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- ⑨ THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm MINIMUM THICK CIRCUIT BOARD OR FOR 20 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.



FCIconnect.com

Copyright FCI



RECOMMENDED PC BOARD
HOLE PATTERN
(COMPONENT SIDE)

mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family METRAL (tm)
ltr	ec'n no	dr	date	tolerances unless otherwise specified		MM scale 1:1	title
A	V82172	MDF	1/13/99	angles	linear		POWER CONNECTOR ASSEMBLY, 5 ROW
B	V01599	JWS	7/13/00				
C	V05-0183	DAI	04/14/05	0°±2°			
D	M06-0277	MHT	7/22/06	dr	M.FETROW	12/16/98	
E	M07-0111	MHT	2/14/07	engr	C.PENDLETON	12/16/98	
F	M08-0134	MHT	5/14/08	chr	C.PENDLETON	12/16/98	
				appd	C.PENDLETON	12/16/98	
sheet index	revision sheet	F	1				type Product Customer Drawing

