

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN R. KOMIYAMA		22JUN00		 TE Connectivity	
		CHN N. SAI		22JUN00			
DIMENSIONS: 尺寸 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 公差 除非 另有规定		APVD N. SAI		NAME	
		0-PLC 公差: ±0.3		PRODUCT SPEC		025 SERIES 24 POSITION (PCB V-TYPE) CAP HOUSING ASSEMBLY	
		1-PLC 公差: ±0.3		108-5668			
		2-PLC 公差: ±0.3		APPLICATION SPEC			
		3-PLC 公差: ±0.3		114-5250			
MATERIAL 材料 CONTACT: BRASS HOUSING: SEE TABLE		FINISH 表面处理 SEE TABLE		WEIGHT 重量 SEE TABLE		SIZE CASE CODE DRAWING NO A1 00079 C-1376111	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 of 2 REV C2		RESTRICTED TO -	

① 検査相手ワシジンの解番号は、TABLE 1 に参照。
 プラズリワシジニアセンパとよく似た検査すること。
 ② 推奨取扱い： JIS B1115、B1122 タップシヤに
 なすべく、呼び径 3、長さ 6 以下。
 (1.6mm 基準の適合)
 ③ ねじ締め付対トルク： 0.392N・m (約)
 ④ 取読説明書 NO： 411-5928
 ⑤ 図解番号は F I G. 1 に参照
 ⑥ コンタクト仕上調別記号： 表参照。
 ⑦ $\frac{-Z-}{-}$ 面から 6mm の範囲で測定。
 ⑧ $\frac{-Z-}{-}$ 面から 2mm の範囲で測定。
 ⑨ 番番 1376111-5、-6、-7、-8、-9、-11 に他の印字される。



TABLE - I	
-----------	--

D

D

C


C

B

B

A

A



CAP ASSEMBLY & PLUG ASSEMBLY ENGAGEMENT DRAWING
キャップアッセンブリ & プラグアッセンブリ 嵌合図

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED

0 PLC ±0.5

1 PLC ±0.13

2 PLC ±0.13

3 PLC ±0.001

4 PLC ±1°00'

ANGLES

FINISH

PRODUCT SPEC

SEE 1 OF 2

APPLICATION SPEC

SEE 1 OF 2

WEIGHT

SEE 1 OF 2

CUSTOMER DRAWING

TE

TE Connectivity

NAME

025 SERIES 24 POSITION (PCB V-TYPE)
CAP HOUSING ASSEMBLY

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

SCALE

4:1

SHEET

2

OF

2

REV

C2