

IRK.71, .91 SERIES

THYRISTOR/ DIODE and THYRISTOR/ THYRISTOR

NEWADD-A-pak™ Power Modules

Features

- Electrically isolated: DBC base plate
- 3500 V_{RMS} isolating voltage
- Standard JEDEC package
- Simplified mechanical designs, rapid assembly
- Auxiliary cathode terminals for wiring convenience
- High surge capability
- Wide choice of circuit configurations
- Large creepage distances
- UL E78996 approved 

75 A

95 A


Description

These IRK series of NEW ADD-A-paks use power diodes and thyristors in a variety of circuit configurations. The semiconductor chips are electrically isolated from the base plate, allowing common heatsinks and compact assemblies to be built. They can be interconnected to form single phase or three phase bridges or AC controllers. These modules are intended for general purpose high voltage applications such as high voltage regulated power supplies, lighting circuits, and temperature and motor speed control circuits.

Major Ratings and Characteristics

Parameters	IRK.71	IRK.91	Units
$I_{T(AV)}$ or $I_{F(AV)}$ @ 85°C	75	95	A
$I_{O(RMS)}$ (*)	165	210	A
I_{TSM} @ 50Hz	1665	1785	A
I_{FSM} @ 60Hz	1740	1870	A
I^2t @ 50Hz	13.86	15.91	KA ² s
@ 60Hz	12.56	14.52	KA ² s
$I^2\sqrt{t}$	138.6	159.1	KA ² √s
V_{RRM} range	400 to 1600		V
T_{STG}	- 40 to 125		°C
T_J	- 40 to 125		°C

(*) As AC switch.



IRK.71, .91 Series

Bulletin I27132 rev. D 09/97


International
IR Rectifier

ELECTRICAL SPECIFICATIONS

Voltage Ratings

Type number	Voltage Code	V_{RRM} , maximum repetitive peak reverse voltage V	V_{RSM} , maximum non-repetitive peak reverse voltage V	V_{DRM} , max. repetitive peak off-state voltage, gate open circuit V	I_{RRM} I_{DRM} 125°C mA
IRK.71/.91	04	400	500	400	15
	06	600	700	600	
	08	800	900	800	
	10	1000	1100	1000	
	12	1200	1300	1200	
	14	1400	1500	1400	
	16	1600	1700	1600	

On-state Conduction

Parameters	IRK.71	IRK.91	Units	Conditions	
$I_{T(AV)}$ Max. average on-state current (Thyristors) $I_{F(AV)}$ Max. average forward current (Diodes)	75	95	A	180° conduction, half sine wave, $T_c = 85^{\circ}\text{C}$	
$I_{O(RMS)}$ Max. continuous RMS on-state current. As AC switch	165	210			
I_{TSM} Max. peak, one cycle or non-repetitive on-state or forward current I_{FSM}	1665	1785		t=10ms No voltage reappplied	Sinusoidal half wave, Initial $T_J = T_J$ max.
	1740	1870		t=8.3ms	
	1400	1500		t=10ms 100% V_{RRM} reappplied	
	1470	1570		t=8.3ms	
	1850	2000		t=10ms $T_J = 25^{\circ}\text{C}$,	
	1940	2100		t=8.3ms no voltage reappplied	
I^2t Max. I^2t for fusing	13.86	15.91	KA^2s	t=10ms No voltage reappplied	Initial $T_J = T_J$ max.
	12.56	14.52		t=8.3ms	
	9.80	11.25		t=10ms 100% V_{RRM} reappplied	
	8.96	10.27		t=8.3ms	
	17.11	20.00		t=10ms $T_J = 25^{\circ}\text{C}$,	
	15.60	18.30		t= 8.3ms no voltage reappplied	
$I^2\sqrt{t}$ Max. $I^2\sqrt{t}$ for fusing (1)	138.6	159.1	$\text{KA}^2\sqrt{\text{s}}$	t=0.1 to 10ms, no voltage reappplied	
$V_{T(TO)}$ Max. value of threshold voltage (2)	0.82	0.80	V	Low level (3)	$T_J = T_J$ max
	0.85	0.85		High level (4)	
r_t Max. value of on-state slope resistance (2)	3.00	2.40	$\text{m}\Omega$	Low level(3)	$T_J = T_J$ max
	2.90	2.25		High level (4)	
V_{TM} Max. peak on-state or forward voltage V_{FM}	1.59	1.58	V	$I_{TM} = \pi \times I_{T(AV)}$ $I_{FM} = \pi \times I_{F(AV)}$	$T_J = 25^{\circ}\text{C}$
di/dt Max. non-repetitive rate of rise of turned on current	150		$\text{A}/\mu\text{s}$	$T_J = 25^{\circ}\text{C}$, from 0.67 V_{DRM} , $I_{TM} = \pi \times I_{T(AV)}$, $I_g = 500\text{mA}$, $t_r < 0.5 \mu\text{s}$, $t_p > 6 \mu\text{s}$	
I_H Max. holding current	200		mA	$T_J = 25^{\circ}\text{C}$, anode supply = 6V, resistive load, gate open circuit	
I_L Max. latching current	400			$T_J = 25^{\circ}\text{C}$, anode supply = 6V, resistive load	

(1) I^2t for time $t_x = I^2\sqrt{t} \times \sqrt{t_x}$

(2) Average power = $V_{T(TO)} \times I_{T(AV)} + r_t \times (I_{T(RMS)})^2$

(3) $16.7\% \times \pi \times I_{AV} < I < \pi \times I_{AV}$

(4) $I > \pi \times I_{AV}$

Triggering

Parameters		IRK.71	IRK.91	Units	Conditions	
P _{GM}	Max. peak gate power	12	12	W		
P _{G(AV)}	Max. average gate power	3.0	3.0			
I _{GM}	Max. peak gate current	3.0	3.0	A		
-V _{GM}	Max. peak negative gate voltage	10		V	Anode supply = 6V resistive load	
V _{GT}	Max. gate voltage required to trigger	4.0				
		2.5				
		1.7				
I _{GT}	Max. gate current required to trigger	270		mA	Anode supply = 6V resistive load	
		150				
		80				
V _{GD}	Max. gate voltage that will not trigger	0.25				
I _{GD}	Max. gate current that will not trigger	6		mA	T _J = 125°C, rated V _{DRM} applied	

Blocking

Parameters	IRK.71	IRK.91	Units	Conditions
I_{RRM} Max. peak reverse and off-state leakage current at V_{RRM} , V_{DRM}	15		mA	$T_J = 125^\circ\text{C}$, gate open circuit
V_{INS} RMS isolation voltage	2500 (1 min) 3500 (1 sec)		V	50 Hz, circuit to base, all terminals shorted
dv/dt Max. critical rate of rise of off-state voltage (5)	500		V/ μs	$T_J = 125^\circ\text{C}$, linear to $0.67 V_{DRM}$, gate open circuit

(5) Available with $dv/dt = 1000\text{V}/\mu\text{s}$, to complete code add S90 i.e. IRKT91/16 S90.

Thermal and Mechanical Specifications

Parameters		IRK.71	IRK.91	Units	Conditions
T _J	Junction operating temperature range	- 40 to 125		°C	
T _{stg}	Storage temp. range	- 40 to 125			
R _{thJC}	Max. internal thermal resistance, junction to case	0.165	0.135	K/W	Per module, DC operation
R _{thCS}	Typical thermal resistance case to heatsink	0.1			Mounting surface flat, smooth and greased. Flatness <0.03mm; roughness <0.02mm
T	Mounting torque ± 10% to heatsink	5		Nm	A mounting compound is recommended and the torque should be rechecked after a period of 3 hours to allow for the spread of the compound
	busbar	3			
wt	Approximate weight	83 (3)		g (oz)	
Case style		TO-240AA		JEDEC	

IRK.71, .91 Series

Bulletin I27132 rev. D 09/97


International
IR Rectifier

ΔR Conduction (per Junction)

(The following table shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC)

Devices	Sine half wave conduction					Rect. wave conduction					Units
	180°	120°	90°	60°	30°	180°	120°	90°	60°	30°	
IRK.71	0.06	0.07	0.09	0.12	0.18	0.04	0.08	0.10	0.13	0.18	°C/W
IRK.91	0.04	0.05	0.06	0.08	0.12	0.03	0.05	0.06	0.08	0.12	


Outlines Table



(*) For terminals connections, see Circuit configurations Table

NOTE: To order the Optional Hardware see Bulletin I27900

Circuit Configurations Table



Ordering Information Table

Device Code

IRK	T	91	/	16	S90
-----	---	----	---	----	-----

①
②
③
④
⑤

- 1** - Module type
- 2** - Circuit configuration (See Circuit Configuration table)
- 3** - Current code **
- 4** - Voltage code (See Voltage Ratings table)
- 5** - dv/dt code: S90 = dv/dt 1000 V/μs
No letter = dv/dt 500 V/μs

IRK.92 types
With no auxiliary cathode

** Available with no auxiliary cathode.
To specify change: 71 to 72
91 to 92
e.g. : IRKT92/16 etc.




Fig. 1 - Current Ratings Characteristics




Fig. 2 - Current Ratings Characteristics

IRK.71, .91 Series

Bulletin I27132 rev. D 09/97

International
IR Rectifier




Fig. 3 - On-state Power Loss Characteristics




Fig. 4 - On-state Power Loss Characteristics




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 6 - Maximum Non-Repetitive Surge Current




Fig. 7 - On-state Power Loss Characteristics




Fig. 8 - On-state Power Loss Characteristics




Fig. 9 - On-state Power Loss Characteristics




Fig. 10 - Current Ratings Characteristics




Fig. 11 - Current Ratings Characteristics




Fig. 12 - On-state Power Loss Characteristics




Fig. 13 - On-state Power Loss Characteristics




Fig. 14 - Maximum Non-Repetitive Surge Current




Fig. 15 - Maximum Non-Repetitive Surge Current




Fig. 16 - On-state Power Loss Characteristics




Fig. 17 - On-state Power Loss Characteristics




Fig. 18 - On-state Power Loss Characteristics




Fig. 19 - On-state Voltage Drop Characteristics




Fig. 20 - On-state Voltage Drop Characteristics

IRK.71, .91 Series

Bulletin I27132 rev. D 09/97

International
IR Rectifier




Fig. 21 - Recovery Charge Characteristics




Fig. 22 - Recovery Current Characteristics




Fig. 23 - Thermal Impedance Z_{thJC} Characteristics




Fig. 24 - Gate Characteristics